


DESIGN CROSS SECTION CHART


TOTAL THICKNESS 0.8 MM +/- 0.08 MM



L1: TOP CONDUCTOR - COPPER 0.035 MM

\* DIELECTRIC - FR-4 0.73 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	FINISHED_SIZE	PLATED	QTY
◉	0.2	PLATED	271
⊙	0.2	PLATED	25
•	0.9	PLATED	1
△	1.501	NON-PLATED	4