


* SURFACE - AIR 0 MM
L1: TOP CONDUCTOR - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.73 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM
* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 0.8 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
.	0.2	PLATED	117
▲	1.0	PLATED	4
#	0.9	NON-PLATED	2
.	2.2	NON-PLATED	2