

PMP11432ControlCard REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB100	1		PMP11432ControlCard	Any	Printed Circuit Board	
C100, C104	2	220pF	06031C221KAT2A	AVX	CAP, CERM, 220 pF, 100 V, +/- 10%, X7R, 0603	0603
C101	1	2200pF	06031C222KAT2A	AVX	CAP, CERM, 2200pF, 100V, +/-10%, X7R, 0603	0603
C102, C123	2	22pF	06035A220JAT2A	AVX	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C103, C111, C112, C113, C118, C134	6	0.1uF	C0603C104J4RACTU	Kemet	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	0603
C105	1	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1uF, 25V, +/-5%, X7R, 0603	0603
C106	1	0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 uF, 100 V, +/- 5%, X7R, 0603	0603
C107, C109	2	1uF	C0603C105K4PACTU	Kemet	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	0603
C108	1	0.01uF	0603ZC103KAT2A	AVX	CAP, CERM, 0.01 uF, 10 V, +/- 10%, X7R, 0603	0603
C110	1	10uF	C0805C106K8PACTU	Kemet	CAP, CERM, 10uF, 10V, +/-10%, X5R, 0805	0805
C114, C115, C116, C117, C135	5	2.2uF	0805YD225KAT2A	AVX	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X5R, 0805	0805
C119, C120, C121, C122, C124	5	33pF	06035A330JAT2A	AVX	CAP, CERM, 33pF, 50V, +/-5%, C0G/NP0, 0603	0603
C125, C126, C127, C128, C129, C130, C131	7	1000pF	06035A102KAT2A	AVX	CAP, CERM, 1000pF, 50V, +/-10%, C0G/NP0, 0603	0603
C132	1	4.7uF	0603ZD475KAT2A	AVX	CAP, CERM, 4.7 uF, 10 V, +/- 10%, X5R, 0603	0603
C133	1	1uF	C1608X5R1A105K	TDK	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0603	0603
D100, D101	2	30V	BAT54A-7-F	Diodes Inc.	Diode, Schottky, 30V, 0.2A, SOT-23	SOT-23
J100	1		NPPN202FJFN-RC	Sullins Connector Solutions	Receptacle, 2mm, 20x2, Gold, R/A, TH	Header, 20x2 2 mm pitch receptacle Right Angle
J101	1		PEC02SAAN	Sullins Connector Solutions	Header, 100mil, 2x1, Tin, TH	Header, 2 PIN, 100mil, Tin
J102	1		5103308-1	TE Connectivity	Header (shrouded), 100mil, 5x2, Gold, TH	5x2 Shrouded header
R100	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R101, R107	2	35.7k	CRCW060335K7FKEA	Vishay-Dale	RES, 35.7 k, 1%, 0.1 W, 0603	0603
R102	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00k ohm, 1%, 0.1W, 0603	0603
R103, R104, R105	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R106	1	100k	RC0603FR-07100KL	Yageo America	RES, 100 k, 1%, 0.1 W, 0603	0603
R108	1	1.0	CRCW08051R00JNEA	Vishay-Dale	RES, 1.0, 5%, 0.125 W, 0805	0805
R109	1	0.5	RL0603FR-070R5L	Yageo America	RES, 0.5 ohm, 1%, 0.1W, 0603	0603
R110, R118, R122, R126	4	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100 ohm, 1%, 0.1W, 0603	0603
R111, R112, R113, R114, R115	5	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R116, R117, R119, R121, R123, R124	6	100	RC0603FR-07100RL	Yageo America	RES, 100, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R120, R127, R128	3	1.5k	CRCW06031K50JNEA	Vishay-Dale	RES, 1.5k ohm, 5%, 0.1W, 0603	0603
R125	1	2.00k	RC0603FR-072KL	Yageo America	RES, 2.00k ohm, 1%, 0.1W, 0603	0603
R129	1	220	CRCW0603220RJNEA	Vishay-Dale	RES, 220, 5%, 0.1 W, 0603	0603
U100	1		OPA376AIDBVR	Texas Instruments	Low-Noise, Low Quiescent Current, Precision Operational Amplifier e-trim Series, DBV0005A	DBV0005A
U101	1		LP3985IM5-3.3	Texas Instruments	Micropower, 150mA Low-Noise Ultra Low-Dropout CMOS Voltage Regulator, 5-pin SOT-23	MF05A
U102	1		UCD3138ARJAR	Texas Instruments	Highly Integrated Digital Controller for Isolated Power, RMH0040A	RMH0040A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated