




* SURFACE - AIR 0 MM
L1: TOP CONDUCTOR - COPPER 0.035 MM
* DIELECTRIC - FR-4 0.175 MM
L2: L2 PLANE - COPPER 0.018 MM
* DIELECTRIC - FR-4 1.14 MM
L3: L3 PLANE - COPPER 0.018 MM
* DIELECTRIC - FR-4 0.175 MM
L4: BOTTOM CONDUCTOR - COPPER 0.035 MM
* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 1.60MM +/- 0.16MM



DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILLIMETERS				
FIGURE	FINISHED_SIZE	ROTATION	PLATED	QTY
◦	0.2	-	PLATED	517
◉	0.2	-	PLATED	25
▲	1.501	-	NON-PLATED	4
0	3.0x1.0	90.000	PLATED	2