

Running NDK Examples for KeyStone™ Devices

ABSTRACT

This document is a collection of frequently asked questions (FAQ) on running the NDK examples on the KeyStone™ family of devices.

Contents

1	How to Run Legacy MCSDK NDK Examples on C6678, C6670, and C6657 KeyStone™ I Devices	2
2	How to Run NDK Examples on K2H Devices	2
3	How to Run NDK Examples on K2E Devices	3
4	How to run Processor SDK Based NDK Examples on C6678 and C6657 KeyStone™ I Devices	4
5	How to run Processor SDK Based NDK Examples on K2H and K2E KeyStone™ II Devices	6
6	How to run NDK Examples on K2H Devices	6
7	How to run NDK Examples on K2E Devices	7
8	Other Resources	7

Trademarks

KeyStone, Code Composer Studio are trademarks of Texas Instruments.

1 How to Run Legacy MCSDK NDK Examples on C6678, C6670, and C6657 KeyStone™ I Devices

Generally, users would get two NDK examples, hello world and client. The following list provides the file paths.

- KeyStone™ 1 NDK examples from Latest MCSDK: C:\ti\mcsdk_2_01_02_06\examples\ndk
- KeyStone 2 NDK examples from Latest MCSDK: C:\ti\mcsdk_bios_3_01_03_06\examples\ndk

To run the examples:

1. Set the boot mode to DSP No boot mode (Emulation).
2. Connect the Ethernet cable to LAN or to the PC (EVM to PC) according to the IP mode (DHCP IP or STATIC IP) that is displayed.

Follow the next step for KeyStone I devices.

3. Select the IP mode by the DIP switch (SW9) settings in the [TMDXEVM6678L EVM Hardware Setup](#) wiki.
4. Connect core 0 and call the gel file, then load and run the NDK program (gel file must be selected).
5. Find the IP address from the local LAN server (DHCP server) in the NDK example output log in Code Composer Studio™ (CCS).
6. Type the IP address in the Internet browser to open the client application.

2 How to Run NDK Examples on K2H Devices

Use the following instructions to run NDK examples on K2H devices.

1. Set the boot mode to DSP No boot mode (Emulation).
2. Connect the Ethernet cable to LAN or to the PC (EVM to PC) according to the IP mode (DHCP IP or STATIC IP) that is displayed.

NOTE: Users must use the Ethernet port that is close to the SIM card connector (PORT0, ENET0, see [EVMK2H Hardware Setup](#)).

KeyStone II boards use DHCP IP mode by default. This setting must be changed by altering the code to run in STATIC IP mode.

```
Line no: 305 (client.c) if (0) TO if (1)
```

3. Connect core 0, then load and run the NDK program (gel file must be selected).
4. Find the IP address from the local LAN server (DHCP server) in the NDK example output log in Code Composer Studio™ (CCS).
5. Type the IP address in the Internet browser to open the client application.

3 How to Run NDK Examples on K2E Devices

Use the following instructions to run NDK examples on K2E devices.

1. Set the boot mode to DSP No boot mode or Emulation.
2. Connect the Ethernet cable to LAN or to the PC (EVM to PC) according to the IP mode (DHCP IP or STATIC IP) that is displayed.

NOTE: Users must use Ethernet PORT0. See [EVMK2E Hardware Setup](#).

KeyStone II boards use DHCP IP mode by default (on K2E devices). This setting must be changed by altering the code to run in STATIC IP mode.

Line no: 305 (client.c) if (0) TO if (1)

3. Connect core 0.
4. Run the setupPhy script (Scripts → DSP Clock Estimation → setupPhy).
5. Load and run the program.
6. Find the IP address from the local LAN server (DHCP server) in the NDK example output log in CCS.
7. Type the IP address in the Internet browser to open the client application.

The following snippet is a sample NDK log.

```
[C66xx_0] QMSS successfully initialized

CPPI successfully initialized

PA successfully initialized

TCP/IP Stack 'Hello World!' Application
TCP/IP Stack 'Hello World!' Application

PASS successfully initialized

Ethernet subsystem successfully initialized

Ethernet eventId : 48 and vectId (Interrupt) : 7

Registration of the EMAC Successful, waiting for link up ..

Service Status: DHCPC : Enabled : : 000

Service Status: DHCPC : Enabled : Running : 000

Network Added: If-1:10.100.1.26

Service Status: DHCPC : Enabled : Running : 017
```

4 How to run Processor SDK Based NDK Examples on C6678 and C6657 KeyStone™ I Devices

In the Processor SDK package, the NDK examples do not come prebuilt in the software package. The user must create these projects by running the `pdkProjectCreate.bat` script and invoking the necessary parameters (such as platform name, endianness, and others).

For C6678, do the following command to create the NDK examples (NIMU) in Processor SDK package of C6678: `C:\ti\pdk_c667x_2_0_3\pdkProjectCreate.bat C6678 all little nimu dsp`

For C6657, do the following command to create the NDK examples (NIMU) in Processor SDK package of C6657: `C:\ti\pdk_c665x_2_0_3\packages\pdkProjectCreate.bat C6657 all little nimu dsp`.

Please refer to the following TI wiki pages to know more about the creating and rebuilding the Processor SDK package.

- [Processor SDK Building The SDK](#)
- [Processor SDK — Create PDK projects](#)

Then, users get the following Hello world and Client examples in the following directory (MyExampleProjects).

- C6678:
 - `C:\ti\pdk_c667x_2_0_3\packages\MyExampleProjects\NIMU_emacClientExample_EVMC6678C66BiosExampleProject`
 - `C:\ti\pdk_c667x_2_0_3\packages\MyExampleProjects\NIMU_emacExample_EVMC6678C66BiosExampleProject`
- C6657:
 - `C:\ti\pdk_c665x_2_0_3\packages\MyExampleProjects\NIMU_emacExample_EVMC6657C66BiosExampleProject`

Use the following instructions to run the Processor SDK examples on the EVM.

1. Set boot mode to DSP No boot mode (Emulation).
2. Connect the Ethernet cable to LAN (switch) or to the host PC (EVM to PC) according to the desired IP mode (DHCP IP or STATIC IP).
3. Use the following KeyStone I board (C6678 and C6657) hardware-setup pages for setting up the emulator and boot mode.
 - [TMDXEVM6678L EVM Hardware Setup](#)
 - [TMDSEVM6657L EVM Hardware Setup](#)

By default, the KeyStone NDK hello world and client examples are configured to STATIC IP mode or DHCP IP mode; users can alter the examples to run the code in a different mode (see the following code snippets).

For the C6678 Hello world example (for DHCP IP):

```
C:\ti\pdk_c667x_2_0_3\packages\ti\transport\ndk\nimu\example\helloWorld\src
Line no: 322 (helloworld.c)
if (1)
to
if (0)
```

For the C6678 Client example (for STATIC IP):

```
C:\ti\pdk_c667x_2_0_3\packages\ti\transport\ndk\nimu\example\client\src
Line no: 263 (client.c)
if (0)
to
if (1)
```

For the C6657 Hello world example (for STATIC IP):

```
C:\ti\pdk_c665x_2_0_3\packages\ti\transport\ndk\nimu\example\helloWorld\src
Line no: 322 (helloworld.c)
if (0)
to
if (1)
```

4. Rebuild the project.
5. Connect core 0 and call the gel file, then load and run the NDK program (ensure that the appropriate gel file is selected).
Now, the EVM board will get the IP address from the local LAN server (DHCP server) and print the IP in the NDK example output log on the CCS console.
6. Type the IP address in the browser for running the NDK Client example.
7. Use the following command terminal based winapps to test the connectivity for the Hello world NDK example: C:\ti\ndk_2_24_03_35\packages\ti\ndk\winapps.

5 How to run Processor SDK Based NDK Examples on K2H and K2E KeyStone™ II Devices

In the Processor SDK package, users will not get any example by default, so users must create the examples and mention the platform name, module, and endianness by using the `pdkProjectCreate.bat` script.

For K2H, do the following command to create the NDK examples (NIMU) for ARM and DSP cores in the Processor SDK package of K2H `C:\ti\pdk_k2hk_4_0_3\packages\pdkProjectCreate.bat` K2H all little nimu dsp `C:\ti\pdk_k2hk_4_0_3\packages\pdkProjectCreate.bat` K2H all little nimu arm.

For K2E, do the following command to create the NDK examples (NIMU) for ARM and DSP cores in the Processor SDK package of K2E `C:\ti\pdk_k2e_4_0_3\packages\pdkProjectCreate.bat` K2E all little nimu dsp `C:\ti\pdk_k2e_4_0_3\packages\pdkProjectCreate.bat` K2E all little nimu arm.

Please refer to the following TI wiki pages to know more about the creating and rebuilding the Processor SDK package.

- [Processor SDK Building The SDK](#)
- [Processor SDK — Create PDK projects](#)

Then, users would get the following Hello world and Client (ARM and DSP) examples in the following directory (MyExampleProjects).

- K2H ARM NDK Hello world:
 - `C:\ti\pdk_k2hk_4_0_3\packages\MyExampleProjects\NIMU_emacExample_EVMK2H_armBiosExampleProject`
- K2H DSP NDK Hello world:
 - `C:\ti\pdk_k2hk_4_0_3\packages\MyExampleProjects\NIMU_emacExample_EVMK2HC66BiosExampleProject`
- K2E ARM NDK Hello world:
 - `C:\ti\pdk_k2e_4_0_3\packages\MyExampleProjects\NIMU_emacExample_EVMK2E_armBiosExampleProject`
- K2E DSP NDK Hello world:
 - `C:\ti\pdk_k2e_4_0_3\packages\MyExampleProjects\NIMU_emacExample_EVMK2EC66BiosExampleProject`

6 How to run NDK Examples on K2H Devices

Use the following instructions to run NDK examples on K2E devices.

1. Set the boot mode to DSP No boot mode or Emulation.
2. Connect the Ethernet cable to LAN or to the PC (EVM to PC) according to the IP mode (DHCP IP or STATIC IP) that is displayed.

NOTE: Users must use Ethernet PORT0. See [EVMK2E Hardware Setup](#).

KeyStone II boards use STATIC IP mode by default (on K2H devices). This setting must be changed by altering the code to run in DHCP IP mode.

```
Line no: 322 (helloworld.c) if (1) TO if (0)
```

3. Connect core 0.
4. Run the `setupPhy` script (Scripts → DSP Clock Estimation → `setupPhy`).
5. Load and run the program.
6. Find the IP address from the local LAN server (DHCP server) in the NDK example output log in CCS.
7. Type the IP address in the Internet browser to open the client application.

7 How to run NDK Examples on K2E Devices

Use the following instructions to run NDK examples on K2E devices.

1. Set the boot mode to DSP No boot mode or Emulation.
2. Connect the Ethernet cable to LAN or to the PC (EVM to PC) according to the IP mode (DHCP IP or STATIC IP) that is displayed.

NOTE: Users must use Ethernet PORT0. See [EVMK2E Hardware Setup](#).

KeyStone II boards use DHCP IP mode by default (on K2E devices). This setting must be changed by altering the code to run in STATIC IP mode.

```
Line no: 322 (helloworld.c) if (1) TO if (0)
```

3. Connect core 0.
4. Run the setupPhy script (Scripts → DSP Clock Estimation → setupPhy).
5. Load and run the program.
6. Find the IP address from the local LAN server (DHCP server) in the NDK example output log in CCS.
7. Type the IP address in the Internet browser to open the client application.

NOTE: Use the following ARM gel file for running the ARM NDK examples:
C:\ti\ccsv6\ccs_base\emulation\boards\xtcievmk2x\gel\xtcievmk2x_arm.gel.

8 Other Resources

The following list contains other helpful NDK (frequently asked questions) FAQs and information.

1. [Before asking for NDK support](#)
2. [NDK, PA Resource Wiki for Keystone Devices](#)
3. [Network Developers Kit FAQ](#)

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com