

H.264 Baseline Profile Decoder (2.00) on C64x+

FEATURES

- eXpressDSP™ Digital Media (XDM 1.0 IVIDDEC2) interface compliant
- Validated on the DM644x EVM
- Up to level 3.0 features of the baseline profile (BP) supported
- Progressive frame type picture decoding supported
- Multiple slices and multiple reference frames supported
- CAVLC decoding supported
- Intra-prediction and inter-prediction modes supported
- Up to 16 MV per MB supported
- Frame size being non-multiples of 16 through frame cropping supported
- Frame width of the range 32 to 720 pixels supported
- Byte-stream syntax and NAL unit format for the input bit stream supported
- Long term reference frames supported
- Gaps in the frame_num
- Decoding of streams with IPCM coded macroblocks supported
- Skipping of non-reference pictures supported
- Configurable delay for display of frames supported
- Error resiliency supported
- Error concealment supported
- Outputs are available in YUV 420 planar and 422 interleaved little endian formats
- Tested for compliance with JM version 12.2 reference decoder
- ASO and FMO error concealment feature

supported

- Redundant slices supported
- Parsing of Supplemental Enhancement Information(SEI) and Video Usability Information (VUI) supported
- Adaptive reference picture marking supported
- Reference picture list reordering supported
- All resolutions up to D1 (PAL and NTSC) including CIF and QCIF supported
- This codec can be used on any of TI's C64x+ based platforms such as DM644x, DM648, DM643x, OMAP35xx, and their derivatives.

DESCRIPTION

H.264 (from ITU-T, also called as H.264/AVC) is a popular video coding algorithm enabling high quality multimedia services on a limited bandwidth network. H.264 standard defines several profiles and levels which specify restrictions on the bit stream and hence limits the capabilities needed to decode the bit streams. Each profile specifies a subset of algorithmic features and limits that all decoders conforming to that profile may support. Each level specifies a set of limits on the values that may be taken by the syntax elements in the profile.

PRODUCT PREVIEW



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.
All other trademarks are the property of their respective owners.

Performance Summary

This section describes performance of the H.264 Baseline Profile Decoder on DM644x EVM.

Table 1. Configuration Table

CONFIGURATION	ID
Level 1.0 Baseline Profile	H264_DEC_001
Level 2.0 Baseline Profile	H264_DEC_002
Level 3.0 Baseline Profile	H264_DEC_003

Table 2. Cycles Information – Profiled on DM644x EVM With Code Generation Tools Version 6.0.8

CONFIGURATION ID	PERFORMANCE STATISTICS ⁽¹⁾ (MEGA CYCLES PER SECOND) ⁽²⁾		
	TEST DESCRIPTION	AVERAGE ⁽³⁾	PEAK ⁽⁴⁾
H264_DEC_001	foreman_i_p1.264, YUV422ILE, 4MV, QCIF(176x144), @ 300kbps	30	33
	FM1_BT_B.264,YUV422ILE, FMO with all types of slice-groups, QCIF(176x144), 270@ kbps	60	88
	FM1_FT_D.264,YUV422ILE,40% non-FMO, non-ASO frames and 60% ASO/FMO frames, QCIF(176x144), @ 187 kbps	44	63
	FM2_SVA_A.264,YUV422ILE, ASO/FMO frames, QCIF(176x144), @ 151kbps	59	64
	FM3_FT_A.264,YUV422ILE,ASO/FMO present, QCIF(176x144), @241 kbps	50	76
H264_DEC_002	Cities_CIF_500Kbps.264, YUV422ILE, 4MV, CIF(352x288), @ 500 kbps	88	109
	traffic_multiple_slice_aso.264,YUV422ILE, only ASO present on all frames, CIF(352x288), @ 560 kbps	95	121
H264_DEC_003	foreman_vga_1mbps_100f.264, YUV422ILE, 4MV, VGA(640x480), @ 1 mbps	203	282
	fire_30frames_2_Mbps.264, YUV422ILE, 16MV, D1(720x480), @ 2 mbps	292	311
	sheilds_720x480_1MV_1_5Mbps.264 , YUV422ILE, 1MV, D1 (720x480) @ 1.5Mbps	220	336

- (1) Average and peak MCPS measurements can vary by +/-5%.
- (2) Measured with program memory, stack, I/O buffers in external memory, 32K-bytes L1P Cache, 64K-bytes L1D Data memory, 16K-bytes L1D Cache, 64K-bytes L2 Cache, DDR speed at 162 MHz, and CPU speed at 486 MHz
- (3) Based on average number of cycles per frame @ 30 frames per second (fps)
- (4) Based on worst case cycles per frame @ 30 fps

Table 3. Memory Statistics - Generated With Code Generation Tools Version 6.0.8

CONFIGURATION ID	MEMORY STATISTICS ⁽¹⁾				TOTAL
	PROGRAM MEMORY	DATA MEMORY			
		INTERNAL	EXTERNAL	STACK	
H264_DEC_001	472	62	1290	12	1836
H264_DEC_002	472	62	4048	12	4596
H264_DEC_003	472	62	6280	12	6826

- (1) All memory requirements are expressed in kilobytes (1K-byte = 1024 bytes) and there could be a variation of approximately 1-5% in values

Table 4. Internal Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - INTERNAL ⁽¹⁾		
	SHARED		INSTANCE ⁽²⁾
	CONSTANTS	SCRATCH	
H264_DEC_001	0	62	0
H264_DEC_002	0	62	0
H264_DEC_003	0	62	0

(1) Internal memory refers to L1D RAM. All memory requirements are expressed in kilobytes and there could be a variation of approximately 1-5% in values.

(2) I/O buffers not included. Some of the instance memory buffers could be scratch.

Table 5. External Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY-EXTERNAL ⁽¹⁾		
	CONSTANT	FAR	PERSISTENT
H264_DEC_001	5	10	1275
H264_DEC_002	5	10	4033
H264_DEC_003	5	10	6265

(1) All memory requirements are expressed in kilobytes (1K-byte = 1024 bytes) and there could be a variation of approximately 1-5% in values

Notes

- Evaluation version performance values may be higher than the values specified in the performance table.
- Display buffer for YUV422 interleaved format is 810K-bytes for 625 SD format (720 x 576)
- Input buffer to algorithm is assumed to have at least one encoded frame data. Otherwise, the application must provide CPB buffer size amount of valid data to the algorithm. For a specific level, the CPB size could be referred from the standard.
- Memory Configuration
 - L1P: 32K-bytes program cache (32 bytes cache line width, direct mapped cache)
 - L1D: 64K-bytes data memory and 16K-bytes data cache (64 bytes cache line width, 2-way set associative cache)
 - L2: 64K-bytes cache (128 bytes cache line width, 4-way set associative cache)
- The performances obtained in [Table 2](#) are sensitive to algorithm code placement. See the sample linker file provided in the test application setup for algorithm code placement. This is used for profiling in [Table 2](#).
- The algorithm uses 4 QDMA channels. Channels 0, 2, and 3 each require up to a maximum of 8 linked transfers. Channel 1 requires 24 PARAM sets to perform 24 linked transfers. The algorithm uses DMAN3 interface for logical allocation of these channels.
- Total data memory for N non pre-emptive instances = Constants + Runtime Tables + Scratch + N*(Instance + I/O buffers + Stack)
- Total data memory for N pre-emptive instances = Constants + Runtime Tables + N*(Instance + I/O buffers + Stack + Scratch)

References

- ISO/IEC 14496-10:2005 (E) Rec. - Information technology – Coding of audio-visual objects – H.264 (E) ITU-T Recommendation
- *H.264 Baseline Profile Decoder on C64x+ User's Guide* (literature number: SPRUEA1C)

Glossary

Term	Description
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

Acronyms

Acronym/Abbreviation	Description
625SD	Level 3.0 maximum resolution format size 720 x 576
CIF	Common Intermediate Format
CPB	Coded Picture Buffer
D1	SDTV image resolution (720x480)
DMA	Direct Memory Access
DMAN3	DMA Manager
EVM	Evaluation module
QCIF	Quarter Common Intermediate Format
QDMA	Quick Direct Memory Access
SDTV	Standard Definition Television
SEI	Supplemental Enhancement Information
VGA	Video Graphics Array (640 x 480 resolution)
VUI	Video Usability Information
XDM	eXpressDSP Digital Media

Revision History

This data sheet revision history highlights the changes made to the SPRS315B codec specific data sheet to make it SPRS315C.

Table 6. Revision History of H264 Decoder on C64x+

SECTION	ADDITIONS/MODIFICATIONS/DELETIONS
Global	Modified Code Generation Tools version to 6.0.8
Section 1	Features: <ul style="list-style-type: none"> • Updated XDM version • Added the following: <ul style="list-style-type: none"> – Error resiliency supported – All resolutions up to D1 (PAL and NTSC) including CIF and QCIF supported • Added supported platforms
Table 2	Cycles Information: <ul style="list-style-type: none"> • Added the last row to Test Description column • Updated Average and Peak values
Table 3	Memory Statistics: <ul style="list-style-type: none"> • Updated Program Memory, Internal, External, Stack, and Total values
Table 4	Internal Data Memory Split-up: <ul style="list-style-type: none"> • Updated Scratch values
Table 5	Added table for External Data Memory Split-up

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright 2008, Texas Instruments Incorporated