


Symbol	Count	Hole Size	Plated	Hole Tolerance (+)	Hole Tolerance (-)	Hole Length
○	24	27.56mil (0.700mm)	PTH			-
▽	1018	8.00mil (0.203mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	1042 Total					

Symbol	Count	Hole Size	Plated	Hole Type	Drill Layer Pair	Via/Pad	Pad Shape	Template	Description	Hole Tolerance (+)	Hole Tolerance (-)
○	24	27.56mil (0.700mm)	PTH	Round	Top Layer - Bottom Layer	Pad	<Mixed>	<Mixed>			
▽	1018	8.00mil (0.203mm)	PTH	Round	Top Layer - Bottom Layer	Via	Rounded	v46h20m0mx0<To18-8>		3.00mil (0.076mm)	3.00mil (0.076mm)
	1042 Total										



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC198	REV: B	SUN REV: Not in version control
MI Board Outline LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Fabrication Drawing 2	GENERATED : 8/12/2024 11:20:12 AM		TEXAS INSTRUMENTS