


REVISIONS				
REV	DATE	DESCRIPTION	CHG	APPR
A	JAN 18 '22	CHG BASE SHAPE (WAS U-SHAPE) AND FLIP HOLE LOCATION, U-SHAPE SYMMETRICALLY	T. Y.	T. Y.



NOTES : UNLESS OTHERWISE SPECIFIED

1. INTERPRET DIMENSIONS AND TOLERANCES PER ANSI Y14.5M.

2. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].

3. MATERIAL : ALUMINUM 6063

4. FINISH : BLACK ANODIZE

5. TOLERANCES :

.XX ±0.254 [.010]

.XXX ±0.127 [.005]

ANGLES ± 1°

6. REMOVE ALL BURRS AND BREAK SHARP EDGES.

UNSPECIFIED CORNER R0.5 MAX OR C0.5 MAX.

7. A BEND OF THE FIN: THE FINS MUST NOT CONTACT.

8. FIN REMOVAL MARKS MAX 0.3MM

9. BASED ON ALPHA STANDARD HEAT SINK Z40-6.3B

ITEM	PART NO.	PART NAME	REMARK	Q'TY
ALPHA CO.,LTD.			CSTMRS PART NO.	
		MATERIAL NOTE 3, 4	NAME Z2940-6BM	
SCALE 1 : 1		APPR & CHCK T. YANAGIDAIRA	PART NO. & DWG NO. S08EDR03	
DATE DEC.01,2021		DSGN & DWG T. YANAGIDAIRA		
RDCTN:			LOFF:	