




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	PU REV: E1	SUN REV: 6980
LAYER NAME = Top Overlay			
PLOT NAME = Top Overlay	GENERATED : 04/06/2026 22:16:31	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	PU REV: E1	SUN REV: 6980
LAYER NAME = Top Solder			
PLOT NAME = Top Solder Mask	GENERATED : 04/06/2026 22:16:31	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	PU REV: E1	SUN REV: 6980
LAYER NAME = Top Layer			
PLOT NAME = Top Layer	GENERATED : 04/06/2026 22:16:31	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-01012	PU REV: E1	SUN REV: 6980
LAYER NAME =			
PLOT NAME = Signal Layer 1	GENERATED : 04/06/2026 22:16:31	TEXAS INSTRUMENTS	







ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	MU REV: E1	SUN REV: 6980
LAYER NAME =			
PLOT NAME = Signal Layer 2	GENERATED : 04/06/2026 22:16:31	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	PU REV: E1	SUN REV: 6980
LAYER NAME = Bottom Layer			
PLOT NAME = Bottom Layer	GENERATED : 04/06/2026 22:16:32	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-01012	PU REV: E1	SUN REV: 6980
LAYER NAME = Bottom Solder			
PLOT NAME = Bottom Solder Mask	GENERATED : 04/06/2026 22:16:32	TEXAS INSTRUMENTS	





ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	MU REV: E1	SUN REV: 6980
LAYER NAME = Bottom Overlay			
PLOT NAME = Bottom Overlay	GENERATED : 04/06/2026 22:16:32		TEXAS INSTRUMENTS

Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
	46	16.19mm (0.6375in)	NPTH	Round	Top Layer - Bottom Layer	
	4	50.80mm (2.000in)	NPTH	Round	Top Layer - Bottom Layer	
	1	62.50mm (2.4609in)	NPTH	Round	Top Layer - Bottom Layer	
	8	76.20mm (3.000in)	NPTH	Round	Top Layer - Bottom Layer	
	1	76.20mm (3.000in)	NPTH	Round	Top Layer - Bottom Layer	
	4	106.68mm (4.1964in)	NPTH	Round	Top Layer - Bottom Layer	
	4	214.36mm (8.4354in)	NPTH	Round	Top Layer - Bottom Layer	
	2468	7.62mm (0.3000in)	PTH	Round	Top Layer - Bottom Layer	
	2	15.24mm (0.6000in)	PTH	Round	Top Layer - Bottom Layer	
	4	16.43mm (0.6469in)	PTH	Round	Top Layer - Bottom Layer	
	10	17.46mm (0.6874in)	PTH	Round	Top Layer - Bottom Layer	
	10	43.30mm (1.7047in)	PTH	Round	Top Layer - Bottom Layer	
	6	47.26mm (1.8571in)	PTH	Round	Top Layer - Bottom Layer	
	10	55.75mm (2.1949in)	PTH	Round	Top Layer - Bottom Layer	
	46	56.12mm (2.2094in)	PTH	Round	Top Layer - Bottom Layer	
	46	56.87mm (2.2390in)	PTH	Round	Top Layer - Bottom Layer	
	64	62.50mm (2.4609in)	PTH	Round	Top Layer - Bottom Layer	
	10	63.50mm (2.5000in)	PTH	Round	Top Layer - Bottom Layer	
	15	152.40mm (6.0000in)	PTH	Round	Top Layer - Bottom Layer	
	2030 Total					



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	PU REV: E1	SUN REV: 6980
LAYER NAME = Drill Drawing			
PLOT NAME = Drill Drawing	GENERATED : 04/06/2026 22:16:32	TEXAS INSTRUMENTS	



(000.00mm)

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: TIDA-011012	MU REV: E1	SUN REV: 6980
LAYER NAME = M2 Board Dimensions			
PLOT NAME = Board Dimensions	GENERATED : 04/06/2026 22:16:34	TEXAS INSTRUMENTS	