



Through Holes All Drills (unless specified) +/- 0.076 (mm)				
Symbol	Diameter (mm)	Tolerance (mm)	Quantity	Plated
⊠	0.200		6	Yes
×	0.300		23	Yes
⊕	0.457		167	Yes
□	1.016		10	Yes
⊠	1.100	+0.100 / -0.050	8	Yes
⊠	2.300		6	Yes



TPS65320_EVM RevB 01/24/12 LAYER 1 (CO) SIGNAL (DUT SIDE)



S65320_EVM RevB 01/24/12 LAYER 2 (SO) SIGNAL (TESTER SIDE)