


Notes:

- 1) Refer to BOM for stuffing options.
- 2) Observe polarity on diodes and capacitors.

REVISIONS				
REV.	REV.	DESCRIPTION	DATE	APPROVED



SECONDARY SIDE

APPLICATION		CONTRACT NO.	DWN:	om	9/14	TEXAS INSTRUMENTS				
USED ON	NEXT ASSY.		CHK:							
		UNLESS OTHERWISE SPECIFIED 1. TOLERANCES: LINEAR = : 0.26 (.010) ANGULAR = : 0.50 ° 2. ALL DIMENSIONS ARE IN MM (INCHES). 3. INTERPRET DRAWING IN ACCORDANCE WITH DOD-STD-100.	P.E.:			TITLE: ASSEMBLY DRAWING, TIDM-SOMPLC-FCC				
			DES.ENG.:							
			P.C.:							
			Q.C.:							
			C.M.:							
			REL:							
			MFG:							
			ENG.WGR:							
			OTHER:							
			OTHER:							
MATERIAL: SEE NOTE			OTHER:			SIZE	CAGE CODE NO.	DRAWING NO.		REV:
FINISH: SEE NOTE						C				1
DO NOT SCALE DRAWING						SCALE:				