



Input Voltage VCC: 5V (Supplied by PC)
Input Voltage VM: 8V to 45V

DRV8840EVM Single DC Motor Driver (5A) with BRAKE
DRV8842EVM Single DC Motor Driver (5A) INx Control

Size B		DWG No. CPG005	Rev A
		Sheet 2 of 3	

