

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LP5912-0.9DRVR   | WSO          | DRV             | 6    | 3000 | 178.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.0DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.1DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.1DRVRG4 | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.2DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.2DRVRG4 | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.2DRVT   | WSO          | DRV             | 6    | 250  | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.5DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.8DRVR   | WSO          | DRV             | 6    | 3000 | 178.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-1.8DRVRG4 | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-2.5DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-2.5DRVRG4 | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-2.8DRVR   | WSO          | DRV             | 6    | 3000 | 178.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-3.0DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-3.3DRVR   | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-3.3DRVRG4 | WSO          | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |

| Device           | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LP5912-3.3DRVT   | WSON         | DRV             | 6    | 250  | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-5.0DRVR   | WSON         | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |
| LP5912-5.0DRVRG4 | WSON         | DRV             | 6    | 3000 | 180.0              | 8.4                | 2.3     | 2.3     | 1.15    | 4.0     | 8.0    | Q2            |

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LP5912-0.9DRVR   | WSON         | DRV             | 6    | 3000 | 208.0       | 191.0      | 35.0        |
| LP5912-1.0DRVR   | WSON         | DRV             | 6    | 3000 | 210.0       | 185.0      | 35.0        |
| LP5912-1.1DRVR   | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-1.1DRVRG4 | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-1.2DRVR   | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-1.2DRVRG4 | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-1.2DRVT   | WSON         | DRV             | 6    | 250  | 182.0       | 182.0      | 20.0        |
| LP5912-1.5DRVR   | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-1.8DRVR   | WSON         | DRV             | 6    | 3000 | 208.0       | 191.0      | 35.0        |
| LP5912-1.8DRVRG4 | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-2.5DRVR   | WSON         | DRV             | 6    | 3000 | 210.0       | 185.0      | 35.0        |
| LP5912-2.5DRVRG4 | WSON         | DRV             | 6    | 3000 | 210.0       | 185.0      | 35.0        |
| LP5912-2.8DRVR   | WSON         | DRV             | 6    | 3000 | 208.0       | 191.0      | 35.0        |
| LP5912-3.0DRVR   | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-3.3DRVR   | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-3.3DRVRG4 | WSON         | DRV             | 6    | 3000 | 182.0       | 182.0      | 20.0        |
| LP5912-3.3DRVT   | WSON         | DRV             | 6    | 250  | 182.0       | 182.0      | 20.0        |
| LP5912-5.0DRVR   | WSON         | DRV             | 6    | 3000 | 210.0       | 185.0      | 35.0        |

---

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LP5912-5.0DRVRG4 | WSON         | DRV             | 6    | 3000 | 210.0       | 185.0      | 35.0        |