

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS51116PWPR | HTSSOP       | PWP             | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.1     | 1.6     | 8.0     | 16.0   | Q1            |
| TPS51116RGER | VQFN         | RGE             | 24   | 3000 | 330.0              | 12.4               | 4.25    | 4.25    | 1.15    | 8.0     | 12.0   | Q2            |
| TPS51116RGET | VQFN         | RGE             | 24   | 250  | 180.0              | 12.4               | 4.25    | 4.25    | 1.15    | 8.0     | 12.0   | Q2            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS51116PWPR | HTSSOP       | PWP             | 20   | 2000 | 350.0       | 350.0      | 43.0        |
| TPS51116RGER | VQFN         | RGE             | 24   | 3000 | 346.0       | 346.0      | 33.0        |
| TPS51116RGET | VQFN         | RGE             | 24   | 250  | 210.0       | 185.0      | 35.0        |

## TUBE



\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TPS51116PWP   | PWP          | HTSSOP       | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TPS51116PWP.A | PWP          | HTSSOP       | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TPS51116PWP.B | PWP          | HTSSOP       | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |
| TPS51116PWPG4 | PWP          | HTSSOP       | 20   | 70  | 530    | 10.2   | 3600   | 3.5    |