

National Semiconductor / Texas Instruments Cross Reference

QML Class V* LS Device Family

NSC Generic Part Number	NSC Part Number (NSID)	TI Cross Reference Part Number	NSC Generic Part Number	NSC Part Number (NSID)	TI Cross Reference Part Number
DM54LS08J-MLS	DM54LS08J-MLS	JM38510/31004SCA	JM38510/30004SDA	JD54LS05SDA	JM38510/30004SDA
DM54LS08W-MLS	DM54LS08W-MLS	JM38510/31004SDA	JM38510/30005SCA	JD54LS10SCA	JM38510/30005SCA
DM54LS109W-MLS	DM54LS109W-MLS	JM38510/30109SFA	JM38510/30005SDA	JD54LS10SDA	JM38510/30005SDA
DM54LS14J-MLS	DM54LS14J-MLS	5962-9665801VCA	JM38510/31001SCA	JD54LS11SCA	JM38510/31001SCA
DM54LS14W-MLS	DM54LS14W-MLS	5962-9665801VDA	JM38510/31001SDA	JD54LS11SDA	JM38510/31001SDA
DM54LS154W-MLS	DM54LS154W-MLS	No Cross	JM38510/30701SEA	JD54LS138SEA	JM38510/30701SEA
DM54LS161AJ-MLS	DM54LS161AJ-MLS	5962-7600801VEA	JM38510/30701SFA	JD54LS138SFA	JM38510/30701SFA
DM54LS161AW-MLS	DM54LS161AW-MLS	5962-7600801VFA	JM38510/30702SFA	JD54LS139SFA	JM38510/30702SFA
DM54LS161J-MLS	DM54LS161J-MLS	5962-7600801VEA	JM38510/30901SEA	JD54LS151SEA	JM38510/30901SEA
DM54LS165J-MLS	DM54LS165J-MLS	5962-7700601VEA	JM38510/30901SFA	JD54LS151SFA	JM38510/30901SFA
DM54LS173J-MLS	DM54LS173J-MLS	JM38510/3610SEA	JM38510/30902SEA	JD54LS153SEA	JM38510/30902SEA
DM54LS173W-MLS	DM54LS173W-MLS	JM38510/3610SDA	JM38510/30902SFA	JD54LS153SFA	JM38510/30902SFA
DM54LS195AJ-MLS	DM54LS195AJ-MLS	No Cross	JM38510/30903SEA	JD54LS157SEA	JM38510/30903SEA
DM54LS240J-MLS	DM54LS240J-MLS	5962-7801201VRA	JM38510/30904SEA	JD54LS158SEA	JM38510/30904SEA
DM54LS240W-MLS	DM54LS240W-MLS	5962-7801201VSA	JM38510/30605SCA	JD54LS164SCA	JM38510/30605SCA
DM54LS245J-MLS	DM54LS245J-MLS	5962-8002101VRA	JM38510/30605SDA	JD54LS164SDA	JM38510/30605SDA
DM54LS245W-MLS	DM54LS245W-MLS	5962-8002101VSA	JM38510/30106SEA	JD54LS174SEA	JM38510/30106SEA
DM54LS257AW-MLS	DM54LS257AW-MLS	5962-7603701VFA	JM38510/30106SFA	JD54LS174SFA	JM38510/30106SFA
DM54LS26J-MLS	DM54LS26J-MLS	5962-7602001VCA	JM38510/30107SEA	JD54LS175SEA	JM38510/30107SEA
DM54LS273J-MLS	DM54LS273J-MLS	5962-7801001VRA	JM38510/30107SFA	JD54LS175SFA	JM38510/30107SFA
DM54LS32J-MLS	DM54LS32J-MLS	JM38510/30501SCA	JM38510/31508SEA	JD54LS193SEA	JM38510/31508SEA
DM54LS32W-MLS	DM54LS32W-MLS	JM38510/30501SDA	JM38510/31508SFA	JD54LS193SFA	JM38510/31508SFA
DM54LS367AW-MLS	DM54LS367AW-MLS	JM38510/32203SFA	JM38510/30007SDA	JD54LS20SDA	JM38510/30007SDA
DM54LS368AJ-MLS	DM54LS368AJ-MLS	5962-xxxxx01VEA**	JM38510/32403SRA	JD54LS244SRA	JM38510/32403SRA
DM54LS670W-MLS	DM54LS670W-MLS	5962-7704201VFA	JM38510/32403SSA	JD54LS244SSA	JM38510/32403SSA
DM54LS73W-MLS	DM54LS73W-MLS	5962-9675101VDA	JM38510/30905SFA	JD54LS251SFA	JM38510/30905SFA
JM38510/30001SCA	JD54LS00SCA	JM38510/30001SCA	JM38510/30009SCA	JD54LS30SCA	JM38510/30009SCA
JM38510/30001SDA	JD54LS00SDA	JM38510/30001SDA	JM38510/32203SEA	JD54LS367SEA	JM38510/32203SEA
JM38510/30301SCA	JD54LS02SCA	JM38510/30301SCA	JM38510/32203SFA	JD54LS367SFA	JM38510/32203SFA
JM38510/30301SDA	JD54LS02SDA	JM38510/30301SDA	JM38510/30102SCA	JD54LS74SCA	JM38510/30102SCA
JM38510/30002SCA	JD54LS03SCA	JM38510/30002SCA	JM38510/30102SDA	JD54LS74SDA	JM38510/30102SDA
JM38510/30002SDA	JD54LS03SDA	JM38510/30002SDA	JM38510/31101SE	JD54LS85SEA	JM38510/31101SE
JM38510/30003SCA	JD54LS04SCA	JM38510/30003SCA	JM38510/31101SFA	JD54LS85SFA	JM38510/31101SFA
JM38510/30003SDA	JD54LS04SDA	JM38510/30003SDA	JM38510/30502SCA	JD54LS86SCA	JM38510/30502SCA
JM38510/30004SCA	JD54LS05SCA	JM38510/30004SCA			

* All listed parts are QMLV devices. The referenced JAN part numbers have a class S in the part number but are not full Class S devices. The SMD part numbers have a V which denotes Class V.

** SMD number will be furnished upon device setup/request.

TI Worldwide Technical Support

Internet

TI Semiconductor Home Page

www.ti.com/corp/technical_support.htm

TI Semiconductor KnowledgeBase Home Page

www-k.ext.ti.com/sc/technical_support/knowledgebase.htm

Product Information Centers

Americas

Phone +1(972) 644-5580
Fax +1(214) 480-7800
Internet www.ti.com/sc/ampic

Europe, Middle East, and Africa

Phone
Belgium (English) +32 (0) 27 45 55 32
France +33 (0) 1 30 70 11 64
Germany +49 (0) 8161 80 33 11
Israel (English) 1800 949 0107
Italy 800 79 11 37
Netherlands (English) +31 (0) 546 87 95 45
Spain +34 902 35 40 28
Sweden (English) +46 (0) 8587 555 22
United Kingdom +44 (0) 1604 66 33 99
Fax +44 (0) 1604 66 33 34
Email epic@ti.com
Internet www.ti.com/sc/epic

Japan

Phone
International +81-3-3344-5311
Domestic 0120-81-0026
Fax
International +81-3-3344-5317
Domestic 0120-81-0036
Internet
International www.ti.com/sc/jpic
Domestic www.tij.co.jp/pic

Asia

Phone
International +886-2-23786800
Domestic Local Access Code TI Number
Australia 1-800-881-011 -800-800-1450
China 1-0810 -800-800-1450
Hong Kong 800-96-1111 -800-800-1450
India 000-117 -800-800-1450
Indonesia 001-801-10 -800-800-1450
Korea 080-551-2804 -
Malaysia 1-800-800-011 -800-800-1450
New Zealand 000-911 -800-800-1450
Philippines 105-11 -800-800-1450
Singapore 800-0111-111 -800-800-1450
Taiwan 080-006800 -
Thailand 0019-991-1111 -800-800-1450
Fax 886-2-2378-6808
Email tiasia@ti.com
Internet www.ti.com/sc/apic

Important Notice: The products and services of Texas Instruments and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

B121400

