




- \* SURFACE - AIR 0 MM
- L1: TOP CONDUCTOR - COPPER 0.035 MM
- \* DIELECTRIC - FR-4 0.175 MM
- L2: L2 PLANE - COPPER 0.018 MM
- \* DIELECTRIC - FR-4 1.14 MM
- L3: L3 PLANE - COPPER 0.018 MM
- \* DIELECTRIC - FR-4 0.175 MM
- L4: BOTTOM CONDUCTOR - COPPER 0.035 MM
- \* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 1.60MM +/- 0.16MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	FINISHED_SIZE	PLATED	QTY
◉	0.2	PLATED	359
◉	0.2	PLATED	25
▲	1.501	NON-PLATED	4