

\* SURFACE - AIR 0 MM

L1: TOP CONDUCTOR - COPPER 0.035 MM


\* DIELECTRIC - FR-4 0.73 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM

\* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 0.8 MM



| DRILL CHART: TOP to BOTTOM   |       |            |     |
|------------------------------|-------|------------|-----|
| ALL UNITS ARE IN MILLIMETERS |       |            |     |
| FIGURE                       | SIZE  | PLATED     | QTY |
| •                            | 0.2   | PLATED     | 397 |
| ●                            | 0.2   | PLATED     | 25  |
| ·                            | 0.4   | PLATED     | 25  |
| ▲                            | 1.501 | NON-PLATED | 4   |