



```
DIO_1 (CTX) : LOW   & DIO_30 (CSD): HIGH  ---> Rx
DIO_1 (CTX) : HIGH  & DIO_30 (CSD): HIGH  ---> Tx
DIO_1 (CTX) : X     & DIO_30 (CSD): LOW   ---> Sleep
```

Frequency (MHz)	C484	L332	C485	C486	L333	C487	ANT1	ANT2	BOM
470 - 510	DNM	0 ohm	DNM	DNM	DNM	0 ohm	5.6 pF	68 nH	Rev 2.0.1
420 - 440	3.9 pF	9.1 nH	2.7 pF	3.9 pF	15 nH	6.8 pF	6.8 pF	91 nH	Rev 2.0.2
400 - 420	3.9 pF	10 nH	4.0 pF	6.0 pF	15 nH	8.0 pF	7.5 pF	100 nH	Rev 2.0.3

