





1. M1509  
WCMA/HSDDA/R5/GSM/GPRS/EDGE/R99  
VCC 3.3~4.2V      typ=3.8V  
2.750A(max)  
1.1A(max)  
3. M2509  
CDMA/EVDO 1900 MHz/ 800 MHz/GPS  
Power 3.3~4.2V      typ=3.8V  
2.750A(max)  
1.1A(max)  
5. M1599  
CDMA/EVDO 1900 MHz/ 800 MHz/GPS  
Power 3.3~4.2V      typ=3.8V  
2.750A(max)  
1.1A(max)  
4. MGT732  
WCMA/HSDDA/R5/GSM/GPRS/EDGE  
Power 3.3~4.2V      typ=3.8V  
1800mA(max)  
5. MC8630 CDMA 200 1X EVDO Rev.A 800MHz  
Power 3.0~4.3V  
Power 3.0~4.2V      typ=3.6V  
1000mA(max)  
6. LM7870  
WCMA/HSDDA/R5/GSM/GPRS/EDGE/R99  
VCC 4.0~3.3V  
2.750A(max)  
1.1A(max)

VPOS353-Interface

## Wireless Module

FSCM NO.	DWG. NO.	REV	V08
----------	----------	-----	-----

SIZE C	SCALE		SHEET	2 of 4
--------	-------	--	-------	--------



REVISIONS			
REV	DESCRIPTION	DATE	APPROVE

CONTRACT NO.			VPOS353-Interface				
APPROVALS		DATE					
DRAWN	LiuJie		Camera & GPS				
CHECKED							
ISSUED			FSCM NO.		DWG. NO.	REV	V0
			SIZE	C	SCALE	SHEET	3 of 4

CONTRACT NO.			VPOS353-Interface					
APPROVALS		DATE						
DRAWN	LiuJie		Audio Switch					
CHECKED			FSCM NO.		DWG. NO.		REV	V08
ISSUED			SIZE C SCALE		SHEET		4 of 4	

