



* SURFACE - AIR 0 MM
L1: TOP CONDUCTOR - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.73 MM
L2: BOTTOM CONDUCTOR - COPPER 0.035 MM

* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART
TOTAL THICKNESS 0.8 MM

DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
•	0.2	PLATED	275
⊙	0.2	PLATED	25
.	0.4	PLATED	25
△	1.501	NON-PLATED	4