




* SURFACE - AIR 0 MM
L1: TOP CONDUCTOR - COPPER 0.035 MM
* DIELECTRIC - FR-4 0.175 MM
L2: L2 CONDUCTOR - COPPER 0.018 MM
* DIELECTRIC - FR-4 1.14 MM
L3: L3 CONDUCTOR - COPPER 0.018 MM
* DIELECTRIC - FR-4 0.175 MM
L4: BOTTOM CONDUCTOR - COPPER 0.035 MM
* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 1.596 MM
39.3



DRILL CHART: TOP to BOTTOM

ALL UNITS ARE IN MILLIMETERS

FIGURE	SIZE	PLATED	QTY
●	0.2	PLATED	277
.	0.4	PLATED	21
▲	1.501	NON-PLATED	4