




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EUM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Top Overlay			
PLOT NAME = Top Overlay	GENERATED : 9/11/2014 8:38:34 AM		TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EVM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Top Solder			
PLOT NAME = Top Solder Mask	GENERATED : 9/11/2014 8:38:34 AM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EVM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Top Layer			
PLOT NAME = Top Layer	GENERATED : 9/11/2014 8:38:35 AM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EVM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Bottom Layer			
PLOT NAME = Bottom Layer	GENERATED : 9/11/2014 8:38:36 AM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EVM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Bottom Solder			
PLOT NAME = Bottom Solder Mask	GENERATED : 9/11/2014 8:38:36 AM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EVM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Bottom Overlay			
PLOT NAME = Bottom Overlay	GENERATED : 9/11/2014	8:38:37 AM	TEXAS INSTRUMENTS



Symbol	Hit Count	Tool Size	Plated	Hole Type
□	6	12.992mil (0.33mm)	PTH	Round
○	103	15mil (0.381mm)	PTH	Round
✱	10	38mil (0.965mm)	PTH	Round
✕	18	40mil (1.016mm)	PTH	Round
▽	2	47.244mil (1.2mm)	PTH	Round
⊕	6	50mil (1.27mm)	PTH	Round
145 Total				

Drill Table

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRU8848EUM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = Drill Drawing			
PLOT NAME = Drill Drawing	GENERATED : 9/11/2014	8:38:37 AM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: DRV8848EVM	REV: REV A	SUN REV: Not In VersionControl
LAYER NAME = M2 Board Dimensions			
PLOT NAME = Board Dimensions	GENERATED : 9/11/2014 8:38:38 AM	TEXAS INSTRUMENTS	