Filename: Pro20D7.tmp
Variant: **001
Generated: 11/2/2017 1:57:52 PM
TID #: TIDA-01463

TIDA-01463 REV A Bill of Materials



TID #:	TIDA-01463 REV A Bill of Materials INSTRUMENTS						
Item #	Designator IPCB1	Quantity	Value	PartNumber TIDA-01463	Manufacturer Any	Description Printed Circuit Board	PackageReferen
2	C1, C3, C34, C48 C2, C4, C36, C37, C38, C39.	1 4 15	1uF 0.1uF	C1005X5R1A105K050BB 885012205037	TDK Wurth Elektronik	Printed Circuit Board CAP, CERM, 1 μF, 10 V, +/- 10%, X5R, 0402 CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0402	0402 0402
	C37, C38, C39, C40, C41, C42, C43, C44, C45, C49, C51, C54						
4 5	C5 C6, C7, C8, C9	1 4	4700pF 0.01uF	1812GC472KAT1A GRM188R72A103KA01D	AVX MuRata	CAP, CERM, 4700 pF, 2000 V, +/- 10%, X7R, 1812	1812 0603
6 7	C10 C11, C12	1 2	1000pF 1000pF	GR443QR73D102KW01L C1608X7R2A102K080AA	MuRata TDK	CAP, CERM, 0.01 µF, 100 V, +/- 10%, X/R, 0603 CAP, CERM, 1000 pF, 2000 V,+/- 10%, X/R, 1812 CAP, CERM, 1000 pF, 100 V, +/- 10%, X/R, 0603	1812 0603
8	C13, C14, C15, C16	4	330pF	885012006060	Wurth Elektronik	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
9 10 11	C17 C18, C23, C24 C19, C20, C21,	1 3 5	100uF 0.1uF 2.2uF	EEV-FK2A101M C0805C104K1RACTU C1210C225K1RACTU	Panasonic Kemet Kemet	CAP, AL, 100 µF, 100 V, +/- 20%, 0.17 ohm, SMD CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805 CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	SMT Radial J16 0805 1210
12	C22, C31 C25 C26	1 1	1uF 470oF	885012206052 06035A471JAT2A	Wurth Elektronik	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603 CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603 0603
14	C27	- 1	22uF	GRM21BR60J226ME39L	MuRata	CAP, CERM, 22 µF, 6.3 V, +/- 20%, X5R, 0805	0805
15 16	C28, C29 C30	1	10uF 2200pF	GRM188R60J106ME47D 885012206036	MuRata Wurth Elektronik	CAP, CERM, 10 μF, 6.3 V, +/- 20%, X5R, 0603 CAP, CERM, 2200 pF, 16 V, +/- 10%, X7R, 0603	0603 0603
17 18	C32 C33	1	0.01uF 0.022uF 0.22uF	885012206040 885012206091 885012206048	Wurth Elektronik Wurth Elektronik Wurth Elektronik	CAP, CERM, 0.01 µF, 16 V, +/- 10%, X7R, 0603 CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0603	0603 0603
19 20	C46, C58, C62	3	0.01uF	885012205031	Wurth Elektronik Wurth Elektronik	CAP, CERM, 0.22 μF, 16 V, +/- 10%, X7R, 0603 CAP, CERM, 0.01 μF, 16 V, +/- 10%, X7R, 0402	0402
21	C47 C50	1	2.2uF 0.1uF	885012105013 885012206046	Wurth Elektronik	CAP, CERM, 2.2 µF, 10 V, +/- 20%, XSR, 0402 CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0603 CAP, CERM, 18 pF, 50 V, +/- 5%, CUG/NP0, 0402	0402 0603
23	C52, C53 C55, C56	2	18pF 22pF	GRM1555C1H180JA01D GRM1555C1H220JA01D	MuRata MuRata	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402 0402
25 26	C57, C61 C59, C63	2	10uF 1000pF	CGA6P1X7R1E106M250AC 885012205061	TDK Wurth Elektronik	CAP, CERM, 10 μF, 25 V, +/- 20%, X7R, AEC-Q200 Grade 1, 1210 CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0402	1210 0402
27 28	C60, C64 C65, C66	2	100pF 12pF	885012005061 C0402C120J3GACAUTO	Wurth Elektronik Kernet	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402 CAP, CERM, 12 pF, 25 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402 0402
29	D1, D2, D3, D4	4	100V	B2100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 2 A, SMB	SMB
30 31	D6 D6, D7, D8	3	58V Yellow	824520581 150060YS75000	Wurth Elektronik Wurth Elektronik	Diode, TVS, Uni, 58 V, DO-214 LED, Yellow, SMD	DO-214 LED_0603
32 33	D10 FID1, FID2, FID3	3	100V	SS2PH10-M3 N/A	Vishay-Semiconductor N/A	Dlode, Schottky, 100 V, 2 A, DO-220AA Fiducial mark. There is nothing to buy or mount.	DO-220AA Fiducial
34	H1, H2, H3, H4, H5, H6, H7	7		SJ5382	3М	Bumpon, Hemisphere, 0.25 X 0.075, Clear	75x250 mil
35 36	J1 J2, J4, J5, J6, J8,	6		1-406541-1 PTT-102-01-L-S	TE Connectivity Samtec	RJ-45, No LED, tab up, R/A, TH Header, 2mm, 2x1, Gold, TH	16.26x14.54x15.75 Header, 2mm, 2x1,
37	J12 J3, J11	2		PTT-103-01-L-S	Samtec	Header, 2mm, 3x1, Gold, TH	TH Header, 2mm, 3x1,
38	J7	1		691210910002	Wurth Elektronik	Receptacle, 2.54mm, 2x1, Tin, R/A, TH	TH Receptacle, 2.54m 2x1, R/A, TH
39	J9	1		FTSH-105-01-F-DV	Samtec	Header, 1.27mm, 5x2, Gold, Black, SMT	Header, 1.27mm, 5x2, SMT
40	J10	1		PTT-104-01-L-S	Samtec	Header, 2mm, 4x1, Gold, TH	Header, 2mm, 4x1, TH
41 42	L1, L2 L3	2	300 ohm 3.3uH	742792641 744025003	Wurth Elektronik Wurth Elektronik	Ferrite Bead, 300 ohm @ 100 MHz, 2 A, 0603 Inductor, Shielded Drum Core, Ferrite, 3.3 µH, 1.5 A, 0.085 ohm, SMD	0603 Inductor.
43	14	1	33uH	7447714330	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 33 µH, 2.5 A, 0.066 ohm, SMD	2.8x2.8x2.8mm SMD
44 45	L5 L6	1	2.2uH 330uH	744028002 7447779233	Wurth Elektronik Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 2.2 µH, 1.A, 0.125 ohm, SMD Inductor, Shielded Drum Core, Metal Composite, 330 µH, 0.39 A, 1.15	WE-TPC-T SMD
46	Q1, Q2, Q3, Q4	4	100V	FDN8601	Fairchild Semiconductor	moucon, shielded Drum Core, Metal Composite, 330 µh, 0.39 A, 1.15 ohm, SMD MOSFET, N-CH, 100V, 2.7A, SSOT-3	SSOT-3
47	Q5 R1 R2 R3 R4	1 8	-100V -100V	ZMP10A16KTC CRCW060375R0FKFA	Diodes Inc. Vishay-Dale	MOSFET, P-CH, -100 V, 3 A, DPAK RES, 75.0 ohm, 1%, 0.1W, 0603	DPAK 0603
49	R5, R6, R7, R8 R9, R10, R11.	4	1.00Mea	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
50	R12 R13, R14, R15,	4	232k	CRCW0603232KFKEA	Vishay-Dale	RES, 232 k, 1%, 0.1 W, 0603	0603
51	R16 R17	1	53.6k	CRCW060353K6FKEA	Vishay-Dale	RES, 53.6 k, 1%, 0.1 W, 0603	0603
52	R18, R19, R20, R2	4	1.30k	RC0603FR-071K3L	Yageo America	RES, 1.30 k, 1%, 0.1 W, 0603	0603
53 54	R21 R22	1	27.4k 1.00Mea	CRCW060327K4FKEA CRCW04021M00FKED	Vishay-Dale Vishay-Dale	RES, 27.4 k, 1%, 0.1 W, 0603 RES, 1.00 M, 1%, 0.063 W, 0402	0603 0402
55 56	R23 R24	1	0.18 1.3k	MCR25JZHFLR180 ERJ-6GEYJ132V	Rohm Panasonic	RES, 0.18, 1%, 0.5 W, 1210 RES, 1.3 k, 5%, 0.125 W, 0805	1210 0805
57 58	R26, R31, R33 R27	3	49.9k	CRCW060349K9FKEA CRCW06030000Z0EA	Vishay-Dale Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603 RES, 0, 5%, 0.1 W, 0603	0603 0603
59	R28, R49, R51, R59, R69	5	0	ERJ-2GE0R00X	Panasonic	RES, 0, 5%, 0.063 W, 0402	0402
60	R29 R30	1 1	63.4 243	RC0603FR-0763R4L RC0603FR-07243RL	Yageo America Yageo America	RES, 63.4, 1%, 0.1 W, 0603 RES, 243, 1%, 0.1 W, 0603	0603 0603
62 63	R32 R34, R39, R40,	1 8	23.2k 10.0k	CRCW060323K2FKEA CRCW040210K0FKED	Vishay-Dale Vishay-Dale	RES, 23.2 k, 1%, 0.1 W, 0603 RES, 10.0 k, 1%, 0.063 W, 0402	0603 0402
	R41, R42, R44, R47, R60						
64 65	R35 R36	1	301k 105k	CRCW0603301KFKEA CRCW0402105KFKED	Vishay-Dale Vishay-Dale	RES, 301 k, 1%, 0.1 W, 0603 RES, 105 k, 1%, 0.063 W, 0402	0603 0402
66 67	R37 R38	1	24.9k 5.76k	CRCW040224K9FKED CRCW04025K76FKED	Vishay-Dale Vishay-Dale	RES, 24.9 k, 1%, 0.063 W, 0402 RES, 5.76 k, 1%, 0.063 W, 0402	0402 0402
68 69	R43, R48 R45	2	100 1.00k	ERJ-2RKF1000X CRCW06031K00FKEA	Panasonic Vishay-Dale	RES, 100, 1%, 0.1 W, 0402 RES, 1.00 k, 1%, 0.1 W, 0603	0402 0603
70	R46, R52, R53, R54, R55	5	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9, 1%, 0.063 W, 0402	0402
71 72	R56 R57	1	4.87k 2.21k	CRCW04024K87FKED CRCW04022K21FKED	Vishay-Dale Vishay-Dale	RES, 4.87 k, 1%, 0.063 W, 0402 RES, 2.21 k, 1%, 0.063 W, 0402	0402 0402
73 74	R62 S1	1	2.49k	CRCW04022K49FKED SKRKAEE010	Vishay-Dale Alps	RES, 2.49 k, 1%, 0.063 W, 0402 Switch, Push Button, SMD	0402 2.9x2x3.9mm SME
75	SH-J1, SH-J4, SH J5, SH-J6, SH-J7, SH-J8	6	1x2	2SN-BK-G	Samtec	Shunt, 2mm, Gold plated, Black	2mm Shunt, Close Top
76 77	T1 TP1, TP2	2	350 uH	7490220122 5019	Wurth Elektronik Keystone	Transformer, 350 uH, SMT Test Point, Miniature, SMT	14.7x18.29mm Test Point, Miniatu
78	U1	1		TPS2372-4RGWR	Texas Instruments	Mid Power bt PoE PD Interface with Automatic Maintain Power Signature, Advanced Startup and Ultra-Low Standby Power, RGW0020B (VQFN-20)	RGW0020B
79	U2	1		LM3409HVMYX/NOPB	Texas Instruments	(VQFN-2U) PFET Buck Controller for High Power LED Drives, 10-pin eMSOP, Pb- Free	MUC10A
80	U3	1		TPS62740DSSR	Texas Instruments	7166 360nA IQ Step Down Converter for Low Power Applications, DSS0012A (WSON-12)	DSS0012A
81	U4	1		LM5165DRCR	Texas Instruments	3V-65V, 150mA Synchronous Buck Converter With Ultra-Low IQ, DRC0010J (VSON-10)	DRC0010J
82 83	U5 U6	1		TM4C1292NCPDTI3R DP83822IRHBR	Texas Instruments Texas Instruments	Tha C Series Microcontroller, PDT0128A Robust, Low Power 10/100 Ethernet Physical Layer Transceiver,	PDT0128A RHB0032B
84	U7	1		TPD4E05U06QDQARQ1	Texas Instruments	RHB0032B (VQFN-32) 1, 4, 6 CHANNEL PROTECTION SOLUTION FOR SUPER-SPEED (UP	DQA0010A
85	Y1	1		ABS07-32.768KHZ-9-T	Abracon Corporation	TO 6 GBPS) INTERFACE, DQA0010A CRYSTAL, 32.768KHZ, 9PF, SMD	3.2x0.9x1.5mm
86	Y2	1		NX5032GA-25.000M-STD-CSK- 4	NDK	Crystal, 25MHz, SMD	5x3.2mm
87 88	Y3 D9	0	30V	CX3225CA25000D0HSSCC SD107WS-7-F	Kyocera Diodes Inc.	Crystal, 25MHz, 8pF, SMD Diode, Schottky, 30 V, 0.1 A, SOD-323	3.2x2.5mm SOD-323
89 90	D11 R25	0	Yellow 100k	19-21UYC/S530-A4/TR8 CRCW0402100KFKED	Everlight Vishay-Dale	LED, Yellow, SMD RES, 100 k, 1%, 0.063 W, 0402	0.8x1.6mm 0402
91 92	R50 R58	0	0 3.32k	ERJ-2GE0R00X CRCW04023K32FKED	Panasonic Vishay-Dale	RES, 0, 5%, 0.063 W, 0402 RES, 3.32 k, 1%, 0.063 W, 0402	0402 0402
93 94	R61, R65 R63, R66, R67,	0	10.0k 2.49k	CRCW040210K0FKED CRCW04022K49FKED	Vishay-Dale Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402 RES, 2.49 k, 1%, 0.063 W, 0402	0402 0402
95	R68 R64	0	332	CRCW0402332RFKED	Vishay-Dale	RES, 332, 1%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated