

Filename: Pro437F.tmp  
 Variant: 001  
 Generated: 6/6/2017 7:45:12 AM  
 TID #: N/A



**PMP20634 REV A Bill of Materials**

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	22uF	EKXG401ELL220MK20S	Chemi-Con	CAP, AL, 22 µF, 400 V, +/- 20%, TH	12.5x20mm
2	C2	1	0.1uF	ECQ-U3A104MG	Panasonic	CAP, Film, 0.1 µF, 300 V, +/- 20%, TH	TH, 2-Leads, Body 15x8mm, Pin Spacing 12.5mm
3	C3	1	680uF	EKZE250ELL681MJ20S	Chemi-Con	CAP, AL, 680 µF, 25 V, +/- 20%, TH	D10xL20mm
4	C4	1	10uF	GRM219R61E106KA12	MuRata	CAP, CERM, 10 µF, 25 V, +/- 10%, X5R, 0805	0805
5	C6	1	4.7uF	GRM188R6YA475KE15D	MuRata	CAP, CERM, 4.7 µF, 35 V, +/- 10%, X5R, 0603	0603
6	D1	1	600V	RH06-T	Diodes Inc.	Diode, Switching-Bridge, 600 V, 0.5 A, MiniDIP	MiniDIP
7	D2	1	150V	SMBJ150A-13-F	Diodes Inc.	Diode, TVS, Uni, 150 V, 243 Vc, SMB	SMB
8	D3	1	1.05V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600V, 1A, SMA	SMA
9	D4	1	100V	B3100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 3 A, SMC	SMC
10	D5	1	100V	BAS16J,135	NXP Semiconductor	Diode, Switching, 100 V, 0.25 A, SOD-323F	SOD-323F
11	F1	1		0443001.DR	Littelfuse	Fuse, 1 A, 250VAC/VDC, SMD	FUSE 10.1x3.12x3.13mm
12	L1	1	1mH	744821201	Würth Elektronik	Coupled inductor, 1 mH, 2 A, 0.045 ohm, TH	15 x 18 x 7.5mm
13	Q1	1	600V	FCD4N60TM	Fairchild Semiconductor	MOSFET, N-CH, 600 V, 3.9 A, DPAK	DPAK
14	R1, R3	2	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
15	R2	1	73.2k	CRCW040273K2FKED	Vishay-Dale	RES, 73.2 k, 1%, 0.063 W, 0402	0402
16	R4	1	33.2k	CRCW040233K2FKED	Vishay-Dale	RES, 33.2 k, 1%, 0.063 W, 0402	0402
17	R5, R6	2	1.6	CRCW08051R60JNEA	Vishay-Dale	RES, 1.6, 5%, 0.125 W, 0805	0805
18	R8	1	1.33k	CRCW04021K33FKED	Vishay-Dale	RES, 1.33 k, 1%, 0.063 W, 0402	0402
19	T1	1	500uH	750316686	Würth Elektronik	Transformer, 500 uH, EE16/8/5, TH	EE16/8/5
20	TP1, TP2	2		5012	Keystone	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
21	TP4	1		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
22	TP5	1		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
23	U1	1		UCC28730DR	Texas Instruments	Constant-Voltage Constant-Current Flyback Controller With PSR and Wake-Up Monitoring, D0007A (SOIC-7)	D0007A
24	Q2	0	30V	AO3406	AOS	MOSFET, N-CH, 30 V, 3.6 A, SOT-23	SOT-23
25	R7	0	115k	CRCW0402115KFKED	Vishay-Dale	RES, 115 k, 1%, 0.063 W, 0402	0402
26	R9	0	7.5k	CRCW04027K50JNED	Vishay-Dale	RES, 7.5 k, 5%, 0.063 W, 0402	0402
27	R16, R17	0	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
28	R18	0	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
29	TP6	0		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
30	U4	0		VOS617A-7X001T	Vishay-Semiconductor	Optocoupler, 3.75 kV, 80-160% CTR, SMT	7x2.12x2.6mm

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated