## PMP5123 REV E Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		PMP5123	Any	Printed Circuit Board	Ĭ
C1	1	220uF	APXE160ARA221MJ80G	Nippon Chemi-Con	CAP, AL, 220uF, 16V, +/-20%, 0.022 ohm, SMD	J80
C3, C4, C5	3	22uF	GRM32ER61E226KE15L	MuRata	CAP, CERM, 22uF, 25V, +/-10%, X5R, 1210	1210
C6	1	0.047uF	C3216X7R2E473K	TDK	CAP, CERM, 0.047uF, 250V, +/-10%, X7R, 1206	1206
C7, C8, C9, C10,	5	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10uF, 50V, +/-10%, X7R, 1210	1210
C11						
C12, C13, C15,	7	0.1uF	C1005X7R1H104M	TDK	CAP, CERM, 0.1uF, 50V, +/-20%, C0G/NP0, 0402	0402
C16, C17, C22,						
C28						
C14	1	0.47uF	GRM21BR72A474KA73L	MuRata	CAP, CERM, 0.47 μF, 100 V, +/- 10%, X7R, 0805	0805
C18	1	220uF	EEE-FK1C221XP	Panasonic	CAP, AL, 220uF, 16V, +/-20%, 0.34 ohm, SMD	SMT Radial D8
C19	1	100pF	CC0402KRX7R9BB101	Yageo America	CAP, CERM, 100pF, 50V, +/-10%, X7R, 0402	0402
C20	1	0.22uF	GRM155R61A224KE19D	MuRata	CAP, CERM, 0.22uF, 10V, +/-10%, X5R, 0402	0402
C21	1	1000pF	STD	STD	CAP, CERM, 1000pF, 3kV, 1808	1808
C23	1	0.047uF	GRM155R71E473KA88D	MuRata	CAP, CERM, 0.047uF, 25V, +/-10%, X7R, 0402	0402
C24, C30, C31,	6	DNP	N/A	N/A	Do Not Populate	0402
R19, R25, R27						
C25	1	0.1uF	C0805C104K1RACTU	Kemet	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0805	0805
C26	1	0.01uF	C1005X7R1E103K	TDK	CAP, CERM, 0.01uF, 25V, +/-10%, X7R, 0402	0402
C27	1	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047uF, 50V, +/-10%, X7R, 0603	0603
C29	1	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	0402
C32	1	22pF	GRM1555C1H220JA01D	MuRata	CAP, CERM, 22pF, 50V, +/-5%, C0G/NP0, 0402	0402
C33	1	1000pF	C1005X7R1H102K	TDK	CAP, CERM, 1000pF, 50V, +/-10%, X7R, 0402	0402
C34	1	4.7uF	C3216X7R1E475K	TDK	CAP, CERM, 4.7uF, 25V, +/-10%, X7R, 1206	1206
D1	1	200V	ES1D-13-F	Diodes Inc.	Diode, Ultrafast, 200V, 1A, SMA	SMA
D2, D4, D10,	4	100V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100V, 0.25A, SOD-323	SOD-323
D400						
D3	1	10V	MMSZ4697T1G	ON Semiconductor	Diode, Zener, 10 V, 500 mW, SOD-123	SOD-123
D5, D6, D11	3	1.25V	BAV21W-7-F	Diodes Inc.	Diode, Switching, 200V, 0.2A, SOD-123	SOD-123
D7, D14, D15	3	1.4V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100V, 0.25A, SOD-323	SOD-323
D8, D9	2	200V	BAV21W-7-F	Diodes Inc.	Diode, Switching, 200 V, 0.2 A, SOD-123	SOD-123
D12, D13	2	60V	SD101AWS-7-F	Diodes Inc.	Diode, Schottky, 60V, 0.015A, SOD-323	SOD-323
J1, J2	2		ED555/2DS	On-Shore Technology	Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm
L1	1	17.1uH	PA2729.173NL	Pulse Engineering	Inductor, Shielded Drum Core, Ferrite, 17.1 µH, 9.9 A, 0.0091 ohm, SMD	Inductor, 22.2x12.2x19mm
L2	1	1mH	LPS4414-105MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 1mH, 0.11A, 16.3 ohm, SMD	LPS4414
Q1	1	0.6V	BF622,115	NXP Semiconductor	Transistor, NPN, 250V, 0.05A, SOT-89	SOT-89
Q2	1	150V	FDMS86200	Fairchild Semiconductor	MOSFET, N-CH, 150 V, 35 A, PQFN08A	PQFN08A
Q3	1	-80V	FDC3535	Fairchild Semiconductor	MOSFET, P-CH, -80V, 2.1A, SSOT-6	SSOT-6
Q4, Q5	2	100V	CSD19533Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 13 A, SON 5x6mm	SON 5x6mm
Q6	1	100V	CSD19534Q5A	Texas Instruments	MOSFET, N-CH, 100V, 10A, SON 5x6mm	SON 5x6mm
Q7	1	1.6V	MMBT2907A	Fairchild Semiconductor	Transistor, PNP, 60V, 0.8A, SOT-23	SOT-23
Q8	1	0.3V	MMBT2222A	Fairchild Semiconductor	Transistor, NPN, 40V, 0.15A, SOT-23	SOT-23
R1	1	10k	CRCW251210K0JNEG	Vishay-Dale	RES, 10 k, 5%, 1 W, 2512	2512
R2	1	6.49k	CRCW08056K49FKEA	Vishay-Dale	RES, 6.49k ohm, 1%, 0.125W, 0805	0805
R3	1	0.1	ERJ-6RSJR10V	Panasonic	RES, 0.1 ohm, 5%, 0.125W, 0805	0805

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R4, R6, R16, R22,	6	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0k ohm, 1%, 0.063W, 0402	0402
R23, R28						
R5	1	1.00	CRCW08051R00FKEA	Vishay-Dale	RES, 1.00 ohm, 1%, 0.125W, 0805	0805
R7	1	49.9k	CRCW080549K9FKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.125W, 0805	0805
R8	1	10	CRCW040210R0JNED	Vishay-Dale	RES, 10, 5%, 0.063 W, 0402	0402
R9, R26	2	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00k ohm, 1%, 0.063W, 0402	0402
R10, R13, R17,	4	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9k ohm, 1%, 0.063W, 0402, RES, 49.9 k, 1%, 0.063 W, 0402,	0402
R29					RES, 49.9k ohm, 1%, 0.063W, 0402, RES, 49.9k ohm, 1%, 0.063W, 0402	
R11	1	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402	0402
R12	1	7.50k	CRCW04027K50FKED	Vishay-Dale	RES, 7.50 k, 1%, 0.063 W, 0402	0402
R14	1	9.76k	CRCW04029K76FKED	Vishay-Dale	RES, 9.76k ohm, 1%, 0.063W, 0402	0402
R15	1	121k	CRCW0402121KFKED	Vishay-Dale	RES, 121 k, 1%, 0.063 W, 0402	0402
R18	1	2.00k	CRCW04022K00FKED	Vishay-Dale	RES, 2.00k ohm, 1%, 0.063W, 0402	0402
R20	1	71.5k	CRCW040271K5FKED	Vishay-Dale	RES, 71.5 k, 1%, 0.063 W, 0402	0402
R21	1	4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99k ohm, 1%, 0.063W, 0402	0402
R24	1	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100k ohm, 1%, 0.063W, 0402	0402
R30	1	2.61k	CRCW04022K61FKED	Vishay-Dale	RES, 2.61k ohm, 1%, 0.063W, 0402	0402
T1	1	18uH	PA4138NL	Pulse Engineering	Transformer, 18uH, TH	1050x550x1050mil
T2	1		PA1005.100NL	Pulse Engineering	SMT Current Sense Tranformer	P82xx
TP1, TP3	2	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose
						Testpoint
TP2, TP4	2	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose
						Testpoint
U1, U2, U3	3		UCC27511DBV	Texas Instruments	Single-Channel High-Speed Low-Side Gate Driver (with 4-A Peak Source	DBV0006A
					and 8-A Peak Sink), DBV0006A	
U4	1		UCC2897ARGPR	Texas Instruments	Advanced Active Clamp PWM Controller with Current Control, -40 to +125	RGP0020D
					degC, 20-pin QFN (RGP), Green (RoHS & no Sb/Br)	
U5	1		VOS617A-7X001T	Vishay-Semiconductor	OptoCoupler, Phototransitor, 80-160%, SSOP-4	7x2.12x2.6mm
U6	1		TL331DBV	Texas Instruments	SINGLE DIFFERENTIAL COMPARATOR, DBV0005A	DBV0005A
U7	1		TL431AIDBZ	Texas Instruments	PRECISION PROGRAMMABLE REFERENCE, DBZ0003A	DBZ0003A

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.