

66AK2G02 Power Estimation Tool

Catalog Processors

ABSTRACT

This power estimation spreadsheet provides power consumption estimates based on measured and simulated data; they are provided “as is” and are not ensured within a specified precision. Power consumption depends on electrical parameters, silicon process variations, environmental conditions, and use cases running on the processor during operation. Actual power consumption should be verified in the real system.

The spreadsheet discussed in this application report can be downloaded from the following URL: <http://www.ti.com/lit/zip/sprac81>.

Contents

1	Introduction	1
2	Using the Power Estimation Tool	2
3	Important Notes and Limitations	2

Trademarks

All trademarks are the property of their respective owners.

1 Introduction

The Power Estimation Tool (PET) allows users to gain insight into the power consumption of 66AK2G02 DSP + ARM Processor. The tool includes the ability for the user to choose multiple application scenarios and understand the power consumption as well as how advanced power saving techniques can be applied to further reduce overall power consumption.

PET spreadsheet is comprised of two parts:

- Input – The input part of the spreadsheet is the mechanism in which users input device parameters needed for their application. Parameters include device junction temperature, clock configurations and use case input.
- Output – The output part of the spreadsheet contains the information on 66AK2G02 power consumption based on power calculations in the spreadsheet. The output report which includes voltage, current and power will be shown in 66AK2G02 power consumption section.

The data presented in the PET spreadsheet are based on measurements performed on 66AK2G02 silicon, as well as estimates.

For additional details about the 66AK2G02 processor, see the [TI.com product page](#).

2 Using the Power Estimation Tool

The Input part of the spreadsheet consists of two sections: General and Use Case Input. To use the input part of the spreadsheet, users need to modify the input fields with their appropriate usage parameters. Cells that are designed for user input are light blue in color. Simply configure the light blue cells to a value most closely aligned with your intended scenario.

2.1 Macro Buttons

The spreadsheet includes macros. If you can't run macros, please review your excel security settings described in below articles.

- [Change macro security settings in Excel \(Office 2010\)](#)
- [Change macro security settings in Excel \(Office 2007\)](#)

The input part of the spreadsheet has command buttons to run macros as follows:

- "Reset Settings" - Clear all settings and configure them to the default values.
- "Generic" - Set use case condition for typical ARM and DSP usage scenario.
- "High DSP Activity" - Set use case condition for high DSP activity scenario.

2.2 General

This section allows users to set a junction temperature (not ambient temperature) and PLL clock frequency option.

- Junction Temperature (°C) : 0°C to 125°C (negative values are not supported in the tool)
- Power Estimation Mode : Max ('Max' accounts for the worst-case silicon process variation. The option is fixed to Max in this version of the PET)
- Main PLL Frequency (MHz): 600 or 400 MHz
- ARM PLL Frequency (MHz): 600, 400 or 200 MHz
- DDR PLL Frequency (MHz): 400 MHz
- ICSS PLL Frequency (MHz): 225 MHz

2.3 Use Case Input

- Power Domain: Power domain information for each modules
- Module: Name of processing cores or peripheral modules.
- Frequency (MHz): The module operating frequency configured by PLL configurations
- State: Specifies whether a peripheral is enabled and configured for use, or disabled and unconfigured
- Utilization (%): Specifies the utilization as a percentage of processing load relative to a full load condition

2.4 66AK2G02 Power Consumption

The power estimation tool generates a power analysis report in this section. The report lists power supply name, voltage in V, current in mA and power consumption in mW per power rail groups. The total power consumption in mW is listed at the end of the table.

3 Important Notes and Limitations

The following limitations apply to the 66AK2G02 Power Estimation Tool:

It is up to the user to input reasonable utilization numbers for processing cores (MPU and DSP) for the purposes of maximum power analysis. 90-100% loading on the processing cores is not realistic for most application scenarios

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated