## Filename: UCD3138PWR-153-BOM.xls

Date: 04/23/2012

## **BILLOFMATERIALS BOM**

COUNT	RefDes	Value	Description	Size	Part Number	MFR
4	C1, C2, C3, C5	2.2uF	Capacitor, Ceramic Chip, 100V, 5%	1210	Std	STD
4	C11, C12, C13, C14	47uF	Capacitor, Ceramic Chip, 16V, 5%	1210	Std	STD
1	C15	820pF	Capacitor, Ceramic Chip, 16V, 5%	0402	STD	STD
1	C16	68nF	Capacitor, Ceramic Chip, 16V, 5%	0402	STD	STD
2	C17, C18	47pF	Capacitor, Ceramic Chip, 100V, 5%	0603	STD	STD
1	C23	0.01uF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
3	C24, C25, C28	1nF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
	C26, C37, C40, C41,					
7	C44, C45, C51	0.1uF	Capacitor, Ceramic Chip, 16V, 5%	0402	STD	STD
1	C27	2.2nF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
2	C31, C39	1uF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
1	C32	4.7uF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
2	C34, C38	10pF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
1	C35	560pF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
1	C36	2200pF	Capacitor, Ceramic Chip, 50V, 5%	0603	STD	STD
2	C42, C50	220pF	Capacitor, Ceramic Chip, 50V, 5%	0402	STD	STD
2	C43, C48	4.7uF	Capacitor, Ceramic Chip, 16V, 10%	0805	STD	STD
1	C46	22nF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
1	C47	680pF	Capacitor, Ceramic Chip, 500V, 5%	1206	STD	STD
1	C49	10uF	Capacitor, Ceramic Chip, 16V, 10%	0805	STD	STD
1	C52	2200pF	Capacitor, Ceramic Chip, 16V, 10%	0402	STD	STD
1	C6	47pF	Capacitor, Ceramic Chip, 6.3V, 5%	0402	STD	STD
4	C7, C10, C21, C22	0.1uF	Capacitor, Ceramic Chip, 25V, 5%	0603	STD	STD
4	C8, C9, C19, C20	1uF	Capacitor, Ceramic Chip, 16V, 5%	0603	STD	STD
1	D10	5.1V	zener diode 5.1V, SOD323		BZX384	
1	D5	BAT46W	schottky diode 100V SOD123		BAT46W	
1	D6	MMBD7000	DIODE SWITCH DUAL 100V SOT23 SER			
1	D7	BAT54	Schottky SWITCH 30V SOD523		BAT54	
1	J6	HEADER 100-2X4	SHR SHROUDED HEADER 8 POS STRAIGHT		576-2510-6002UB	

					530-	
1	L1	100nH	INDUCTOR POWER .1UH 11A SMD		IHLP1616BZERR10M	
1	L2	1.5uH	POWER XFMR 400W 5:4		RM6	
				0.190 x		
1	L3	MA5401-AE	MA5401-AE Flyback Transformer	0.190 inch	MA5401-AE	Coilcraft
1	ON/OFF	TEST POINT			5012	
1	PGND	TEST POINT			5012	
				QFN5X6m		Vishay
4	Q1, Q2, Q3, Q4	SiS892DN	MOSFET, NChan, For ENG. use only	m	STD	Siliconix
4	Q5, Q6, Q7, Q8	FDMS86101	FDMS8610 Power Pad FET		FDMS8610	
1	R1	7.1	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R11	15	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R12	2.5k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
2	R13, R14	51.1	Resistor, Chip, 1/10W, 1%	0805	STD	STD
1	R15	Copper resistance	Resistor, Chip, 1/16W, 1%	0402	Std	Std
2	R16, R32	15k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R17	4.6k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R18	33.2k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R19	1.5k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
	R2, R4, R6, R8, R9, R10,	,				
8	R21, R29	10k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R20	100	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R22	2k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
3	R24, R26, R42	0	Resistor, Chip, 1/16W, 1%	0402	Std	Std
2	R27, R38, R49	3.32k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
	R3, R5, R23, R25, R28,					
	R30, R31, R36, R41,					
12	R44, R48, R50	1k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R33	6.9k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R34	5.11k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R35	120k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
2	R37, R46	100k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R39	25k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R47	0.75	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R52	NL	Resistor, Chip, 1/16W, 1%	0402	Std	Std

1	R7	130k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	Т2	XFMR 5:2:2	POWER XFMR 300W 5:2:2		RM6	
2	TP1, TP2	None	Test point, 40 mil SMT	None	None	None
			IC, 120 V Boot, 2.5A Peak, High-Freq. High-Side Low-Side			
2	U1, U2	UCC27211DRM	Driver	QFN-8	UCC27211DRM	TI
1	U11	LM60C	IC SENSOR TEMPERATURE SOT-23		LM60C	
1	U3	UCC27524	IC MOSFET DRVR DUAL HS 4A 8-MSOP		023-00019	
1	U4	ISO7420FED	Dual CHANNEL 25 MBPS DIGITAL ISOLATOR		521-ISO7420	
1	U5	OPA365NA	IC, R-R Op Amp, Single Supply,	SOT23-5	OPA365NA	TI
1	U6	UCD3138RHA	IC, Digital Power Controllers	QFN	UCD3138RHA	ТΙ
1	U7	UCC25230	IC, Bias Supply		UCC25230	ТΙ
1	U8	TPS76201	IC 3.3V HI-IN LDO REG 8-SON		521-TPS76201	
1	VIN+	TEST POINT			5012	
2	VOUT+, VOUT-	TEST POINT			5012	

Notes: 1. These assemblies are ESD sensitive, ESD precautions shall be observed.

- 2. These assemblies must be clean and free from flux and all contaminants. Use of no clean flux is not acceptable.
- 3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
- 4. Ref designators marked with an asterisk ('\*\*') cannot be substituted.All other components can be substituted with equivalent MFG's components.

## **IMPORTANT NOTICE FOR TI REFERENCE DESIGNS**

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2013, Texas Instruments Incorporated