

Bill of Materials

TI DESIGNS

TIDM-BOOST-IR-REMOTE - MSP-EXP430FR4133

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1	1	LCD1		FH1138P	Adkom Elektronik	FH-1138P			
2	1	J101		PINHD-2X9	Townes	P101-2*9SGF-116A-NX			
3	1	JP1		JUMPER_2.51MM	Townes	P101-1*02SGF-116C-NX			
4	1	J6		PINHEADER1X3	Townes	P101-1*03SGF-116C-NX			
5	2	J1,J2		PINHEADER1X10	JXT	JT254F-D180-850-110-10D			
6	1	R119	0R	RES ZERO OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-070RL		0402	
7	1	R106	1M	RES 1M OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-071ML		0402	
8	1	R105	1k4	RES 1K4 OHM 1/16W 5% 0402 SMD	Yageo	RC0402FR-071K4L		0402	
9	2	C11,C112	1n	CAP,1NF,+/-10%,X7R,50V,SMD	Murata	GRM155R71H102KA01D		0402	
10	1	C4	1u	CAP,1UF,+/-10%,X5R,6.3V,SMD	Murata	GRM155R60J105ME19D		0402	
11	1	C108	1u	CAP,1UF,+/-10%,X5R,6.3V,SMD	Murata	GRM188R61A105KA61D		0603	
12	1	R126	2k2	RES 2K2 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-072K2L		0402	
13	1	L101	2u2	INDUCTOR 2.2UH 20% 1007 SMD	Taiyo Yuden	CBC2518T2R2M		1206	
14	1	R127	3k3	RES 3K3 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-073K3L		0402	
15	2	C117,C119	4.7u	CAP,4.7UF,+/-10%,X5R,10V,SMD	Murata	GRM188R61A475KE15D		0603	
16	2	C106,C109	4.7u	TCAP,4.7UF,+/-10%,16V,SMD1206(A)	AVX	TAJA475K016RNJ		A	
17	2	R116,R117	4k7	RES 4K7 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-074K7L		0402	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
18	1	R128	6k8	RES 6K8 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-076K8L		0402	
19	2	C110,C111	10p	CAP,10PF,+/-5%,C0G,50V,SMD	Murata	GRM1555C1H100JA01D		0402	
20	1	C7	10u	CAP,10UF,+/-10%,X5R,10V,SMD	Murata	GRM188R61A106KE69D		0603	
21	1	C104	10u	TCAP,10UF,+/-10%,10V,SMD	AVX	TAJA106K010RNJ		A	
22	2	C5,C6	12p	CAP,12PF,+/-5%,C0G,50V,SMD	Murata	GRM1555C1H120JA01D		0402	
23	2	R103,R104	27R	RES 27 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-0727RL		0402	
24	1	Y1	32.768kHz	Crystal 32.768KHz 12.5PF	MICRO CRYSTAL	MS3V-T1R			
25	4	C115,C116,C122,C123	33p	CAP,33PF,+/-5%,C0G,50V,SMD	Murata	GRM1555C1H330JA01D		0402	
26	1	R123	33k	RES 33K OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-0733KL		0402	
27	4	R1,R107,R108,R109	47k	RES 47K OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-0747KL		0402	
28	15	C1,C2,C3,C8,C10,C103,C113,C114,C118,C120,C121,C124,C105,C126	100n	CAP,100NF,+/-10%,X7R,16V,SMD	Murata	GRM155R71C104KA88D		0402	
29	1	R125	150k	RES 150K OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-07150KL		0402	
30	6	R112,R113,R114,R115,R121,R122	220k	RES 220K OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-07220KL		0402	
31	2	C102,C107	220n	CAP,220NF,+/-10%,X5R,10V,SMD	Murata	GRM155R61A224KE19D		0402	
32	1	R124	240k	RES 220K OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-07240KL		0402	
33	5	R4,R5,R101,R102,R120	470R	RES 470 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-07470RL		0402	
34	1	C101	470n	CAP,470NF,+/-10%,X5R,10V,SMD	Murata	GRM155R61A474KE15D		0402	
35	1	R118	820R	RES 820 OHM 1/16W 5% 0402 SMD	Yageo	RC0402JR-07820RL		0402	
36	2	D101,D102	BAS40-05	General-purpose Schottky diodes	NXP	BAS40-05W		SC70	
37	1	T102	BC850CW-115	NPN general purpose transistors	NXP	BC850CW		SC70	
38	1	T101	DMG1013UW	P-Channel Enhancement Mode Field-Effect Transistor	ON	DMG1013UW		SC70	
39	1	MSP101	MSP430F5528IRGC	MSP430 Microcontroller	TI	MSP430F5528IR		RGC64	
40	1	U1	MSP430FR4133IPM	MSP430 Microcontroller	TI	MSP430FR4133IPM		LQFP64	
41	1	MSP102	MSP430G2452IRSA16R	MSP430 Microcontroller	TI	MSP430G2452IR		RSA16	
42	1	J102	Micro-USB	Micro-USB connector	Hirose	ZX62R-B-5P		SMD	
43	1	Q101	CSTCR4M00G15L99	Resonators 4MHZ	Murata	CSTCR4M00G15L99-R0		SMD	
44	2	LED1,LED101	Red	Chip LED RED	Everlight	17-215SURC/S530-A2/TR8		0805	
45	3	S1,S2,S3	T062S	Switch,Tacticle,160gf+/-50gf,black housing,black plunger,6.6*6*4.3MM,SMD	kaler	T062S-043FBT04B		SMD	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
46	1	IC102	TPD4E004DRYR	4-Channel ESD-Protection Array	TI	TPD4E004DRYR		son6	
47	1	IC103	TS5A21366RSER	0.75ohm DUAL SPST analog switch with 1.8v compatible input logic	TI	TS5A21366RSER		RSE8	
48	1	IC101	TLV70033DSE	200mA,Low-Dropout Regulator for portable devices	TI	TLV70033DSE		DSE6	
49	2	LED102,LED2	green	Chip LED Green	Everlight	17-215SYGC/S530-E2/TR8		0805	
50	1	PCB		2 layers PCB,Red Soldermask,white Silkscreen,Immersion gold,58.5mm*101.5mm,MSP-EXP430FR4133 PCB		MSP-EXP430FR4133 PCB			



Bill of Materials

TI DESIGNS

TIDM-BOOST-IR-REMOTE - BOOST-IR

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1	1	C1	100nF	CAP CER 0.1UF 10V 10% X7R	Standard			C0603	
2	1	C2	100uF	CAP CER 100UF 6.3V 20% X5R 1206,Digikey 490-4539-1-ND	Standard			C1206	
3	1	C3	100nF	CAP CER 0.1UF 10V 10% X7R 0603,Digikey 399-1095-2-ND	Standard			C0603	
4	1	C4	10uF	CAP CER 10UF 10V 10% X5R 0805,Digikey 587-1300-1-ND	Standard			C0805	
5	1	C5	1uF	CAP CER 1UF 10V 10% X5R 0603,Digikey 399-3118-2-ND	Standard			C0603	
6	1	IR_RX	TSOP58438	VISHAY TSOP58438 IR RECEIVER, MINICAST AGC2, 38KHZ	Standard	TSOP58438			
7	1	IR_TX	TSAL6200	IR EMITTER, 940NM, T-1 3/4, THROUGH HOLE	Standard	TSAL6200		Radial, 5mm Dia (T 1 3/4)	
8	1	J1		Header, Female 10-pin, 100mil spacing	CM	CNT-F254-1-10-GM2-850-4.2		1X10 SMD	
9	1	J2		Header, Female 10-pin, 100mil spacing	CM	CNT-F254-1-10-GM2-850-4.2		1X10 SMD	
10	1	J3		FPC Connector, UPPER CONTACT, 8pins, 1mm pitch	CM				
11	1	J4		CONN HEADER 3POS .100" SNGL TIN,Digikey SAM1075-03-ND	Standard			1X03	
12	1	J5		TERM BLOCK HDR 2POS VERT 3.5MM,Digikey A104641-ND	Standard			1X02	
13	1	LED		LED BLUE CLEAR 0603 SMD,Digikey 160-1646-6-ND	Standard			CHIPLED_0603	
14	1	R1	OR	RES 0.0 OHM .5W JUMP 1206 SMD, Digikey 541-0.0UBCT-ND	Standard			R1206	
15	1	R2	47R	RES 47 OHM 2/3W 5% 1206 SMD,Digikey P47ALTR-ND	Standard			R1206	
16	1	R3	100R	RES 100 OHM 1/4W 5% 0603 SMD,Digikey RHM100DTR-ND	Standard			R0603	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
17	1	R4	330R	RES 330 OHM 1/4W 5% 0603 SMD,Digikey RHM330DTR-ND	Standard			R0603	
18	1	R5	22R	RES 22 OHM 1/4W 5% 0603 SMD,Digikey RHM22DCT-ND	Standard			R0603	
19	1	R6	100R	RES 100 OHM 1/4W 5% 0603 SMD,Digikey RHM100DTR-ND	Standard			R0603	
20	1	R7	100k	RES 100K OHM 1/4W 5% 0603 SMD,Digikey RHM100KDTR-ND	Standard			R0603	
21	1	R8	1M	RES 1M OHM 1/4W 5% 0603	Standard			R0603	
22	1	R9	1k	RES 1K OHM 1/4W 1% 0603	Standard			R0603	
23	1	T1	FMMT491ATA	Transistors Bipolar - BJT NPN	Standard	FMMT491ATA		SOT-23	
24	1	T2	DMG1013UW-7	MOSFET P-CH 20V 820MA	Standard	DMG1013UW-7		SOT-323	
25	1	KEYPAD1		4x4 Membrane Keypad	CM				

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.