

TIDA-00801

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
IPC B1	1		Printed Circuit Board		TIDA-00801	Any	-	-
C1, C15	2	10uF	CAP, CERM, 10 uF, 50 V, +/- 10%, X7R, 2220	2220	CGA9N3X7R1H106K230KB	TDK		
C3	1	220uF	CAP, AL, 220 uF, 63 V, +/- 20%, 0.26 ohm, SMD	SMT Radial H13	EEE-TK1J221AQ	Panasonic		
C4, C8	2	1uF	CAP, CERM, 1 uF, 25 V, +/- 5%, X7R, 1206 190	1206_190	CL31B105JAHNNNE	Samsung Electro-Mechanics		
C6, C7	2	560uF	CAP, AL, 560 uF, 50 V, +/- 20%, 0.05 ohm, TH	D12.5xL25mm	EEU-FC1H561	Panasonic		
C9, C19, C20	3	100uF	CAP, CERM, 100 uF, 10 V, +/- 20%, X5R, 1210	1210	LMK325ABJ107MMHT	Taiyo Yuden		
C10, C21	2	1uF	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 1206	1206	C1206C105K3RACTU	Kemet		
C12, C27	2	47pF	CAP, CERM, 47 pF, 50 V, +/- 5%, COG/NP0, 0603	0603	GRM1885C1H470JA01D	MuRata		
C13	1	470pF	CAP, CERM, 470 pF, 50 V, +/- 10%, X7R, 0603	0603	C0603C471K5RACTU	Kemet		
C14, C26	2	0.22uF	CAP, CERM, 0.22 uF, 25 V, +/- 10%, X5R, 0603	0603	GRM188R61E224KA88D	MuRata		
C16	1	0.1uF	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603	C0603C104J3RACTU	Kemet		
C17	1	4.7uF	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X5R, 0603_095	0603_095	GRM188R61E475KE11D	MuRata		
C18, C24, C25, C28	4	0.01uF	CAP, CERM, 0.01 uF, 25 V, +/- 10%, X7R, 0603	0603	GRM188R71E103KA01D	MuRata		
C22	1	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603	GRM188R71H102KA01D	MuRata		
C29	1	680pF	CAP, CERM, 680 pF, 25 V, +/- 5%, COG/NP0, 0402	0402	C1005C0G1E681J	TDK		
C30	1	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603	C0603C102K5RACTU	Kemet		
C31	1	0.012uF	CAP, CERM, 0.012 uF, 25 V, +/- 5%, X7R, 0603	0603	06033C123JAT2A	AVX		
C32	1	18pF	CAP, CERM, 18 pF, 50 V, +/- 5%, COG/NP0, 0603	0603	C1608C0G1H180J	TDK		
C33	1	27pF	CAP, CERM, 27 pF, 50 V, +/- 5%, COG/NP0, 0603	0603	06035A270JAT2A	AVX		
C34	1	120pF	CAP, CERM, 120 pF, 50 V, +/- 5%, COG/NP0, 0603	0603	GRM1885C1H121JA01D	MuRata		
C35, C44, C47, C49, C51, C53, C55, C65, C67	9	4.7uF	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X5R, 0805	0805	C2012X5R1E475K125A B	TDK		
C36, C45	2	0.1uF	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402	GCM155R71C104KA55D	MuRata		
C37	1	10uF	CAP, CERM, 10 uF, 16 V, +/- 20%, X5R, 0603	0603	EMK107BBJ106MA-T	Taiyo Yuden		
C38, C40, C41, C42, C43	5	2.2uF	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X5R, 0603	0603	GRM188R61C225KAAD	MuRata		
C39, C46, C48, C50, C52, C54, C56, C66, C68	9	47uF	CAP, CERM, 47 uF, 10 V, +/- 10%, X7R, 1210	1210	GRM32ER71A476KE15L	MuRata		
C57, C58, C59, C60, C61, C62, C63, C64	8	2.2uF	CAP, CERM, 2.2 uF, 6.3 V, +/- 20%, X5R, 0402	0402	GRM155R60J225ME15D	MuRata		
C69	1	0.1uF	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X5R, 0603	0603	GRM188R61C104KA01D	MuRata		
C70	1	1uF	CAP, CERM, 1 uF, 16 V, +/- 10%, X5R, 0603	0603	GRM185R61C105KE44D	MuRata		
C71	1	220pF	CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0603	0603	C1608X7R1H221K	TDK		
C72	1	0.01uF	CAP, CERM, 0.01 uF, 10 V, +/- 10%, X5R, 0402	0402	GRM155R61A103KA01D	MuRata		
C73	1	10uF	CAP, CERM, 10 uF, 25 V, +/- 10%, X5R, 0805	0805	C2012X5R1E106K125A B	TDK		
C74, C75, C76, C82, C83	5	10uF	CAP, CERM, 10 uF, 6.3 V, +/- 10%, X7R, 0805	0805	GRM21BR70J106KE76L	MuRata		
C77	1	0.1uF	CAP, CERM, 0.1 uF, 25 V, +/- 10%, X8R, 0603	0603	CGA3E2X8R1E104K080AA	TDK		
C78	1	10pF	CAP, CERM, 10 pF, 100 V, +/- 5%, COG/NP0, 0603	0603	GRM1885C2A100JA01D	MuRata		
C79, C80, C81	3	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 1%, COG/NP0, 0603	0603	GRM1885C1H102FA01J	MuRata		
D1, D2	2	45V	Diode, Schottky, 45 V, 15 A, CFP15	CFP15	PMEG045V150EPDAZ	NXP Semiconductor		
D3	1	Super Red	LED, Super Red, SMD	LED, 1.6x.6x.8mm	SML-LX0603SRW-TR	Lumex		
D4	1	Green	LED, Green, SMD	1.7x0.65x0.8mm	LG L29K-G2J1-24-Z	OSRAM		
H1, H2, H3, H4	4		Bump on, Hemisphere, 0.375 X 0.235, Black	Black Bump on	SJ61A2	3M		
H5, H6	2		WASHER FLAT 1/4 NYLON	0.260"ID x 0.437"OD x 0.062"THK	3218	Keystone		
J1	1		BANANA JACK, SOLDER LUG, RED, TH	Red Insulated Banana Jack	SPC15363	Tenma		
J2	1		BANANA JACK, SOLDER LUG, BLACK, TH	Black Insulated Banana Jack	SPC15354	Tenma		
J3	1		Header, 100mil, 12x1, Gold, TH	12x1 Header	TSW-112-07-G-S	Samtec		
J4, J5	2		Header, 100mil, 2x1, Gold, TH	Header, 100mil, 2x1, TH	HTSW-102-07-G-S	Samtec		
L1	1	1.8uH	Inductor, Shielded Drum Core, Superflux, 1.8uH, 16A, 0.0035 ohm, SMD	WE-HC6	744325180	Würth Elektronik eiSos		
L2	1	10uH	Inductor, Shielded Drum Core, Powdered Iron, 10uH, 3A, 0.102 ohm, SMD	IHLP-2525CZ	IHLP2525CZER100M01	Vishay-Dale		
L3	1	4.7uH	Inductor, Shielded Drum Core, Powdered Iron, 4.7uH, 5.5A, 0.037 ohm, SMD	IHLP-2525CZ	IHLP2525CZER4R7M01	Vishay-Dale		
L4, L5, L6, L7, L8, L9, L10, L11, L12	9	1uH	Inductor, Shielded Drum Core, Powdered Iron, 1 uH, 4 A, 0.05 ohm, SMD	4.7x1.2x4.3mm	IHLP1616ABER1R0M01	Vishay-Dale		
Q1	1	-60V	MOSFET, P-CH, -60 V, .50 A, DPAK	DPAK	SUD50P06-15L-E3	Vishay-Semiconductor		None
Q2, Q3, Q5, Q6	4	40V	MOSFET, N-CH, 40 V, 19 A, SOIC-8	SOIC-8	Si4840BDY-T1-GE3	Vishay-Siliconix		None
Q4	1	40V	MOSFET, N-CH, 40 V, 42 A, DPAK	DPAK	IRLR3114ZTRPBF	International Rectifier		None
R1	1	0.022	RES, 0.022, 1%, 1 W, 0612	0612	PRL1632-R022-F-T1	Susumu Co Ltd		
R3	1	432k	RES, 432 k, 1%, 0.1 W, 0603	0603	CRCW0603432KFKEA	Vishay-Dale		
R4	1	1.50k	RES, 1.50 k, 1%, 0.1 W, 0603	0603	ERJ-3EK1F1501V	Panasonic		
R5, R11	2	82.5k	RES, 82.5 k, 1%, 0.1 W, 0603	0603	CRCW0603825KFKEA	Vishay-Dale		
R6	1	0.015	RES, 0.015, 1%, 3 W, 4527	4527	WSR3R0150F5A	Vishay-Dale		
R7	1	49.9k	RES, 49.9 k, 0.1%, 0.1 W, 0603	0603	RG1608P-4992-B-T5	Susumu Co Ltd		
R8	1	0.015	RES, 0.015, 1%, 1 W, 0612	0612	PRL1632-R015-F-T1	Susumu Co Ltd		
R10	1	255k	RES, 255 k, 1%, 0.1 W, 0603	0603	CRCW0603255KFKEA	Vishay-Dale		
R12	1	1.0k	RES, 1.0 k, 5%, 0.1 W, 0603	0603	CRCW06031K00JNEA	Vishay-Dale		
R13	1	39k	RES, 39 k, 5%, 0.1 W, 0603	0603	RC0603JR-0739KL	Yageo America		
R14	1	27.0k	RES, 27.0 k, 0.5%, 0.1 W, 0603	0603	RT0603DRD0727KL	Yageo America		
R15, R20, R25	3	10.0k	RES, 10.0 k, 1%, 0.1 W, 0603	0603	RC0603FR-0710KL	Yageo America		
R16, R17, R18, R19	4	2.2k	RES, 2.2 k, 5%, 0.063 W, 0402	0402	CRCW04022K20JNED	Vishay-Dale		
R23, R24	2	0	RES, 0.5%, 0.063 W, 0402	0402	RC0402JR-070RL	Yageo America		
R26, R29, R30	3	10.0k	RES, 10.0 k, 1%, 0.1 W, 0603	0603	CRCW060310K0KFKEA	Vishay-Dale		
R27	1	100k	RES, 100 k, 5%, 0.1 W, 0603	0603	CRCW0603100KJNEA	Vishay-Dale		
R28	1	10.0	RES, 10.0, 0.1%, 0.1 W, 0603	0603	TNPW060310R0BEEA	Vishay-Dale		

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
R31	1	49.9	RES, 49.9, 1%, 0.1 W, 0603	0603	RC0603FR-0749R9L	Yageo America		
R32	1	806	RES, 806, 1%, 0.1 W, 0603	0603	CRCW0603806RFKEA	Vishay-Dale		
S1	1		Switch, 4PST, 0.25 A, 120 V, TH	12.6x12.6mm	15451	MEC Switches		
TP1, TP5, TP16, TP17, TP18, TP19, TP20, TP21, TP22, TP23, TP24, TP25, TP26, TP27	14		PCB Pin, Swage Mount, TH	PCB Pin(2505-2)	2505-2-00-44-00-00-07-0	Mill-Max		
TP3, TP4	2	Black	Test Point, Compact, Black, TH	Black Compact Testpoint	5006	Keystone		
TP6, TP8, TP11, TP12	4	White	Test Point, Miniature, White, TH	White Miniature Testpoint	5002	Keystone		
U1	1		LOW IQ, SINGLE BOOST, DUAL SYNCHRONOUS BUCK CONTROLLER, DAP0038B	DAP0038B	TPS43330AQDAPRQ1	Texas Instruments		Texas Instruments
U2	1		Automotive Power Management Unit (PMU) for Processor, ZWS0169A	ZWS0169A	O9039A360IWSRQ1	Texas Instruments		Texas Instruments
U3	1		5.5-V, 4-A, 16-mO On-Resistance Load Switch, DSG0008A	DSG0008A	TPS22965TDSGRQ1	Texas Instruments	TPS22965TDSGTQ1	Texas Instruments
U4	1		Single Output Automotive LDO, 3 A, 2.3 to 3.5 V Input, with DDR Termination, 10-pin SON (DRC), -40 to 125 degC, Green (RoHS & no Sb/Br)	DRC0010A	TPS51200QDRCRQ1	Texas Instruments	Equivalent	None
C2	0	220uF	CAP, AL, 220 uF, 63 V, +/- 20%, 0.26 ohm, SMD	SMT Radial H13	EEE-TK1J221AQ	Panasonic		
C5	0	560uF	CAP, AL, 560 uF, 50 V, +/- 20%, 0.05 ohm, TH	D12.5xL25mm	EEU-FC1H561	Panasonic		
C11	0	1000pF	CAP, CERM, 1000 pF, 25 V, +/- 5%, COG/NPO, 0603	0603	GRM1885C1E102JA01D	MuRata		
C23	0	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603	GRM188R71H102KA01D	MuRata		
FID1, FID2, FID3, FID4, FID5, FID6	0		Fiducial mark. There is nothing to buy or mount.	Fiducial	N/A	N/A		
R2, R9	0	10.0	RES, 10.0, 1%, 0.1 W, 0603	0603	CRCW060310R0FKEA	Vishay-Dale		
R21, R22	0	0	RES, 0, 5%, 0.063 W, 0402	0402	RC0402JR-070RL	Yageo America		

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.