

PMP4472 BOM

Quantity	Designator	Description	Footprint	Comment	MFR
1	C1	CAP;100nF,CER,275V(UL CSA 250V),10%,CBB,17x6x12,TH	CAPRR_15D24_17D0X6D0X12D0	NA	
1	C2	CAP;2.2nF,CER,1KV,5%,Z5U,9.5x7.0x9.5,TH	CAPRR_10D16_9D5X7D0X9D5	470pF	
1	C3	CAP;15uF,ALUM,400V,20%,ALUM,C10X16,DIP	CAPAE1000X1600_TH	15uF	
1	C4	CAP;220pF,CER,630V,5%,COG,1206,SMD	C1206	220pF	
1	C15	Capacitor, Ceramic	0603	0.1uF	
2	C6, C17	Capacitor, Ceramic	C0603	NA	
1	C8	CAP;1500uF,ALUM,6.3V,20%,ALUM,C10X12,DIP	CAPAE1000X1600_TH	1500uF	
1	C9, C13	Capacitor, Ceramic	C0603	100nF	
2	C10, C18	Capacitor, Ceramic	C1206	NA	
1	C11	Capacitor, Ceramic	C1210	10uF/35V	
1	C12	CAP;100nF,CER,275V(UL CSA 250V),10%,CBB,17x6x12,TH	CAPRR_15D24_17D0X6D0X12D0	100nF	
1	C21	Capacitor, Ceramic	0603	10pF/50V	
1	C50	Capacitor, Ceramic	0603	1uF/25V	
1	C23	Capacitor, Ceramic	0603	3.3nF	
1	C14	CAP;1nF,CER,2KV,10%,X7R,1812,SMD	C1812	NA	
1	C16	Capacitor, Ceramic	C0603	47nF/50V	
2	C19, C20	Capacitor, Ceramic	C1206	22uF	Murata
1	C28	Capacitor, Ceramic	C1206	22uf 6.3V	Murata
1	CON1	CONN HEADER;2x3P,5.08mm,VERT,DIP,LSF-SMT,TIN	CON_LSF-SMT-5D08-C3P6-180	5.08mm LSF-SMT-C3P6	
1	CON2	CONN HEADER;2x3P,3.81mm,VERT,DIP,LSF-SMT,TIN	CON_LSF-SMT-3D81-C3P6-180	3.81mm LSF-SMT-C3P6	
1	CON3	CONN HEADER;2x4P,2.00mm 7.4mm high,VERT,DIP,PIN,TIN	CON_2D00_2X4_TH	2.00mm 2x4 TH HEADER	
1	D1	BRIDGE;BRIDGE RECTIFIER,600V,1A,DFS,4PIN	DIODE_DFS	DF06S	
1	D2	DIODE;GLASS PASSIVATED,600V,1A,POWERDI123,SMD	POWERDI123	DFLR1600	
1	D3	DIODE;SCHOTTKY,40V,10A,POWERDI5,SMD	POWERDI5	PDS1040L	
1	D4	DIODE;HIGH VOLTAGE SWITCHING DIODE,250V,200mA,SOD323,SMD	SOD-323	BAS21HT1G	
2	D5, D7	DIODE TVS	SMB	NA	
1	D6	DIODE TVS	SMB	NA	
1	F1	FUSE;1A,250V,Time-Lag,8.5x4x8.0,TH	F5D08_8D5X4D0X8D0MM	1A	
1	G1	DIODES;gas discharge tube,SMD		NA	
1	L1	SMD Inductor WE-PD S 3.3uH 3.1A	Inductor 744778003	3.3uH	

1	L2	IND;L16D0X12D0X17D5MM,TH	L16D0X12D0X17D5MM	10mH	
1	L3	IND;2Kohm 10MHz,SRF4532-101Y,SMD,SHIELDED,FERRITE	L4D5X3D2X2D8MM	NA	
1	Q1	MOSFET N-CH 600V 2A IPAK	TO-251AB	STD2HNM60Z-1	
1	R1	RES;300Kohm,1/4W,5%,1206,SMD	R1206	300K	
2	R2, R10	RES;300ohm,1/4W,5%,1206,SMD	R1206	300R	
1	R3	RES;15ohm,1/8W,5%,0805,SMD	R0805	NA	
1	R4	RES;2.4Kohm,1/4W,5%,1206,SMD	R1206	2.4k	
1	R5	RES;22ohm,1/10W,5%,0603,SMD	0603	22R	
1	R6	RES;68Kohm,1/10W,1%,0603,SMD	0603	68K 1%	
1	R7	RES;1Kohm,1/8W,5%,0805,SMD	0805	1K	
2	R16, R17	RES;2.2ohm,1/8W,5%,0805,SMD	0805	2.2	
1	R8	RES;360Kohm,1/10W,1%,0603,SMD	0603	NA	
1	R9	RES;47Kohm,1/10W,1%,0603,SMD	0603	47K 1%	
1	R11	RES;10ohm,1/10W,1%,0603,SMD	0603	10	
1	R12	RES;510ohm,1/10W,1%,0603,SMD	0603	510	
1	R13	RES;470ohm,1/10W,1%,0603,SMD	0603	470	
2	R14, R21	RES;10Kohm,1/10W,1%,0603,SMD	0603	10K	
1	R18	RES;1Kohm,1/10W,1%,0603,SMD	0603	1K	
1	R20	RES;196Kohm,1/10W,1%,0603,SMD	0603	196K	
1	R23	RES;72.5Kohm,1/10W,1%,0603,SMD	0603	72.5K	
1	R24	RES;22Kohm,1/10W,1%,0603,SMD	0603	22K	
1	RV1	MOV;MOV-10D681K,31V MOV,MOV-10D,2PIN	MOV-10D	NA	
1	RV2	PTC;MZZ-390N,,PTC-T5MMD10MM,2PIN	PTC-T5MMD10MM	NA	
1	T1	FLYBACK TRANSFORMER;8W,3.3V,2.2A,EPC17,TH,SHIELDED	EPC17	TRNSFMR_EPC17	
1	U1	Buck Step Down Regulator with 4.5 to 18 V Input and 0.76 to 7 V Output, -4	DDA-8	TPS54228D	TI
1	U2	IC REG CTRLR FLYBK ISO 7SOIC	SOIC-7	UCC28740	TI
1	U4	4-Pin Phototransistor Optocoupler	OPTOCOUPLER	FOD817	
1	U5	IC VREF SHUNT ADJ SOT23	SOT-23	TL431AIDBZ	TI

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.