



6/16/2016 2:00:12 PM

**PMP20278 REV B Bill of Materials**

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C18	1	47pF	GRM1885C1H470JA01D	MuRata	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	603
C19	1	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	603
C23	1	330pF	GRM1885C1H331JA01D	MuRata	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0603	603
C12	1	3300pF	GRM188R71H332KA01D	MuRata	CAP, CERM, 3300 pF, 50 V, +/- 10%, X7R, 0603	603
C16, C20	2	0.047uF	GRM188R71E473KA01D	MuRata	CAP, CERM, 0.047 uF, 25 V, +/- 10%, X7R, 0603	603
C21	1	0.068uF	C1608X7R1H683K080AA	TDK	CAP, CERM, 0.068 uF, 50 V, +/- 10%, X7R, 0603	603
C15	1	100pF	GRM21A5C2E101JW01D	MuRata	CAP, CERM, 100 pF, 250 V, +/- 5%, C0G/NP0, 0805	805
C4, C6	2	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0805	805
C11, C17, C22	3	1uF	C0805C105K4RACTU	Kemet	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, 0805	805
C2, C3	2	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 uF, 100 V, +/- 10%, X7R, 1210	1210
C8, C9, C10	3	47uF	GRM32ER61A476KE20L	MuRata	CAP, CERM, 47 uF, 10 V, +/- 10%, X5R, 1210	1210
C1, C13	2	2200pF	C4532X7R3D222K130KA	TDK	CAP, CERM, 2200 pF, 2000 V, +/- 10%, X7R, 1812	1812
C14	1	10uF	EEE-FK1H100UR	Panasonic	CAP, AL, 10 uF, 50 V, +/- 20%, 1.52 ohm, SMD	SMT Radial C
C7	1	330uF	EEE-FK0J331P	Panasonic	CAP, AL, 330 uF, 6.3 V, +/- 20%, 0.26 ohm, SMD	SMT Radial E
C5	1	47uF	EEE-FK1J470P	Panasonic	CAP, AL, 47 uF, 63 V, +/- 20%, 0.65 ohm, SMD	SMT Radial F
D1	1		MURA120T3G	ON Semiconductor	Diode, Ultrafast, 200 V, 1 A, SMA	SMA
D2	1		MMSD4148T1G	ON Semiconductor	Diode, Switching, 100V, 0.2A, SOD-123	SOD-123
D3	1		STPS30L30CG-TR	STMicroelectronics	Diode, Schottky, 30 V, 30 A, DDPAK	DDPAK
D4	1		BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30V, 0.2A, SOT-23	SOT-23
D5	1		MMSD4148T1G	ON Semiconductor	Diode, Switching, 100 V, 0.2 A, SOD-123	SOD-123
J1, J2	2		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
L1	1	3.3uH	LPS3015-332MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 3.3 uH, 1.4 A, 0.13 ohm, SMD	LPS3015
L2	1	330nH	XAL5030-331MEB	Coilcraft	Inductor, Shielded, Composite, 330 nH, 19.2 A, 0.0032 ohm, SMD	5.3x31.x5.5mm
Q1	1		FDMS86252	Fairchild Semiconductor	MOSFET, N-CH, 150 V, 4.6 A, PQFN08A	PQFN08A
R8	1	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	603
R5	1	4.7	CRCW06034R70JNEA	Vishay-Dale	RES, 4.7, 5%, 0.1 W, 0603	603
R18	1	200	CRCW0603200RFKEA	Vishay-Dale	RES, 200, 1%, 0.1 W, 0603	603
R12	1	750	CRCW0603750RFKEA	Vishay-Dale	RES, 750, 1%, 0.1 W, 0603	603
R16	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	603
R7	1	1.50k	CRCW06031K50FKEA	Vishay-Dale	RES, 1.50 k, 1%, 0.1 W, 0603	603
R17	1	3.24k	CRCW06033K24FKEA	Vishay-Dale	RES, 3.24 k, 1%, 0.1 W, 0603	603
R14	1	4.99k	CRCW06034K99FKEA	Vishay-Dale	RES, 4.99 k, 1%, 0.1 W, 0603	603
R13, R15	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	603
R9	1	26.7k	CRCW060326K7FKEA	Vishay-Dale	RES, 26.7 k, 1%, 0.1 W, 0603	603
R10	1	60.4k	CRCW060360K4FKEA	Vishay-Dale	RES, 60.4 k, 1%, 0.1 W, 0603	603
R3	1	4.7	CRCW08054R70JNEA	Vishay-Dale	RES, 4.7, 5%, 0.125 W, 0805	805
R1	1	20k	CRCW080520K0JNEA	Vishay-Dale	RES, 20 k, 5%, 0.125 W, 0805	805
R2	1	51k	CRCW080551K0JNEA	Vishay-Dale	RES, 51 k, 5%, 0.125 W, 0805	805
R11	1	0.1	ERJ-8BWF100V	Panasonic	RES, 0.1, 1%, 0.5 W, 1206	1206
R4	1	10	ERJ-1TYJ100U	Panasonic	RES, 10, 5%, 1 W, 2512	2512
R6	1	75	CRCW251275R0JNEG	Vishay-Dale	RES, 75, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
T1	1		POE300F-50LB	Coilcraft	Transformer, 42 uH, SMT	21x20.57mm
U1	1		LM5021MM-1	Texas Instruments	AC-DC Current Mode PWM Controller, 8-pin MSOP	MUA08A
U2	1		HMHA2801A	Fairchild Semiconductor	Optocoupler, 3.75kV RMS, SMT	Mini Flat Package
U3	1		TLV431AIDBVR	Texas Instruments	LOW-VOLTAGE ADJUSTABLE PRECISION SHUNT REGULATOR, DBV0005A	DBV0005A

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2016, Texas Instruments Incorporated