

TIDA-01458 REV E1 Bill of Materials

Designator	Quantity	y Value	PartNumber	Manufacturer	Description	PackageReference
PCB1	1		TIDA-01458	Any	Printed Circuit Board	
C1	1	0.47uF	GRM188R61E474KA12D	MuRata	CAP, CERM, 0.47 μF, 25 V, +/- 10%, X5R, 0603	0603
C2, C26	2	470uF	35ZL470MEFC10X20	Rubycon	CAP, AL, 470 µF, 35 V, +/- 20%, TH	TH, 2-Leads, Body 10x20mm, Pin Spacing 5mm
C3	1	2.2uF	C1608X5R1V225K080AC	TDK	CAP, CERM, 2.2 µF, 35 V, +/- 10%, X5R, 0603	0603
C4, C5, C19, C21	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210
C6, C7	2	0.47uF	GRM21BR71H474KA88L	MuRata	CAP, CERM, 0.47 µF, 50 V, +/- 10%, X7R, 0805	0805
C8, C9, C10, C33	4	22uF	GRM32ER71E226KE15L	MuRata	CAP, CERM, 22 μF, 25 V, +/- 10%, X7R, 1210	1210
C11, C38, C46, C48, C53, C59, C60, C61	8	1uF	C1608X5R1H105K080AB	TDK	CAP, CERM, 1 μF, 50 V, +/- 10%, X5R, 0603	0603
C12, C14, C15, C22, C25, C27, C36, C42, C44, C52, C54, C55		0.1uF	C1608X7R1H104K080AA	TDK	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0603	0603
C13		4.7pF	08055A4R7CAT2A	AVX	CAP, CERM, 4.7 pF, 50 V, +/- 5%, C0G/NP0, 0805	0805
C16		0.022uF	08055C223KAT2A	AVX	CAP, CERM, 0.022 μF, 50 V, +/- 10%, X7R, 0805	0805
C17, C18, C20, C64	4	10uF	C3216X5R1H106K160AB	TDK	CAP, CERM, 10 μF, 50 V,+/- 10%, X5R, 1206	1206
C23, C24		4.7uF	GRM32ER71H475KA88L	MuRata	CAP, CERM, 4.7 µF, 50 V, +/- 10%, X7R, 1210	1210
C29, C30, C63	3	1uF	GRM21BR71E105KA99L	MuRata	CAP, CERM, 1 μF, 25 V, +/- 10%, X7R, 0805	0805
C31, C35, C41, C50, C57, C62	6	47uF	C3216X5R1E476M160AC	TDK	CAP, CERM, 47 µF, 25 V, +/- 20%, X5R, 1206_190	1206_190
C32	1	0.027uF	GRM188R71E273KA01D	MuRata	CAP, CERM, 0.027 μF, 25 V, +/- 10%, X7R, 0603	0603
C34, C37, C39, C40, C43, C45, C47, C49, C51, C56, C58	11	10uF	C2012X5R1V106K085AC	TDK	CAP, CERM, 10 μF, 35 V, +/- 10%, X5R, 0805	0805
C65		22pF	06035A220JAT2A	AVX	CAP, CERM, 22 pF, 50 V,+/- 5%, C0G/NP0, 0603	0603
D1, D3, D4	3	3.3V	1SMB5913BT3G	ON Semiconductor	Diode, Zener, 3.3 V, 550 mW, SMB	SMB
D2		60V	PDS760-13	Diodes Inc.	Diode, Schottky, 60 V, 7 A, PowerDI5	PowerDI5
D5, D6, D7, D8		60V	B260A-13-F	Diodes Inc.	Diode, Schottky, 60 V, 2 A, SMA	SMA
D9	1	100V	1N4148W-TP		ntDiode, Switching, 100 V, 0.15 A, SOD-123	SOD-123
H1, H2, H5, H6	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H7, H8, H13, H14	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1			TSW-104-07-G-S	Samtec	Header, 100mil, 4x1, Gold, TH	4x1 Header
J2, J3	2		1792876	Phoenix Contact	Terminal Block, 5mm, 3x1, R/A, TH	Terminal Block, 5mm, 3x1, R/A, TH
J4	1		1715721	Phoenix Contact	Terminal Block, 5.08 mm, 2x1, TH	2POS Terminal Block
J5, J6, J7, J8	4		901-144-8RFX	Amphenol RF		SMA Straight Jack, TH
L1	1	10uH	XAL7030-103MEB	Coilcraft	Inductor, Shielded, Composite, 10 µH, 5.3 A, 0.057 ohm, SMD	XAL7030
L2	1	33uH	7443551331	Wurth Elektronik eiSos	Inductor, Shielded Drum Core, WE-Perm, 33uH, 5.5A, 0.0305 ohm, SMD	WE-HCA1
L3, L4	2	2.2uH	XAL7030-222MEB	Coilcraft	Inductor, Shielded, Composite, 2.2uH, 12.9A, 0.0137 ohm, SMD	XAL7030

Designator	Quantity		PartNumber	Manufacturer	Description	PackageReference
Q1, Q3		45 V	BC847CLT1G	ON Semiconductor	Transistor, NPN, 45 V, 0.1 A, SOT-23	SOT-23
Q2	1	100V	BSS123	Fairchild Semiconductor	MOSFET, N-CH, 100 V, 0.17 A, SOT-23	SOT-23
Q4, Q5, Q6	3	45 V	BC857C-7-F	Diodes Inc.	Transistor, PNP, 45 V, 0.1 A, SOT-23	SOT-23
R1	1	240k	CRCW0805240KJNEA	Vishay-Dale	RES, 240 k, 5%, 0.125 W, 0805	0805
R2, R31, R59,	7	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R60, R61, R62,				-		
R63						
R3, R67, R68	3	47k	CRCW080547K0JNEA	Vishay-Dale	RES, 47 k, 5%, 0.125 W, 0805	0805
R4	1	68k	CRCW060368K0JNEA	Vishay-Dale	RES, 68 k, 5%, 0.1 W, 0603	0603
R5	1	470	CRCW0603470RJNEA	Vishay-Dale	RES, 470, 5%, 0.1 W, 0603	0603
R6, R65	2	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R7	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
R8, R10, R14	3	4.70k	RC0603FR-074K7L	Yageo America	RES, 4.70 k, 1%, 0.1 W, 0603	0603
R9	1	20k	CRCW060320K0JNEA	Vishay-Dale	RES, 20 k, 5%, 0.1 W, 0603	0603
R11, R33, R36,	9	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R37, R39, R42,						
R47, R48, R57						
R12, R49, R66	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R13	1	2.0k	CRCW08052K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.125 W, 0805	0805
R15, R28	2	3.3k	CRCW06033K30JNEA	Vishay-Dale	RES, 3.3 k, 5%, 0.1 W, 0603	0603
R16	1	2.7k	CRCW06032K70JNEA	Vishay-Dale	RES, 2.7 k, 5%, 0.1 W, 0603	0603
R17, R20	2	10K	TC33X-2-103E	Bourns	TRIMMER 10K OHM 0.1W	3.8x3.6mm
R18, R50, R53	3	180k	CRCW0603180KJNEA	Vishay-Dale	RES, 180 k, 5%, 0.1 W, 0603	0603
R19	1	33k	CRCW060333K0JNEA	Vishay-Dale	RES, 33 k, 5%, 0.1 W, 0603	0603
R21		2.2k	CRCW06032K20JNEA	Vishay-Dale	RES, 2.2 k, 5%, 0.1 W, 0603	0603
R22	1	3.6k	CRCW06033K60JNEA	Vishay-Dale	RES, 3.6 k, 5%, 0.1 W, 0603	0603
R23, R26, R32,	10	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R35, R38, R41,						
R44, R45, R46,						
R55						
R24, R56	2	22k	CRCW060322K0JNEA	Vishay-Dale	RES, 22 k, 5%, 0.1 W, 0603	0603
R25	1	59.0k	CRCW060359K0FKEA	Vishay-Dale	RES, 59.0 k, 1%, 0.1 W, 0603	0603
R27	1	442k	CRCW0603442KFKEA	Vishay-Dale	RES, 442 k, 1%, 0.1 W, 0603	0603
R29	1	470	CRCW0805470RJNEA	Vishay-Dale	RES, 470, 5%, 0.125 W, 0805	0805
R30	1	220	CRCW0603220RJNEA	Vishay-Dale	RES, 220, 5%, 0.1 W, 0603	0603
R34, R40	2	330	CRCW0603330RJNEA	Vishay-Dale	RES, 330, 5%, 0.1 W, 0603	0603
R43, R52	2	1.2Meg	CRCW06031M20JNEA	Vishay-Dale	RES, 1.2 M, 5%, 0.1 W, 0603	0603
R51, R54	2	15.0k	CRCW060315K0FKEA	Vishay-Dale	RES, 15.0 k, 1%, 0.1 W, 0603	0603
R58	1	93.1k	CRCW060393K1FKEA	Vishay-Dale	RES, 93.1 k, 1%, 0.1 W, 0603	0603
R64	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
U1	1		LM73605RNPR	Texas Instruments		RNP0030A
					(WQFN-30)	
U2, U7, U9	3		TLV2171IDR	Texas Instruments	36V, Low Power, RRO, General Purpose Operational Amplifier, D0008A	D0008A
	-				(SOIC-8)	
U3	1		TL431ACDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, 0 to 70	DBZ0003A
					degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	
U4	1		LMR14050SDDAR	Texas Instruments	40V, 5A SIMPLE SWITCHER, 2.2MHz Step-Down Regulator with 40uA IQ,	DDA0008F
					DDA0008E (SOIC-8)	
U5, U6	2		TPS7A4701RGWR	Texas Instruments		RGW0020A
00,00	-				20)	
U8, U10	2		TPS7A3301RGWR	Texas Instruments	Single Output High PSRR LDO, 1 A, Adjustable -1.18 to -33 V Output, -3 to	RGW0020A
00, 010	2				-36 V Input, with Ultra-Low Noise, 20-pin VQFN (RGW), -40 to 125 degC,	1.0110020/1
					Green (RoHS & no Sb/Br)	

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated