1/24/2017					TEXAS	3
			PMP20676 REV B Bill of Materials INSTRUMENTS			
Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C23	1	47pF	GRM1885C1H470JA01D	MuRata	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	603
C20, C21	2	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, COG/NP0, 0603	603
C14	1	100pF	GRM1885C2A101JA01D	MuRata	CAP, CERM, 100 pF, 100 V, +/- 5%, COG/NP0, 0603	603
C15	1	3300pF	GRM188R72A332KA01D	MuRata	CAP, CERM, 3300 pF, 100 V, +/- 10%, X7R, 0603	603
C24	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 μF, 50 V, +/- 10%, X7R, 0603	603
C22. C26	2	0.022ui	C1608X7R1H473K080AA	TDK	CAP, CERM, 0.047 μF, 50 V, +/- 10%, X7R, 0603	603
C3, C8	2	0.047 di 0.22uF	C2012X7R1H224K125AA	TDK	CAP, CERM, 0.22 μF, 50 V, +/- 10%, X7R, 0805	805
C13, C16, C18, C19, C25	5	1uF	C2012X7R1H105K085AC	TDK	CAP, CERM, 1 μF, 50 V, +/- 10%, X7R, 0805	805
C4, C5, C6, C7	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 μF, 50 V, +/- 10%, X7R, 1210	1210
C10, C11, C12	3	22uF	C3225X7R1C226K250AC	TDK	CAP, CERM, 10 μF, 50 V, +/- 10%, X/R, 1210 CAP, CERM, 22 μF, 16 V, +/- 10%, X/R, 1210	1210
C1, C17	2	2200pF	C4532X7R3D222K130KA	TDK	CAP, CERM, 220 pF, 10 V, 4/- 10 %, X/R, 1210	1812
		180uF	16SVP180MX		CAP, Aluminum Polymer, 180 µF, 16 V, +/- 20%, 0.03 ohm, 10x10.3 SMD	
C9	1	180ur	102 A LI 1801AIX	Panasonic		
C2	1	100uF	EEE-FK1H101P	Panasonic	CAP, AL, 100 μF, 50 V, +/- 20%, 0.34 ohm, AEC-Q200 Grade 2, SMD	SMT Radial F
D1	1		STPS30L60CG-TR	STMicroelectronics	Diode, Schottky, 60 V, 15 A, DDPAK	DDPAK
02	1		ES3BB-13-F	Diodes Inc.	Diode, Superfast Rectifier, 100V, 3A, SMB	SMB
D3, D4	2		MMSD4148T1G	ON Semiconductor	Diode, Switching, 100V, 0.2A, SOD-123	SOD-123
05	1		BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
J1, J2	2		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
_1	1	3.3uH	XAL5030-332MEB	Coilcraft	Inductor, Shielded, Composite, 3.3 µH, 8.1 A, 0.02 ohm, SMD	5.3x31.x5.5mm
2	1	160nH	XAL5030-161MEB	Coilcraft	Inductor, Shielded, Composite, 160 nH, 22.2 A, 0.00215 ohm, SMD	5.3x31.x5.5mm
Q1	1		CSD19534Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 10 A, DQJ0008A (VSONP-8)	DQJ0008A
R12	1	0	ERJ-3GEY0R00V	Panasonic	RES, 0 ohm, 5%, 0.1W, 0603	603
R5, R6	2	4.7	CRCW06034R70JNEA	Vishay-Dale	RES, 4.7 ohm, 5%, 0.1W, 0603	603
R13, R19	2	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00k ohm, 1%, 0.1W, 0603	603
R21	1	1.15k	CRCW06031K15FKEA	Vishay-Dale	RES, 1.15 k, 1%, 0.1 W, 0603	603
R14	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00k ohm, 1%, 0.1W, 0603	603
R22	1	5.23k	CRCW06035K23FKEA	Vishay-Dale	RES, 5.23 k, 1%, 0.1 W, 0603	603
R16	1	5.49k	CRCW06035K49FKEA	Vishay-Dale	RES, 5.49 k, 1%, 0.1 W, 0603	603
R15, R20	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	603
R18	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	603
R11	1	60.4k	CRCW060360K4FKEA	Vishay-Dale	RES, 60.4 k, 1%, 0.1 W, 0603	603
R17	1	68.1k	CRCW060368K1FKEA	Vishay-Dale	RES, 68.1 k, 1%, 0.1 W, 0603	603
R10	1	69.8k	CRCW060369K8FKEA	Vishay-Dale	RES, 69.8 k, 1%, 0.1 W, 0603	603
R7	0	DNP	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	603
₹8	1	20	CRCW080520R0JNEA	Vishay-Dale	RES, 20 ohm, 5%, 0.125W, 0805	805
R1	1	10k	CRCW120610K0JNEA	Vishay-Dale	RES, 10k ohm, 5%, 0.25W, 1206	1206
R3	1	75	CRCW201075R0JNEF	Vishay-Dale	RES, 75, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R9	1	0.025	CSRN2512FK25L0	Stackpole Electronics Inc	RES, 0.025, 1%, 2 W, 2512	2512
R2, R4	2	15	CRCW251215R0JNEG	Vishay-Dale	RES, 15, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
<u>τ2, ττ<del>4</del></u> Γ1	1	1.0	TG-UT38741S	Universal Microelectronics	Transformer, 15 uH, SMT	27.5x28mm
TP1, TP2	2	<del> </del>	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
						Testpoint
TP3, TP4	2		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
J2	1		FOD817AS	Fairchild Semiconductor	Optocoupler, 5 kV, 80-160% CTR, SMT	DIP-4L Gullwing
J1	1		LM5022MM/NOPB	Texas Instruments	60V Low Side Controller for Boost and SEPIC, 10-pin MSOP, Pb-Free	MUB10A
U3	1		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated