



Efficiency




Ripple and Noise

Output Ripple (C11)
20mV/div, 2usec/div
Measured 40mV pk-pk:




Input Ripple (C11)
20mV/div, 2usec/div
Measured 31.3mV pk-pk:




Dynamic Loading

Load Step
2A to 4A step load, 400mA/usec slew rate, 2A/div, 200mV/div, 200usec/div
Measured 553mVpp:




Turn On Response


5V output, 4A load
1V/div, 1msec/div:



5V output, 0A load
1V/div, 1msec/div:




Turn on delay, 4A load
Top: 5V output, 2V/div
Bottom: Vin, 20V/div
50msec/div:




Waveforms

VDS Q1, 57V Input, 4A Load
20V/div, 1usec/div
Measured 131.3Vpp:




VAK D3, 57V Input, 4A Load
5V/div, 1usec/div
Measured 20.3Vpp




Stability


Loop response of the converter with a 48V input and 4A load
 BW=6Khz PM=65 degrees GM=16dB



Loop response of the converter with a 48V input and 2A load
 BW=4.3Khz PM=60 degrees GM=22dB




Loop response of the converter with a 48V input and 400mA load
 BW=2.2Khz PM=46 degrees GM=30dB



Thermal:

Thermal measurements taken with 48V input and 4A load, no air flow.

Top:



Bottom:






Photo:

Top:



Bottom:



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated