

TIDA-00711 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB	1		TIDA-00711	Any	Printed Circuit Board	
C1, C4, C5	3	4.7uF	GRM32ER71K475ME14L	MuRata	4.7uF ±20% 80V Ceramic Capacitor X7R 1210 (3225 Metric)	1210
C3	1	33uF	UPM2A330MPD1TD	Nichicon	33uF 100V Aluminum Capacitors Radial, Can 3000 Hrs @ 105°C	D8xL15mm
C6, C11	2	100uF	EEU-FM1E101	Panasonic	CAP, AL, 100 uF, 25 V, +/- 20%, 0.13 ohm, TH	6.3x11.2mm
C7, C8, C12, C18	4	22uF	GRM32ER61E226KE15L	MuRata	CAP, CERM, 22 uF, 25 V, +/- 10%, X5R, 1210	1210
C9	1	4700pF	GRM21AR72E472KW01D	MuRata	CAP, CERM, 4700 pF, 250 V, +/- 10%, X7R, 0805	0805
C10	1	47uF	ESH476M025AC3AA	Kemet	47uF 25V Aluminum Capacitors Radial, Can 2000 Hrs @ 105°C	RCAP, 5x5mm
C13	1	2.2pF	06035A2R2CAT2A	AVX	CAP, CERM, 2.2 pF, 50 V, +/- 11%, C0G/NP0, 0603	0603
C14	1	0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 uF, 100 V, +/- 5%, X7R, 0603	0603
C15, C19	2	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
C16	1	100pF	GRM1885C2A101JA01D	MuRata	CAP, CERM, 100 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603
C17	1	3600pF	GRM1885C1H362JA01D	MuRata	CAP, CERM, 3600 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
D1	1	150V	FSV20150V	Fairchild Semiconductor	Diode Schottky 150V 20A Surface Mount TO-277-3	TO-277A
D2	1	150V	FSV12150V	Fairchild Semiconductor	Diode Schottky 150V 12A Surface Mount TO-277-3	TO-277A
D3	1	100V	B1100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 1 A, SMA	SMA
D4	1	100V	1N4148W-7-F	Diodes Inc.	Diode, Ultrafast, 100 V, 0.15 A, SOD-123	SOD-123
D5	1	15V	MMSZ5245B-TP	Micro Commercial Co	Zener Diode 15V 500mW ±5% Surface Mount SOD-123	SOD-123
D6	1	1.8V	MMSZ4678-TP	Micro Commercial Co	Zener Diode 1.8V 500mW ±5% Surface Mount SOD-123	SOD-123
D7	1	5.1V	MMSZ5231B-7-F	Diodes Incorporated	Zener Diode 5.1V 500mW ±5% Surface Mount SOD-123	SOD-123
J1, J2, J3	3		OSTVN02A150	On-Shore Technology	Terminal Block, 2.54mm, 2x1, Brass, TH	Terminal Block, 2.54mm, 2-pole, Brass, TH
L1	1	2.2uH	RLB0912-2R2ML	MuRata Toko	Inductor, Shielded, 2.2 uH, 2.6 A, 0.07 ohm, SMD	1008
L2	1	1uH	CIG22E1R0MNE	Samsung	Inductor, Multilayer, 1 uH, 2.2 A, 0.048 ohm, SMD	SMD, Body 2.5x2mm, Height 1.2mm
Q1	1	100V	CSD19531Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 16 A, SON 5x6mm	SON 5x6mm
Q3	1	65 V	BC846BLT1G	ON Semiconductor	Transistor, NPN, 65 V, 0.1 A, SOT-23	SOT-23
R1	1	10.0k	CRM2512-JW-103ELF	Bourns Inc	RES SMD 10K OHM 5% 2W 2512	2512
R2	1	22.1k	CRCW060322K1FKEA	Vishay-Dale	RES, 22.1 k, 1%, 0.1 W, 0603	0603
R3	1	133k	CRCW0603133KfKEA	Vishay-Dale	RES, 133 k, 1%, 0.1 W, 0603	0603
R4	1	470	RC0603FR-07470RL	Yageo America	RES, 470, 1%, 0.1 W, 0603	0603
R5, R10	2	10.0k	CRCW060310K0fKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R6	1	21.0k	RC0603FR-0721KL	Yageo America	RES, 21.0 k, 1%, 0.1 W, 0603	0603
R7	1	20.0k	CRCW060320K0fKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R8	1	86.6k	RC0603FR-0786K6L	Yageo America	RES, 86.6 k, 1%, 0.1 W, 0603	0603
R9	1	0.015	CSRN2512FK15L0	Stackpole Electronics Inc	RES, 0.015, 1%, 2 W, 2512	2512
R11	1	4.99	CRCW06034R99fKEA	Vishay-Dale	RES, 4.99, 1%, 0.1 W, 0603	0603
R20	1	1.82k	CRCW06031K82fKEA	Vishay-Dale	RES, 1.82 k, 1%, 0.1 W, 0603	0603
R21	1	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
T1	1	15uH	750343373	Würth Electronics	Transformer, 15uH, TH	
U1	1		LM5020MM-1/NOPB	Texas Instruments	100V Current Mode PWM Controller, 10-pin MSOP, Pb-Free	MUB10A
C2	0	4.7uF	GRM32ER71K475ME14L	MuRata	4.7uF ±20% 80V Ceramic Capacitor X7R 1210 (3225 Metric)	1210
FID1, FID2	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
R12	0	475	RNCP1206FTD475R	Stackpole Electronics Inc.	RES SMD 475 OHM 1% 1/2W 1206	1206

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated