Filename: PMP20490A_BOM.xls
Variant: 001
Generated: 9/16/2016 10:09:37 AM

updated: December 23, 2016

| PCB200 | Quantity | Value | Description Printed Circuit Board | PackageReference | PartNumber build on PCB | Manufacturer Any | Alternate PartNumber | Alternate Manufacturer |
|-----------------------|---------------|----------------|--|------------------------------|---------------------------------------|-------------------------------|----------------------|------------------------|
| !FCB200 | | | Filited Circuit Board | | PMP20292 rev A | Ally | - | |
| BodeTP, | 2 | | Test Point, Miniature, White, TH | White Miniature | 5002 | Keystone | | |
| PGOOD C1, C3, | 4 | 1uF | CAP, CERM, 1 μF, 25 V, +/- 10%, X5R, 0603 | Testpoint 0603 | C1608X5R1E105K080A | TDK | | |
| C12, C14 | 7 | Tur | CAF, CERNI, 1 µF, 25 V, 47-10 %, ASK, 0003 | 0003 | C 1000X3K 1E 103K000A | TDK | | |
| C2, C13 | 2 | 1000pF | CAP, CERM, 1000 pF, 25 V, +/- 10%, X5R, 0402 | 0402 | GRM155R61E102KA01 | MuRata | | |
| C4, C5, C6, | 8 | 22uF | CAP, CERM, 22 µF, 25 V, +/- 10%, X7R, 1210 | 1210 | D GRM32ER71E226KE15 | MuPata | | |
| C7, C8, C9, | | 2201 | ΟΛΙ , ΟΕΚΙΝΙ, 22 μΙ , 25 V, 47- 1076, ΑΤΚ, 1210 | 1210 | L | wartata | | |
| C10, C11 | | | | | | | | |
| C15, C16 | 2 | 0.1uF | CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0402 | 0402 | GRM155R71C104KA88 | MuRata | | |
| C17, C20 | 2 | 1500pF | CAP, CERM, 1500 pF, 50 V, +/- 10%, X7R, 0402 | 0402 | GRM155R71H152KA01 | MuRata | | |
| | | | | | D | | | |
| C18, C19 C21 | <u>2</u> 1 | 1000pF 10pF | CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, 0805 CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0402 | 0805 0402 | C0805C102K1RACTU GRM1555C1H100JA01 | Kemet MuRata | | |
| 021 | | TOP. | 67 ii , 621 iiii, 16 pi , 66 t , 17 676, 6667 ii 6, 6162 | 0.02 | D | | | |
| C22, C24, | 4 | 4.7uF | CAP, CERM, 4.7uF, 16V, +/-10%, X5R, 0603 | 0603 | GRM188R61C475KAAJ | MuRata | | |
| C25, C26 C23, C27 | 2 | 0.1uF | CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0402 | 0402 | GRM155R71C104KA88 | MuRata | | |
| | | | | | D | | | |
| C29, C30, | 4 | 470uF | CAP, Aluminum Polymer, 470 µF, 2.5 V, +/- 20%, 4.5 | 7.3x1.8x4.3mm | EEFSX0E471E4 | Panasonic | | |
| C31, C32 C33, C35, | 4 | 100uF | ohm, 7.3x1.8x4.3mm SMD CAP, CERM, 100 μF, 6.3 V, +/- 20%, X5R, 1210 | 1210 | GRM32ER60J107ME20 | MuRata | | |
| C508, C509 | | | • | | L | | | |
| C34, C510, | 0 | DNP | CAP, CERM, 100 μF, 6.3 V, +/- 20%, X5R, 1210 | 1210 | GRM32ER60J107ME20 | MuRata | | |
| C515 C36 | 1 | 22pF | CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0402 | 0402 | GRM1555C1H220JA01 | MuRata | | |
| | | • | • | | D | | | |
| C500, C501, | 4 | 0.1uF | CAP, CERM, 0.1 μF, 16 V, +/- 10%, X5R, 0402 | 0402 | GRM155R61C104KA88 | MuRata | | |
| C501, C502, C503 | | <u> </u> | | | | | <u> </u> | |
| C506 | 1 | 1uF | CAP, CERM, 1 µF, 10 V, +/- 10%, X5R, 0402 | 0402 | GRM155R61A105KE15 | MuRata | | |
| C507, C540 | 2 | 0.1uF | CAP, CERM, 0.1 µF, 25 V, +/- 10%, X5R, 0402 | 0402 | D GRM155R61E104KA87 | MuRata | | |
| 0307, 0340 | | 0.141 | ΟΛΙ , ΟΕΚΙΝΙ, Ο. Ι μΙ , 25 V, +/- 1076, ΧΟΙΚ, 0402 | 0402 | D | Iwurkata | | |
| C511, C512 | 2 | 270uF | CAP, Aluminum Polymer, 270 µF, 16 V, +/- 20%, 0.01 | 8.0x9.0mm | 16SEPC270MX | Panasonic | | |
| D500 | 1 | 30V | ohm, TH Diode, Schottky, 30 V, 0.2 A, SOD-323 | SOD-323 | BAT54WS-7-F | Diodes Inc. | | |
| D501 | 1 | Red | LED, Red, SMD | LED_0805 | LTST-C170KRKT | Lite-On | | |
| D502, D503 | 2 | 30V | Diode, Schottky, 30 V, 0.5 A, SOD-123 | SOD-123 | MBR0530T1G | ON Semiconductor | | |
| exc_rtn, GndTP, | 4 | Black | Test Point, Miniature, Black, TH | Black Miniature Testpoint | 5001 | Keystone | | |
| TP502, | | | | Темропп | | | | |
| TP504 | _ | | T . D M D TU | D 1145 : 4 | 5000 | Mariatan a | | |
| ext_clk, TP501, | 5 | Red | Test Point, Miniature, Red, TH | Red Miniature Testpoint | 5000 | Keystone | | |
| TP503, | | | | Тоскроин | | | | |
| TP506, | | | | | | | | |
| VoutTP H200, | 4 | | Machine Screw, Round, #4-40 x 1/4, Nylon, Philips | Screw | NY PMS 440 0025 PH | B&F Fastener Supply | | |
| H201, | | | panhead | 00.011 | | | | |
| H202, H203 | | | Over deff. Here O.F.W. #4.40 No. | Otera deff | 40000 | Mariatan a | | |
| H204, H205, | 4 | | Standoff, Hex, 0.5"L #4-40 Nylon | Standoff | 1902C | Keystone | - | - |
| H206, H207 | | | | | | | | |
| int_clk_EN, | 2 | | Header, 100mil, 2x1, Gold, TH | Sullins 100mil, 1x2, | PBC02SAAN | Sullins Connector Solutions | | |
| int_clk_sel | | | | 230 mil above insulator | | | | |
| J1 | 1 | | Header (shrouded), 100mil, 5x2, Gold, TH | 5x2 Shrouded header | 5103308-1 | TE Connectivity | | |
| - 10 | 1 | | Handar 400mil Old Tin Til | Header, 2 PIN. | DECOCCAAN | Sullins Connector Solutions | | |
| J2 | | | Header, 100mil, 2x1, Tin, TH | 100mil, Tin | PEC02SAAN | Sullins Connector Solutions | | |
| J502, J541 | 2 | | Connector, Ultra-Mini Coaxial, SMD | Ultra small CO-AX | U.FL-R-SMT-1 | Hirose Electric Co. Ltd. | | |
| J503. J506 | 2 | 90A | Terminal 90A Lug | SMD CB70-14-CY | CB70-14-CY | Panduit | | |
| J503, J506 J507 | 1 | JUA | Terminal Block, 5.08 mm, 4x1, Brass, TH | 4x1 5.08 mm | ED120/4DS | On-Shore Technology | | |
| | | | | Terminal Block | | 0, | | |
| J510 J540 | 1 | | Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH Header, 100mil, 2x1, Gold, TH | 7.0x8.2x6.5mm 2x1 Header | ED555/2DS TSW-102-07-G-S | On-Shore Technology Samtec | | |
| L1, L2 | 2 | 330nH | Inductor, Ferrite, 330 nH, 32.8 A, 0.00033 ohm, SMD | SMD, 2-Leads, Body | VLB10090HT-R33K-B2 | TDK | S16100010 | Wurth Electronics |
| | | 05)/ | MODEL MONEY 445 : 5 12 1221 | 10.2x10mm | 000404005-5 | Taura Instaura | | Maria |
| Q500 | 1 | 25V | MOSFET, N-CH, 25 V, 113 A, DualCool SON 5x6mm | DualCool SON 5x6mm | CSD16408Q5C | Texas Instruments | 1 | None |
| Q540 | 1 | 25V | MOSFET, N-CH, 25 V, 100 A, SON 5x6mm | SON 5x6mm | CSD16325Q5 | Texas Instruments | | None |
| R1, R2, | 3 | 1.0 | RES, 1.0, 5%, 0.063 W, 0402 | 0402 | CRCW04021R00JNED | Vishay-Dale | | |
| R540 R3, R4, | 3 | 0 | RES, 0, 5%, 0.063 W, 0402 | 0402 | CRCW04020000Z0ED | Vishay-Dale | | |
| R18 | | | | | | - | | |
| R5 | 1 | 1.50k | RES, 1.50 k, 1%, 0.063 W, 0402 | 0402 | CRCW04021K50FKED | Vishay-Dale | | |
| R6, R8, R13, R15, | 10 | 10.0k | RES, 10.0 k, 1%, 0.063 W, 0402 | 0402 | CRCW040210K0FKED | Vishay-Dale | | |
| R23, R24, | | | | | | | | |
| R28, R29, | | | | | | | | |
| R502, R541 R7, R27 | 2 | 51 | RES, 51, 5%, 0.063 W, 0402 | 0402 | CRCW040251R0JNED | Vishay-Dale | | |
| R9 | 1 | 20.0k | RES, 20.0 k, 1%, 0.063 W, 0402 | 0402 | CRCW040220K0FKED | Vishay-Dale | | |
| R10, R11 | 2 | 1.0 | RES, 1.0, 5%, 0.25 W, 1206 | 1206 | CRCW12061R00JNEA | Vishay-Dale | | |
| R14 R12, R16, | 0 | 100k DNP | RES, 100 k, 1%, 0.063 W, 0402 DNP | 0402 0402 | CRCW0402100KFKED DNP | Vishay-Dale Vishay-Dale | | |
| R17 | | | | | | - | | |
| R19 | 1 | 187k | RES, 187 k, 1%, 0.063 W, 0402 | 0402 | CRCW0402187KFKED | Vishay-Dale | | |
| R20 R21, R22 | 2 | 121k 47.5k | RES, 121 k, 1%, 0.063 W, 0402 RES, 47.5 k, 1%, 0.063 W, 0402 | 0402 0402 | CRCW0402121KFKED CRCW040247K5FKED | Vishay-Dale Vishay-Dale | | |
| R25, R26 | 2 | 51.1k | RES, 51.1 k, 1%, 0.063 W, 0402 | 0402 | CRCW040251K1FKED | Vishay-Dale | | |
| R500, R503 | 2 | 8.06k | RES, 8.06 k, 1%, 0.063 W, 0402 | 0402 | CRCW04028K06FKED | Vishay-Dale | | |
| R501 R504 | 1 | 200k 330 | RES, 200 k, 1%, 0.063 W, 0402 RES, 330, 5%, 0.063 W, 0402 | 0402 0402 | CRCW0402200KFKED CRCW0402330RJNED | Vishay-Dale Vishay-Dale | | |
| | | | | | | | | |

| Designator | Quantity | Value | Description | PackageReference | PartNumber | Manufacturer | Alternate PartNumber | Alternate Manufacturer |
|------------|----------|-------|---|---------------------|------------------|---------------------------|----------------------|------------------------|
| R505, | 11 | 0.3 | RES, 0.3, 1%, 2 W, 2512 | 2512 | CSRN2512FKR300 | Stackpole Electronics Inc | | |
| R506, | | | | | | | | |
| R507, | | | | | | | | |
| R508, | | | | | | | | |
| R509, | | | | | | | | |
| R510, | | | | | | | | |
| R511, | | | | | | | | |
| R512, | | | | | | | | |
| R513, | | | | | | | | |
| R514, R515 | | | | | | | | |
| R527, R543 | 2 | 49.9 | RES, 49.9, 1%, 0.063 W, 0402 | 0402 | CRCW040249R9FKED | Vishay-Dale | | |
| R528 | 1 | 75.0 | RES, 75.0, 1%, 0.1 W, 0603 | 0603 | CRCW060375R0FKEA | Vishay-Dale | | |
| R529 | 1 | 249 | RES, 249, 1%, 0.1 W, 0603 | 0603 | | Vishay-Dale | | |
| R542 | 1 | 0.01 | RES, 0.01, 1%, 1 W, 2512 | 2512 | | Panasonic | | |
| TP500, | 2 | | Test Point, Compact, SMT | Testpoint_Keystone_ | 5016 | Keystone | | |
| TP505 | | | | Compact | | | | |
| U1, U2 | 2 | | 4.5V-18V, 35A PMBUS STACKABLE SYNCHRONOUS | RVF0040A | TPS546C23RVFR | Texas Instruments | TPS546C23RVFT | Texas Instruments |
| | | | BUCK CONVERTERS, RVF0040A | | | | | |
| U501 | 1 | | | D0008A | TLC555CD | Texas Instruments | | Texas Instruments |
| U502 | 1 | | DUAL 4-A PEAK HIGH SPEED LOW- SIDE POWER | D0008A | UCC27324D | Texas Instruments | | Texas Instruments |
| | | | MOSFET DRIVERS, D0008A | | | | | |

Notes:

All parts may be substituted with equivalents, except for L1, L2, U1, U2, Q500, Q540, U501, U502. L1 & L2 show two sources, both have been tested with. See Test report.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated