Filename:
 ProCBAB.tmp

 Variant:
 001

 Generated:
 8/1/2017 7:18:53 PM

 TID #:
 PMP40281

PMP40281 REV 1.0 Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	2.2uF	C2012X7R1V225K085AC	TDK	CAP, CERM, 2.2 μF, 35 V, +/- 10%, X7R, 0805	0805
2	C2	1	4.7uF	GRM188Z71C475KE21D	MuRata	CAP, CERM, 4.7 μF, 16 V, +/- 10%, X7R, 0603	0603
3	C3	1	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
4	C4, C10	2	150pF	GRM31A5C2J151JW01D	MuRata	CAP, CERM, 150 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
5	C5	1	2.2uF	C1206C225K4RACTU	Kemet	CAP, CERM, 2.2 μF, 16 V, +/- 10%, X7R, 1206	1206
6	C6	1	3.3pF	GRM1555C1H3R3CA01D	MuRata	CAP, CERM, 3.3 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
7	C7	1	0.15uF	GRM155R71C154KA12D	MuRata	CAP, CERM, 0.15 μF, 16 V, +/- 10%, X7R, 0402	0402
8	C8	1	47pF	GRM1555C1H470FA01D	MuRata	CAP, CERM, 47 pF, 50 V, +/- 1%, C0G/NP0, 0402	0402
9	C9	1	0.015uF	GRM2195C1H153JA01D	MuRata	CAP, CERM, 0.015 μF, 50 V, +/- 5%, C0G/NP0, 0805	0805
10	C11	1	220pF	GRM1555C1H221JA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
11	C12	1	3.9pF	GRM1555C1H3R9CA01D	MuRata	CAP, CERM, 3.9 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
12	D1, D2	2	600V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, AEC-Q101, SMA	SMA
13	D3	1	600V	ES1JAF	Fairchild Semiconductor	Diode, Ultrafast, 600 V, 1 A, AEC-Q101, SMAF	SMAF
14	J1	1		4-644694-4	TE Connectivity	Header, 100 mil, 14x1, Tin, R/A, TH	Header, 100 mil,
							14x1, R/A, TH
15	J2	1		5-146261-1	TE Connectivity	Header, 100mil, 2x1, Gold, TH	Header, 2x1, 100mil
	R1, R2, R4	3	1.65k	CRCW12061K65FKEA	Vishay-Dale	RES, 1.65 k, 1%, 0.25 W, 1206	1206
17	R3	1	2.2	CRCW06032R20JNEA	Vishay-Dale	RES, 2.2, 5%, 0.1 W, 0603	0603
18	R5	1	174	CRCW1206174RFKEA	Vishay-Dale	RES, 174, 1%, 0.25 W, 1206	1206
	R6	1	750k	CRCW0402750KFKED	Vishay-Dale	RES, 750 k, 1%, 0.063 W, 0402	0402
	R7	1	487k	CRCW0402487KFKED	Vishay-Dale	RES, 487 k, 1%, 0.063 W, 0402	0402
21	R8	1	35.7k	CRCW060335K7FKEA	Vishay-Dale	RES, 35.7 k, 1%, 0.1 W, 0603	0603
22	R9, R10, R11	3	4.99Meg	CRCW12064M99FKEA	Vishay-Dale	RES, 4.99 M, 1%, 0.25 W, 1206	1206
	R12	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
24	R13	1	140k	CRCW0402140KFKED	Vishay-Dale	RES, 140 k, 1%, 0.063 W, 0402	0402
25	TP3	1		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose
							Testpoint
	U1	1		UCC25630-1DDBR	Texas Instruments	Enhanced LLC Resonant Controller with Driver, DDB0014A (SOIC-14)	DDB0014A
	C13	0	120uF	35ZLQ120MEFC6.3X11	Rubycon	CAP, AL, 120 μF, 35 V, +/- 20%, TH	D6.3xL11mm
28	Q1, Q2	0	60V	2N7002KW	Fairchild Semiconductor	MOSFET, N-CH, 60 V, 0.31 A, SOT-323	SOT-323
29	R14, R15	0	487k	CRCW0402487KFKED	Vishay-Dale	RES, 487 k, 1%, 0.063 W, 0402	0402
30	R16, R17	0	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated