PMP20745 REV A Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB	1		PMP9334	Any	Printed Circuit Board	
C1	1	10uF	C5750X7S2A106M230KB	TDK	CAP, CERM, 10 µF, 100 V, +/- 20%, X7S, 2220	2220
C105	1	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C111, C112	2	470uF	EMVY350ATR471MKE0S	Chemi-Con	CAP, AL, 470 μF, 35 V, +/- 20%, 0.07 ohm, SMD	KE0
C121	1	0.33uF	GRM21BR71E334KA01L	MuRata	CAP, CERM, 0.33 μF, 25 V, +/- 10%, X7R, 0805	0805
CC1, CSS	2	0.47uF	C0603C474K4RACTU	Kemet	CAP, CERM, 0.47 μF, 16 V, +/- 10%, X7R, 0603	0603
CC2	1	330pF	C0603C331K5RACTU	Kemet	CAP, CERM, 330 pF, 50 V, +/- 10%, X7R, 0603	0603
CIN	1	10uF	C2012X5R1E106K125AB	TDK	CAP, CERM, 10 µF, 25 V, +/- 10%, X5R, 0805	0805
CIN1, CIN2, CIN3,	4	0.047uF	C1812V473KDRACTU	Kemet	CAP, CERM, 0.047 μF, 1000 V, +/- 10%, X7R, 1812	1812
CIN4						
CISO1, CISO2	2	1000pF	VJ1210A102JXGAT5Z	Vishay-Vitramon	CAP, CERM, 1000 pF, 1000 V, +/- 5%, C0G/NP0, 1210	1210
CVCC	1	1uF	GRM188R61E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0603	0603
D1	1	15V	CMZ5929B TR13	Central Semiconductor	Diode, Zener, 15 V, 1.5 W, SMA	SMA
D2	1	5.1V	MMSZ5231B-7-F	Diodes Inc.	Diode, Zener, 5.1 V, 500 mW, SOD-123	SOD-123
D3	1	18V	CMZ5931B LEAD FREE	Central Semiconductor	Diode, Zener, 18 V, 900 mW, SMA	SMA
D4	1	200V	MBRB20200CTT4G	ON Semiconductor	Diode, Schottky, 200 V, 20 A, DDPAK	DDPAK
D105	1	200V	BAV21W-7-F	Diodes Inc.	Diode, Switching, 200 V, 0.2 A, SOD-123	SOD-123
J1	1		1707027	Phoenix Contact	Terminal Block, 7.62mm, 2 Pos, TH	Terminal Block,
						7.62mm, 2 Pos, TH
J2	1		1727010	Phoenix Contact	Conn Term Block, 2POS, 3.81mm, TH	2POS Terminal Block
Q100	1	1000V	FQD2N100TM	Fairchild Semiconductor	MOSFET, N-CH, 1000 V, 1.6 A, DPAK	DPAK
Q101	1	40 V	CMST2222A TR	Central Semiconductor	Transistor, NPN, 40 V, 0.6 A, SOT-323	SOT-323
Q102	1	1000V	STP8NK100Z	STMicroelectronics	MOSFET, N-CH, 1000 V, 6.5 A, TO-220AB	TO-220AB
R1, R2, R3	3	200k	CRCW0805200KJNEA	Vishay-Dale	RES, 200 k, 5%, 0.125 W, 0805	0805
R4, R5, R6	3	1.0Meg	CRCW08051M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.125 W, 0805	0805
R106	1	2.49k	CRCW12062K49FKEA	Vishay-Dale	RES, 2.49 k, 1%, 0.25 W, 1206	1206
R108	1	3.32k	CRCW06033K32FKEA	Vishay-Dale	RES, 3.32 k, 1%, 0.1 W, 0603	0603
R110	1	18.7k	RG1608P-1872-B-T5	Susumu Co Ltd	RES, 18.7 k, 0.1%, 0.1 W, 0603	0603
R111	1	1.50k	CRCW06031K50FKEA	Vishay-Dale	RES, 1.50 k, 1%, 0.1 W, 0603	0603
R112	1	16	CRCW060316R0JNEA	Vishay-Dale	RES, 16, 5%, 0.1 W, 0603	0603
R114	1	215k	CRCW0603215KFKEA	Vishay-Dale	RES, 215 k, 1%, 0.1 W, 0603	0603
R115	1	0.51	MCR25JZHFLR510	Rohm	RES, 0.51, 1%, 0.5 W, 1210	1210
R116	1	1.00	CRCW12061R00FKEA	Vishay-Dale	RES, 1.00, 1%, 0.25 W, 1206	1206
R117	1	100	CRCW1206100RFKEA	Vishay-Dale	RES, 100, 1%, 0.25 W, 1206	1206
R121	1	392k	CRCW0603392KFKEA	Vishay-Dale	RES, 392 k, 1%, 0.1 W, 0603	0603
RC1	1	1.87k	CRCW06031K87FKEA	Vishay-Dale	RES, 1.87 k, 1%, 0.1 W, 0603	0603
REN	1	20.5k	CRCW060320K5FKEA	Vishay-Dale	RES, 20.5 k, 1%, 0.1 W, 0603	0603
T100	1	3mH	G094215LF	GCI Technologies	Transformer, 3 mH, TH	26x27mm
U1	1		LM5022MM	Texas Instruments	60V Low Side Controller for Boost and SEPIC, 10-pin MSOP	MUB10A
C2, C3, C4, C5	0	10uF	C5750X7S2A106M230KB	TDK	CAP, CERM, 10 µF, 100 V, +/- 20%, X7S, 2220	2220
D103	0	1200V	STTH112A	STMicroelectronics	Diode, Ultrafast, 1200 V, 1 A, SMA	SMA
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
Z1	0	250V	SMAJ250A	Littelfuse	Diode, TVS, Uni, 250 V, 400 W, SMA	SMA

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated