



1 Photo

The photographs below show the PMP10767 Rev A assembly. This circuit was built on a PMP9176 Rev A PCB.

Top side




Bottom side





2 Converter Efficiency





V_{in}=120V_{AC}/60Hz

Vin(V)	lin(mA)	Pin(W)	Vout(V)	Iout(A)	Pout(W)	Losses(W)	Efficiency (%)
120.02	57.22	2.721	14.96	0.1406	2.103	0.618	77.30%
120.03	49.87	2.310	14.95	0.1199	1.793	0.517	77.60%
120.04	42.82	1.926	14.95	0.0998	1.492	0.434	77.47%
120.04	36.11	1.571	14.95	0.0807	1.206	0.365	76.80%
120.05	28.94	1.203	14.95	0.0608	0.909	0.294	75.56%
120.05	20.62	0.802	14.94	0.0399	0.596	0.206	74.27%
120.07	12.35	0.436	14.97	0.0200	0.300	0.136	68.78%
120.07	7.82	0.255	14.99	0.0104	0.155	0.100	60.85%
120.08	2.28	0.059	15.4	0.0000	0.000	0.059	0.00%

PMP10767 Rev A Test Results



 V_{in} =230 V_{AC} /50Hz

Vin(V)	lin(mA)	Pin(W)	Vout(V)	lout(A)	Pout(W)	Losses(W)	Efficiency (%)
230	36.39	2.691	14.96	0.1400	2.094	0.597	77.83%
230	32.36	2.335	14.95	0.1210	1.809	0.526	77.47%
230	27.88	1.953	14.95	0.1002	1.498	0.455	76.70%
230	23.52	1.592	14.95	0.0802	1.199	0.393	75.31%
230	19.11	1.238	14.95	0.0612	0.915	0.323	73.90%
230	13.77	0.837	14.97	0.0402	0.602	0.235	71.97%
230	8.24	0.457	14.99	0.0204	0.306	0.151	66.95%
230	4.96	0.251	14.96	0.0098	0.147	0.104	58.48%
230	1.50	0.063	15.04	0.0000	0.000	0.063	0.00%



3 Thermal Images

The thermal images below show a top view and bottom view of the board under $120V_{AC}/60Hz$ and $230V_{AC}/50Hz$ input conditions. The ambient temperature was $20^{\circ}C$ with no forced air flow. The output was at full load: 15V/0.14A.


V_{in}=120V_{AC}/60Hz Top Side



Spot analysis	Value
Amb Temperature	23.7°C
U1Temperature	44.4°C
D4Temperature	41.4°C
L2 Temperature	42.6°C




V_{in}=120V_{AC}/60Hz Bottom Side



Spot analysis	Value
Amb Temperature	26.3°C




V_{in}=230V_{AC}/50Hz Top Side



Spot analysis	Value
Amb Temperature	24.2°C
U1Temperature	44.2°C
D4Temperature	41.4°C
L2 Temperature	45.3°C



V_{in}=230V_{AC}/50Hz Bottom Side




Spot analysis	Value
Amb Temperature	25.9°C



4 Startup Waveforms

The output voltages at startup with constant current load are shown in the images below.

4.1 Start Up @ 85V_{AC}/60Hz: 15V/0.14A.



4.2 Start Up @ 85VAC/60Hz: no load.






4.3 Start Up @ 230V_{AC}/50Hz: 15V/0.14A.



4.4 Start Up @ 230VAC/50Hz: no load.







5 Output Ripple Voltages

The output ripple voltages are shown in the plots below.

5.1 120V_{AC}/60Hz: 15V/0.14A.




5.2 120V_{AC}/60Hz: No load.






5.3 230V_{AC}/50Hz: 15V/0.14A.



5.4 230V_{AC}/50Hz: No load.







6 Switching Waveforms

The images below show key switching waveforms of PMP10767RevA. The waveforms are measured with 0.14A full load.

6.1 Diode D4 @ 85V_{AC}/60Hz



6.2 Diode D4 @ 264VAC/50Hz



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated