

Filename: PMP3597_REVA_bom.xls

Date: 06/10/2009

PMP3597_REVA BOM

COUNT	RefDes	Value	Description	Size	Part Number	MFR
2	C1	0.1uF	Capacitor, Leaded, Film, 0.10 uF, 275 VAC	6.0 x 12.0 x 17.9mm	1779 410M2F	Vishay
	C2	0.1uF	Capacitor, Leaded, Film, 0.10 uF, 275 VAC	6.0 x 12.0 x 17.9mm	1779 410M2F	Vishay
2	C3	1nF	Capacitor, Ceramic, 50V, X7R, 10%	0805	Std	Std
1	C4	10nF	Capacitor, Ceramic, 25V, X7R, 10%	0805	Std	Std
	C5	1nF	Capacitor, Ceramic, 50V, X7R, 10%	0805	Std	Std
1	C6	22uF	Capacitor, Aluminum, 25V, 20%	5 x 11mm	Std	Std
2	C7	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0805	Std	Std
1	C8	10nF	Capacitor, Ceramic disc, 1KV	5mm dia	Std	Std
1	C9	2.2nF, Y1	Capacitor, Ceramic Disk, Y1	10mm dia	Std	Std
1	C10	10nF	Capacitor, Ceramic disc, 200V	5mm dia	Std	Std
1	C11	220uF	Capacitor, Aluminum, 100V, 20%, Low ESR	12.5 x 31.5mm	UHE2A221MHD	Nichicon
1	C12	2.2uF	Capacitor, Ceramic, 100V, X7R, 10%	1812	Std	Std
1	C13	0.47uF	Capacitor, Ceramic, 25V, X7R, 10%	0805	Std	Std
	C14	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0805	Std	Std
4	D1	1N4007	Diode, 1000V, 1A	DO-41	1N4007	Diodes
	D2	1N4007	Diode, 1000V, 1A	DO-41	1N4007	Diodes
	D3	1N4007	Diode, 1000V, 1A	DO-41	1N4007	Diodes
	D4	1N4007	Diode, 1000V, 1A	DO-41	1N4007	Diodes
1	D5	18V, 1W	Diode, Zener, 18-V, 1W	DO-41	1N4746A	Vishay
1	D6	BAT54S	Diode, Dual Schottky, 200-mA, 30-V	SOT23	BAT54S	Zetex
2	D7	FR107	Diode, Fast, 1000V, 1A	DO-41	FR107	TSC
	D8	FR107	Diode, Fast, 1000V, 1A	DO-41	FR107	TSC
1	D9	MUR160	Diode, Ultrafast, 600V, 1A	DO-41	MUR160	On Semi
1	D10	FR107	Diode, Fast, 1000V, 1A	DO-41	FR107	TSC
1	D11	12V	DIODE, Zener, 12V, 0.5W, 5%	DO-35	1N5242B	Vishay
1	D12	91V, 1W	Diode, Zener, 91V, 1W	DO-41	1N4763A	Vishay
1	F1	1A	Fuse	5x20mm	0215 001.MXEP	Littelfuse
1	L1	5.6mH	Common mode Inductor, 0.5A, 0.575ohm	UU10.5	75401	Prismatic
1	L2	500uH	Inductor, 0.4A	10 x 12mm	24501	Prismatic
1	Q1	FQP6N60C	Transistor, NFET, 600V, 6A	TO-220AB	FQP6N60C	Fairchild
3	R1	220K	Resistor, Chip, 1/4W, 5%	1206	Std	Std
	R2	220K	Resistor, Chip, 1/4W, 5%	1206	Std	Std

	R3	220K	Resistor, Chip, 1/4W, 5%	1206	Std	Std
1	R4	75K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R5	0	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R6	10	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R7	100	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R8	0.22	Resistor, Chip, 1/2W, 5%	2010	Std	Std
1	R9	15	Resistor, Chip, 1/4W, 5%	1206	Std	Std
1	R10	22K	Resistor, Power, 2W, \pm 5%	TH-990	MOS2CT52R223J	KOA
1	R11	33	Resistor, Chip, 1/4W, 5%	1206	Std	Std
1	R12	100K	Resistor, Power, 2W, \pm 5%	TH-990	MOS2CT52R104J	KOA
1	R13	10K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R14	13K	Resistor, 1W, 5%	1218	Std	Std
1	R15	10K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R16	51.1K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R17	14K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
2	R18	1K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R19	100	Resistor, Chip, 1/8W, 1%	0805	Std	Std
	R20	1K	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R21	0.47	Resistor, Metal Film, 1/4 watt, \pm 5%	1206	Std	Std
1	RT1	275V	MOV, 275V	10mm dia	Std	Std
1	T1	EE-25	Transformer, EE2507, 10 pin Horizontal	EE2507H	Custom	
1	U1	UCC28600D	IC, Quasi-Resonant Flyback Green Mode Controller	SO8	UCC28600D	TI
1	U2	PC817A	IC, Optocoupler	DIP-4A	PC817A	Sharp
1	U3	TL103WID	IC, Dual Op Amp With Internal Reference	SO8	TL103WID	TI
1	HS1	513201	Heatsink, TO-220, Vertical-mount, 5°C/W	0.5x1.38in.	513201	Aavid
1	J1	4300.0097	Header, 2-pin, 5mm spacing	0.197 inch x 2	ED1660	OST
1	J2	D120/2DS	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35 inch	D120/2DS	OST
1	TP1	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone

- Notes:
1. These assemblies are ESD sensitive, ESD precautions shall be observed.
 2. These assemblies must be clean and free from flux and all contaminants.
Use of no clean flux is not acceptable.
 3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
 4. Ref designators marked with an asterisk (***) cannot be substituted.
All other components can be substituted with equivalent MFG's components.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video
Wireless	www.ti.com/wireless-apps

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated