Variant: 001 Generated: 10/7/2019 3:51:24 PM TID #: 020029

TIDA-020029 REV A Bill of Materials



Item #		Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1 2	!PCB1 C100, C109,	6	0.047uF	TIDA-020029 CGA4J2X7R2A473K125AA	Any TDK	Printed Circuit Board CAP, CERM, 0.047 uF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
	C203, C206, C400, C405						
3	C101, C102,	12	4.7uF	CGA4J1X7R1V475K125AC	TDK	CAP, CERM, 4.7 uF, 35 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
	C300, C305, C317, C322,						
	C401, C402, C600, C605,						
	C617, C622		4000. =	00405007004	TDV	04D 05DN 4000-5 400V -/ 457 150 150 050	longo.
4	C103, C108, C334, C335,	8	1000pF	CGA3E2X7R2A102K080AA	TDK	CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
	C403, C404, C634, C635						
5	C204	1	0.1uF	C0805C104K5RACAUTO	Kemet	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 0, 0805	0805
6	C205, C316, C333, C616,	5	0.01uF	CGA3E2C0G1H103J080AA	TDK	CAP, CERM, 0.01 uF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0603	0603
7	C633		0.1uF	CGA4J2X8R1H104M125AA	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 20%, X8R, AEC-Q200 Grade 0, 0805	0805
,	C301, C306, C318, C323,	9	o. rui	COA402X0KIIIIO4WIZOAA	T DK	CAT , CERTIN, 0.1 dl , 30 V, 47-20/6, ADIX, AEC-4200 Glade 0, 0003	0003
	C500, C601, C606, C618,						
8	C623 C302, C303,	48	1000pF	CGA2B2C0G1H102J050BA	TDK	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1,	0402
	C304, C307,	40	Тооорі	COAZBZCOO II II OZGOODA	Ibk	0402	0402
	C308, C309, C310, C311,						
	C312, C313,						
	C314, C315, C319, C320,						
	C321, C324, C325, C326,						
	C327, C328,						
	C329, C330, C331, C332,						
	C602, C603, C604, C607,						
	C608, C609,						
	C610, C611, C612, C613,						
	C614, C615,						
	C619, C620, C621, C624,						
	C625, C626, C627, C628,						
	C629, C630,						
9	C631, C632 C501, C502	2	100pF	CGA3E2NP01H101J080AA	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 0,	0603
10	D300, D301,	96	Red	LR G6SP-CBEA-1-1-Z	OSRAM	0603 LED, Red, SMD	LED. RED.
10	D300, D301, D302, D303,	96	Red	LR G6SP-CBEA-1-1-Z	OSRAM	LED, Red, SMD	3.5x2.1x3.2mm
	D304, D305, D306, D307,						
	D308, D309,						
	D310, D311, D312, D313,						
	D314, D315, D316, D317,						
	D318, D319,						
	D320, D321, D322, D323,						
	D324, D325,						
	D326, D327, D328, D329,						
	D330, D331, D332, D333,						
	D334, D335,						
	D336, D337, D338, D339,						
	D340, D341,						
	D342, D343, D344, D345,						
	D346, D347, D600, D601,						
	D602, D603,						
	D604, D605, D606, D607,						
	D608, D609,						
	D610, D611, D612, D613,						
,,	D614, D615,	_		4705000	Dheeniy Centr	Terminal Block Cut 2 54mm, TH	Terminal Disable 5
11	J100, J400	2		1725698	Phoenix Contact	Terminal Block, 6x1, 2.54mm, TH	Terminal Block, 6x1, 2.54mm, TH
12	L100, L400	2		XEL3530-122MEC	Coilcraft	Shielded Power Inductors	SMT_IND_3MM2_3N M5
13	R100, R101,	4	0	RCS06030000Z0EA	Vishay-Dale	RES, 0, 0%, 0.25 W, AEC-Q200 Grade 0, 0603	0603
14	R400, R401 R204, R207	2	60.4	CRCW080560R4FKEA	Vishay-Dale	RES, 60.4, 1%, 0.125 W, AEC-Q200 Grade 0, 0805	0805
15	R205, R206, R300, R301,	32	10.0k	RMCF0603FT10K0	Stackpole Electronics Inc	RES, 10.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
	R302, R303,						
	R304, R305, R308, R309,						
	R310, R311, R312, R313,						
	R314, R315,						
	R501, R502, R600, R601,						
	R602, R603,						
	R604, R605, R608, R609,						
	R610, R611,						
	R612, R613, R614, R615		1	1	1		
16	R306, R316,	4	12.4k	ERJ-6ENF1242V	Panasonic	RES, 12.4 k, 1%, 0.125 W, AEC-Q200 Grade 0, 0805	0805
17	R606, R616 R500	1	4.70k	ERJ-P06F4701V	Panasonic	RES, 4.70 k, 1%, 0.5 W, AEC-Q200 Grade 0, 0805	0805
18 19	R503, R504 U201	2	22	CRCW060322R0JNEA TCAN1044DRBTQ1	Vishay-Dale Texas Instruments	RES, 22, 5%, 0.1 W, AEC-Q200 Grade 0, 0603 Automotive High Speed CAN Transceiver, DRB0008F (VSON-8)	0603 DRB0008F
20	U300, U301,	4		TPS929120QPWPRQ1	Texas Instruments	12-Channel Automotive FlexLED Driver, PWP0024P (HTSSOP-24)	PWP0024P
21	U600, U601 U500	1		TLIN1029DRQ1	Texas Instruments	Local Interconnect Network (LIN) Transceiver with Dominant State	D0008A
						Timeout, D0008A (SOIC-8)	
22	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated