

PMP11303 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
PCB1	1		PMP11303	Any	Printed Circuit Board	
C1, C7, C68	3	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603
C2, C3	2	10uF	GMK316AB7106KL	Taiyo Yuden	CAP, CERM, 10uF, 35V, +/-10%, X7R, 1206	1206
C4, C5, C6	3	470pF	C0603C471K5RACTU	Kemet	CAP, CERM, 470pF, 50V, +/-10%, X7R, 0603	0603
C8	1	2200pF	C0603C222K5RACTU	Kemet	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0603	0603
C9	1	1000pF	C0603C102K5RACTU	Kemet	CAP, CERM, 1000pF, 50V, +/-10%, X7R, 0603	0603
C10, C15	2	100pF	DE6B3KJ101KN3A	MuRata	CAP CER 100PF 300VAC 10% RADIAL	TH, 2- Leads, Body 8x7mm, Pin Spacing 7.5mm
C11, C17	2	220pF	DE6B3KJ221KN3A	MuRata	CAP, CERM, 220 pF, 300 V, +/- 10%, B, TH, 2- Leads, Body 8x7mm, Pin Spacing 7.5mm	TH, 2- Leads, Body 8x7mm, Pin Spacing 7.5mm
C12, C25	2	1uF	C0603C105K8PACTU	Kemet	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0603	0603
C13, C14	2	0.47uF	ECQ-U2A474ML	Panasonic	CAP, Film, 0.47uF, 275V, +/-20%, TH	Radial 25x8.5x18.5
C16, C28	2	47pF	GRM1555C1E470JA01D	MuRata	CAP, CERM, 47pF, 25V, +/-5%, C0G/NP0, 0402	0402
C18	1	270uF	380LQ271M450K022	Cornell Dubilier Electronics	CAP, AL, 270 uF, 450 V, +/- 20%, 0.737 ohm, TH	D30xL30mm
C19	1	0.33uF	ECQ-U2A334ML	Panasonic	CAP, Film, 0.33uF, 275V, +/-20%, TH	RCAP, 17.5x17.5x9.5mm
C20	1	47uF	GRM32ER70J476KE20L	MuRata	CAP, CERM, 47uF, 6.3V, +/-10%, X7R, 1210	1210
C21, C48	2	100uF	EEU-EB1E101S	Panasonic	CAP, AL, 100 uF, 25 V, +/- 20%, TH	6.3x11.2mm
C23	1	1uF	GRM21BR71H105KA12L	MuRata	CAP, CERM, 1uF, 50V, +/-10%, X7R, 0805	0805
C24	1	2200pF	DE6E3KJ222MN3A	MuRata	CAP, CERM, 2200 pF, 300 V, +/- 20%, E, TH, 2- Leads, Body 9x7mm, Pin Spacing 7.5mm	TH, 2- Leads, Body 9x7mm, Pin Spacing 7.5mm
C26, C43	2	DNP	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Used in PnP output
C27	1	100pF	06033C101KAT2A	AVX	CAP, CERM, 100 pF, 25 V, +/- 10%, X7R, 0603	0603
C29	1	1uF	UMK107AB7105KA-T	Taiyo Yuden	CAP, CERM, 1 uF, 50 V, +/- 10%, X7R, 0603	0603
C30, C31, C33, C34, C35, C37, C38	7	680uF	35ZLH680MEFC10X23	Rubycon	CAP ALUM 680UF 20% 35V RADIAL	10x25
C32	1	0.1uF	C3216C0G1E104J	TDK	CAP, CERM, 0.1 uF, 25 V, +/- 5%, C0G/NP0, 1206	1206
C36	1	0.012uF	ECW-H8123HA	Panasonic	CAP, Film, 0.012uF, 800V, +/-3%, TH	Cap, 15.4x11.7x5.8mm
C39	1	0.047uF	121MPE473J	Rubycon	CAP, Film, 0.047 uF, 1250 V, +/- 5%, TH	18.5x11.5x21mm
C40	1	1uF	12063C105KAT2A	AVX	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 1206	1206
C41, C42	2	100pF	06035A101FAT2A	AVX	CAP, CERM, 100pF, 50V, +/-1%, C0G/NP0, 0603	0603
C47	1	470pF	GRM188R72A471KA01D	MuRata	CAP, CERM, 470 pF, 100 V, +/- 10%, X7R, 0603	0603
C49	1	0.1uF	08055C104JAT2A	AVX	CAP, CERM, 0.1uF, 50V, +/-5%, X7R, 0805	0805
C51	1	10uF	CGA5L3X5R1H106K160AB	TDK	CAP, CERM, 10 uF, 50 V, +/- 10%, X5R, 1206_190	1206_190
C52	1	0.01uF	GRM188R71E103KA01D	MuRata	CAP, CERM, 0.01 uF, 25 V, +/- 10%, X7R, 0603	0603
C54, C102, C103	3	470uF	16ZLJ470MTA8X11.5	Rubycon	CAP, AL, 470 uF, 16 V, +/- 20%, 0.075 ohm, TH	CAP, 8x11.5mm
C55	1	22uF	GCM32ER71C226KE19L	MuRata	CAP, CERM, 22 uF, 16 V, +/- 10%, X7R, 1210	1210
C56, C65, C66	3	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
C57	1	0.047uF	GRM32DR72J473KW01L	MuRata	CAP, CERM, 0.047 uF, 630 V, +/- 10%, X7R, 1210	1210
C58, C59, C60	3	1uF	C0603C105K4PACTU	Kemet	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	0603
C62	1	0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 uF, 100 V, +/- 5%, X7R, 0603	0603
C63, C101	2	22uF	1206YD226MAT2A	AVX	CAP, CERM, 22 uF, 16 V, +/- 20%, X5R, 1206	1206

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C64	1	1uF	GRM31MR71H105KA88L	MuRata	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 1206	1206
C67	1	4.7pF	06035A4R7CAT2A	AVX	CAP, CERM, 4.7 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C69	1	27uF	25ZL27MEFC5X7	Rubycon	CAP ALUM 27UF 20% 25V RADIAL	6.3x5.5mm
C104	1	1000pF	06031C102KAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, 0603	0603
C105	1	2.2uF	C3225X7R1H225K250AB	TDK	CAP, CERM, 2.2 µF, 50 V, +/- 10%, X7R, 1210	1210
D1, D2	2	800V	DA2JF8100L	Panasonic	Diode, Fast Rectifier, 800V, 0.2A, TVS, 1.7x.7x1.25mm	TVS, 1.7x.7x1.25mm
D3, D4, D9, D12	4	100V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100V, 0.25A, SOD-323	SOD-323
D5	1	600V	1N5406	Vishay-Semiconductor	Diode, Switching-Bridge, 600V, 3A, TH	DO-201AD
D6	1	600V	C3D04060A	Cree	Diode, Schottky, 600V, 4A, TH	TO-220-F2
D7	1	420V	GBU8J-BP	Micro Commercial Component	Diode, Switching-Bridge, 420V, 8A, TH	GBU
D8, D10	2	100V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100 V, 0.25 A, SOD-323	SOD-323
D11	1	600V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, SMA	SMA
D14	1	18V	MMSZ5248B-7-F	Diodes Inc.	Diode, Zener, 18V, 500mW, SOD-123	SOD-123
D17	1	120V	SMAJ120A	Littelfuse	Diode, TVS, Uni, 120 V, 400 W, SMA	SMA
D18	1	1.7V	US1M-13-F	Diodes Inc.	Diode, Ultrafast, 1000V, 1A, SMA	SMA
D19	1	100V	B3100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 3 A, SMC	SMC
D20	1	100V	SS110-TP	Micro Commercial Component	Diode, Schottky, 100 V, 1 A, SMA	SMA
D21	1	100V	1N4148W-TP	Micro Commercial Component	Diode, Switching, 100 V, 0.15 A, SOD-123	SOD-123
D22	1	100V	MMDL914-TP	Micro Commercial Component	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323
F1	1		0216008.MXESPP	Littelfuse	Fuse, 8A, 250V, TH	Fuse, 20x5.2mm
H1	1		578622B03200G	Aavid	Twin Channel Style Heat Sink, TO-220, Vertical	Twin Channel Style Heat Sink, TO-220
H3, H9, H10, H16, H21, H22	6		4824	Keystone	HEX STANDOFF 6-32 NYLON 1-1/2"	HEX STANDOFF 6-32 NYLON 1-1/2"
H5, H11, H12, H17, H18, H24	6		1903C	Keystone	Standoff, Hex, 0.5"L #6-32 Nylon	6-32 HEX Nylon standoff 0.500 mil
H26, H27, H28, H29, H30	5		MAX01NG	Aavid Thermalloy	MAX Clip	Clip
HS1, HS2	2		782653B04250G	Aavid	HEATSINK VERT MAX CLIP, BLACK, 4.25 INCHES	4.25 INCH EXTRUDED HEAT SINK
J1	1		923345-06-C	3M	Jumper Wire, 600mil spacing, Blue, pkg of 150, TH	600 mil Jumper Wire
J2	1		1-1318301-3	TE Connectivity	Header, 312mil, 3x1, Tin, TH	19.7x10.7 x8.5 mm
J3	1		ED120/4DS	On-Shore Technology	Terminal Block, 4x1, 5.08mm, TH	TERM_BLK, 4pos, 5.08mm
J4	1	2x1	1715721	Phoenix Contact	Conn Term Block, 2POS, 5.08mm, TH	2POS Terminal Block
L1	1		RLTI-1108	Renco Electronics	Inductor, ?, , A, TH	1800x1740x1750mil
L2	1	2.2mH	7448258022	Würth Elektronik eiSos	Coupled inductor, 2.2mH, 8A, 0.014 ohm, +/-30%, TH	30x35x21mm
L3	1	10mH	744825510	Würth Elektronik	Coupled inductor, 10 mH, 5 A, 0.055 ohm, TH	30x35x21mm
L5	1	40uH	RLTI-1154	Renco Electronics	Inductor, 40 µH, 0.02 ohm, TH	925x915mil
Q1	1	600V	BSS126 H6906	Infineon Technologies	MOSFET, N-CH, 600V, 0.021A, SOT-23	SOT-23
Q2, Q6	2	100V	BSS123	Fairchild Semiconductor	MOSFET, N-CH, 100 V, 0.17 A, SOT-23	SOT-23
Q3	1	550V	IPP50R199CPXKSA1	Infineon	MOSFET N-CH 550V 17A TO-220	TO-262
Q4, Q7	2	550V	IPP50R199CP	Infineon	MOSFET N-CH 550V 17A TO-220	TO-262
Q5, Q8	2	100V	CSD19533KCS	Texas Instruments	MOSFET, N-CH, 100 V, 86 A,	
Q9, Q10	2	40 V	MMBT4403	Fairchild Semiconductor	Transistor, PNP, 40 V, 0.6 A, SOT-23	SOT-23
Q11	1	60V	2N7002-7-F	Diodes Inc.	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	SOT-23
Q12	1	600V	AOD2N60	AOS	MOSFET, N-CH, 600 V, 2 A, DPAK	DPAK
R4, R5, R6, R13, R14, R15	6	3.09Meg	CRCW12063M09FKEA	Vishay-Dale	RES, 3.09Meg ohm, 1%, 0.25W, 1206	1206

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R7, R8, R9	3	10.0Meg	CRCW120610M0FKEA	Vishay-Dale	RES, 10.0Meg ohm, 1%, 0.25W, 1206	1206
R10	1	75.0k	CRCW060375K0FKEA	Vishay-Dale	RES, 75.0k ohm, 1%, 0.1W, 0603	0603
R11	1	3.3Meg	CRCW06033M30JNEA	Vishay-Dale	RES, 3.3Meg ohm, 5%, 0.1W, 0603	0603
R12, R20, R81	3	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R16, R17	2	470	RC0603FR-07470RL	Yageo America	RES, 470 ohm, 1%, 0.1W, 0603	0603
R18	1	2.21k	CRCW06032K21FKEA	Vishay-Dale	RES, 2.21 k, 1%, 0.1 W, 0603	0603
R19	1	3.32k	CRCW06033K32FKEA	Vishay-Dale	RES, 3.32k ohm, 1%, 0.1W, 0603	0603
R21	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
R22	1	3.3	CRCW06033R30JNEA	Vishay-Dale	RES, 3.3, 5%, 0.1 W, 0603	0603
R23, R27, R37, R42	4	10.0	RC0603FR-0710RL	Yageo America	RES, 10.0, 1%, 0.1 W, 0603	0603
R24, R38	2	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.1W, 0603	0603
R25, R39	2	221k	CRCW0603221KFKEA	Vishay-Dale	RES, 221k ohm, 1%, 0.1W, 0603	0603
R26	1	1.00	CRCW06031R00FKEA	Vishay-Dale	RES, 1.00, 1%, 0.1 W, 0603	0603
R28	1	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0, 5%, 0.25 W, 1206	1206
R29, R43, R50, R58	4	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R30, R34, R35	3	0.68	CSRN2512FKR680	Stackpole Electronics Inc.	RES SMD 0.68 OHM 1% 2W 2512	2512
R31, R32, R33	3	0.068	CSRN2512FK68L0	Stackpole Electronics Inc.	RES SMD 0.068 OHM 1% 2W 2512	2512
R40, R49	2	3.30	ERJ-8RQF3R3V	Panasonic	RES, 3.30 ohm, 1%, 0.25W, 1206	1206
R41	1	2.2	CRCW08052R20JNEA	Vishay-Dale	RES, 2.2, 5%, 0.125 W, 0805	0805
R44	1	1.00	ERJ-6RQF1R0V	Panasonic	RES, 1.00 ohm, 1%, 0.125W, 0805	0805
R45, R47, R52, R80	4	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R46, R48	2	51.1	CRCW060351R1FKEA	Vishay-Dale	RES, 51.1, 1%, 0.1 W, 0603	0603
R53	1	1.21k	CRCW12061K21FKEA	Vishay-Dale	RES, 1.21 k, 1%, 0.25 W, 1206	1206
R55	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R56	1	49.9	ERJ-8ENF49R9V	Panasonic	RES, 49.9 ohm, 1%, 0.25W, 1206	1206
R59	1	22.6k	CRCW060322K6FKEA	Vishay-Dale	RES, 22.6 k, 1%, 0.1 W, 0603	0603
R64	1	4.87k	CRCW06034K87FKEA	Vishay-Dale	RES, 4.87 k, 1%, 0.1 W, 0603	0603
R66	1	2.49k	CRCW06032K49FKEA	Vishay-Dale	RES, 2.49 k, 1%, 0.1 W, 0603	0603
R68	1	20.0k	CRCW080520K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.125 W, 0805	0805
R70	1	20.5	CRCW120620R5FKEA	Vishay-Dale	RES, 20.5, 1%, 0.25 W, 1206	1206
R71	1	0	MCR18EZJH000	Rohm	RES, 0, 5%, 0.25 W, 1206	1206
R72	1	2.0k	CRCW06032K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.1 W, 0603	0603
R73	1	56.2k	CRCW060356K2FKEA	Vishay-Dale	RES, 56.2 k, 1%, 0.1 W, 0603	0603
R74, R77	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R75	1	4.99k	CR0603-FX-4991ELF	Bourns	RES, 4.99 k, 1%, 0.1 W, 0603	0603
R76, R78	2	1.0k	CRCW06031K00JNEA	Vishay-Dale	RES, 1.0 k, 5%, 0.1 W, 0603	0603
R79	1	330	CRCW1206330RJNEA	Vishay-Dale	RES, 330, 5%, 0.25 W, 1206	1206
R82	1	787	CRCW0603787RFKEA	Vishay-Dale	RES, 787, 1%, 0.1 W, 0603	0603
R83	1	27.4k	CRCW060327K4FKEA	Vishay-Dale	RES, 27.4 k, 1%, 0.1 W, 0603	0603
R84	1	36.5k	CRCW060336K5FKEA	Vishay-Dale	RES, 36.5 k, 1%, 0.1 W, 0603	0603
R85, R86	2	1.82	CRCW08051R82FKEA	Vishay-Dale	RES, 1.82, 1%, 0.125 W, 0805	0805
R101	1	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
RT1, RT2	2	10 ohm	CL-60	GE Sensing	Thermistor NTC, 10 ohm, 25%, Disc, 220x770 mil	Disc, 220x770 mil
S1, S2	2		200USP9T1A1M2RE	E-Switch	Switch, Toggle, SPST, 1Pos, TH	Switch, 7.0x9.6x4.5mm
T1	1	200µH	RLTI-1155	Renco Electronics	Transformer, 200 uH, TH	1850x1500mil
T2	1	650 uH	RLTI-1156	Renco Electronics	Transformer, 650 uH, TH	675x760mil
TP1, TP4	2	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
TP3	1	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP5, TP6	2	White	5012	Keystone	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
TP7, TP9	2	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP8, TP10	2	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
U1	1		UCC29950DR	Texas Instruments	CCM PFC and LLC Combo Controller, D0016A	D0016A
U2, U4	2		UCC24610DR	Texas Instruments	GREEN Rectifier Controller Device, D0008A	D0008A
U3	1		UCC27532DBVR	Texas Instruments	2.5-A and 5-A, 35-VMAX VDD FET and IGBT Single-Gate Driver, DBV0006A	DBV0006A
U5	1		UCC27714D	Texas Instruments	High-Speed,4A, 600V High-side Low-side Gate Driver Device, D0014A	D0014A
U7, U13	2		PC817X4NSZ0F		Opto-Isolator, 1 Channel, TH	DIP-4
U9	1		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U10	1		UCC24650DBVR	Texas Instruments	200-V Wake-Up Monitor for Fast Transient PSR, DBV0005A	DBV0005A
U11	1		TPS71550DCKR	Texas Instruments	Single Output LDO, 50 mA, Fixed 5 V Output, 3 to 24 V Input, 5-pin SC70 (DCK), -40 to 85 degC, Green (RoHS & no Sb/Br)	DCK0005A
U12	1		UCC28730DR	Texas Instruments	Constant-Voltage Constant-Current Flyback Controller With PSR and Wake-Up Monitoring, D0007A	D0007A
V1	1	300V	B72207S2301K101	EPCOS Inc	Varistor, 300V, 1.75kA, 7MM Radial, TH	Varistor, TH, 7MM
C22, C46	0	0.1uF	08055C104JAT2A	AVX	CAP, CERM, 0.1uF, 50V, +/-5%, X7R, 0805	0805
C44	0	0.01uF	C0603C103K5RACTU	Kemet	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, 0603	0603
C50	0	10uF	CGA5L3X5R1H106K160AB	TDK	CAP, CERM, 10 uF, 50 V, +/- 10%, X5R, 1206_190	1206_190
C53	0	0.1uF	C0603C104K4RACTU	Kemet	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0603	0603
D13	0	12V	BZX384-C12,115	NXP Semiconductor	Diode, Zener, 12V, 300mW, SOD-323	SOD-323
D15, D16	0	100V	BAV99,215	NXP Semiconductor	Diode, Switching, 100V, 0.215A, SOT-23	SOT-23
R1, R2, R3	0	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.25W, 1206	1206
R36, R51	0	DNP	Used in BOM report	Used in BOM report	RES, xxx ohm, x%, xW, [PackageReference]	Used in PnP output
R54	0	100	CRCW1206100RFKEA	Vishay-Dale	RES, 100, 1%, 0.25 W, 1206	1206
R57	0	10.0Meg	RC0603FR-0710ML	Yageo America	RES, 10.0 M, 1%, 0.1 W, 0603	0603
R61	0	1.21k	CRCW12061K21FKEA	Vishay-Dale	RES, 1.21 k, 1%, 0.25 W, 1206	1206
R62	0	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R63	0	1.10Meg	CRCW06031M10FKEA	Vishay-Dale	RES, 1.10 M, 1%, 0.1 W, 0603	0603
R65	0	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R67	0	1.20k	RC0603FR-071K2L	Yageo America	RES, 1.20k ohm, 1%, 0.1W, 0603	0603
U6	0		TPS7A1601DGNT	Texas Instruments	Single Output LDO, 100 mA, Adjustable 1.2 to 18.5 V Output, 3 to 60 V Input, with Enable and Power Good, 8-pin MSOP (DGN), -40 to 125 degC, Green (RoHS & no Sb/Br)	DGN0008C
U8	0		PC817X4NSZ0F		Opto-Isolator, 1 Channel, TH	DIP-4

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.