PMP40025 REV E1 Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1		0.22uF	890324025027CS	Wurth Elektronik	CAP, Film, 0.22 µF, 275 V, +/- 10%, TH	18x6x11.5mm
C2, C3		47uF	ESMG451ELL470MLP1S	Chemi-Con	CAP, AL, 47 μF, 450 V, +/- 20%, TH	D16xL35.5mm
C4	1	470uF	EEU-FC1J471	Panasonic	CAP, AL, 470 µF, 63 V, +/- 20%, 0.059 ohm, AEC-Q200 Grade 2, TH	D16xL20mm
C6	1	0.1uF	C0805C104K1RACTU	Kemet	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	0805
C7, C8		4.7uF	GRM319R61H475KA12	MuRata	CAP, CERM, 4.7 μF, 50 V, +/- 10%, X5R, 1206	1206
C9	1	2200pF	DE1E3KX222MA4BL01	MuRata	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, Cap, 7x12x9 mm	Cap, 7x12x9 mm
C10	1	1000pF	C3216C0G2J102J	TDK	CAP, CERM, 1000 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
C11	1	1000pF	08055A102FAT2A	AVX	CAP, CERM, 1000 pF, 50 V, +/- 1%, C0G/NP0, 0805	0805
C12	1	4.7uF	C2012X5R1E475K125AB	TDK	CAP, CERM, 4.7 μF, 25 V, +/- 10%, X5R, 0805	0805
C13	1	1000pF	C1608C0G2A102J080AA	TDK	CAP, CERM, 1000 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603
C14	1	470pF	GRM31A7U2J471JW31D	MuRata	CAP, CERM, 470 pF, 630 V, +/- 5%, U2J, 1206	1206
C15	1	100uF	ECA-2AM101	Panasonic	CAP, AL, 100 μF, 100 V, +/- 20%, TH	D10xL16mm
D1	1	600V	Z4DGP406L-HF	Comchip Technology	Diode, P-N-Bridge, 600 V, 4 A, Z4-D	Z4-D
D3	1	600V	ES1J-LTP		en Diode, Superfast Rectifier, 600 V, 1 A, SMA	SMA
D4	1	200V	BAS20HT1G	ON Semiconductor	Diode, Switching, 200 V, 0.2 A, AEC-Q101, SOD-323	SOD-323
D5	1	30V	BAT54HT1G	ON Semiconductor	Diode, Schottky, 30 V, 0.2 A, SOD-323	SOD-323
D6	1	600V	FEP16JT	ON Semiconductor	Diode, Ultrafast, 600 V, 4 A, TH	TO-220AB
D7	1	180V	1SMB5955BT3G	ON Semiconductor	Diode, Zener, 180 V, 550 mW, SMB	SMB
D8	1	12V	1SMA5927BT3G	ON Semiconductor	Diode, Zener, 12 V, 1.5 W, SMA	SMA
F1	1		39213150000	Littelfuse	Fuse, 3.15 A, 250VAC/VDC, TH	8x8.5x4mm
J1, J2	2		282841-2	TE Connectivity	Terminal Block, 2x1, 5.08mm, TH	10.16x15.2x9mm
L1	1	33uH	DO3308P-333MLB	Coilcraft	Inductor, Drum Core, Ferrite, 33 µH, 1.2 A, 0.25 ohm, SMD	DO3308P
L2	1	1mH	744821201	Wurth Elektronik	Coupled inductor, 1 mH, 2 A, 0.045 ohm, TH	15 x 18 x 7.5mm
L3	1	600 ohm	FBMH3225HM601NT	Taiyo Yuden	Ferrite Bead, 600 ohm @ 100 MHz, 3 A, 1210	1210
Q1	1	650V	TK11A65D	TOSHIBA	MOSFET, N-CH, 650 V, 11 A, TO-220AB	TO-220AB
Q2	1	60 V	MMBT3906	Fairchild Semiconductor	Transistor, PNP, 60 V, 0.8 A, SOT-23	SOT-23
Q3, Q4	2	40 V	MMBT3904	Fairchild Semiconductor	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
R1	1	100k	CRCW1206100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.25 W, 1206	1206
R2	1	510k	RC0603FR-07510KL	Yageo America	RES, 510 k, 1%, 0.1 W, 0603	0603
R3	1	510k	CRCW0805510KJNEA	Vishay-Dale	RES, 510 k, 5%, 0.125 W, 0805	0805
R4	1	2.00	CRCW08052R00FKEA	Vishay-Dale	RES, 2.00, 1%, 0.125 W, 0805	0805
R5	1	68k	CRCW080568K0JNEA	Vishay-Dale	RES, 68 k, 5%, 0.125 W, 0805	0805
R6	1	390k	RC0603FR-07390KL	Yageo America	RES, 390 k, 1%, 0.1 W, 0603	0603
R7	1	2.00	RC1206FR-072RL	Yageo America	RES, 2.00, 1%, 0.25 W, 1206	1206
R8	1	1.00k	RC1206FR-071KL	Yageo America	RES, 1.00 k, 1%, 0.25 W, 1206	1206
R9	1	27k	CRCW060327K0JNEA	Vishay-Dale	RES, 27 k, 5%, 0.1 W, 0603	0603
R10	1	150k	RC0603FR-07150KL	Yageo America	RES, 150 k, 1%, 0.1 W, 0603	0603
R11, R12	2	0.5	CSR1206FKR500	Stackpole Electronics Inc	RES, 0.5, 1%, 0.5 W, 1206	1206
R13	1	10	CRCW120610R0JNEA	Vishay-Dale	RES, 10, 5%, 0.25 W, 1206	1206
R14	1	100k	CRCW0805100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.125 W, 0805	0805
R15, R16	2	1.0Meg	CRCW12061M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.25 W, 1206	1206
R17	1	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R18	1	2.00	CRCW06032R00FKEA	Vishay-Dale	RES, 2.00, 1%, 0.1 W, 0603	0603
R19	1	1.00Meg	RC0603FR-071ML	Yageo America	RES, 1.00 M, 1%, 0.1 W, 0603	0603

Page 1 of 2

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R20	1	100k	RC1206FR-07100KL	Yageo America	RES, 100 k, 1%, 0.25 W, 1206	1206
R21, R22	2	100	RC1206FR-07100RL	Yageo America	RES, 100, 1%, 0.25 W, 1206	1206
T1	1	160uH	750343192	Wurth Elektronik	RM10,	TH
U1	1		UCC24650DBVR	Texas Instruments	200-V Wake-Up Monitor for Fast Transient PSR, DBV0005A	DBV0005A
U2	1		UCC28730DR	Texas Instruments	Constant-Voltage Constant-Current Flyback Controller With PSR and	D0007A
					Wake-Up Monitoring, D0007A	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

Tl's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter Tl's applicable published warranties or warranty disclaimers for Tl products, and no additional obligations or liabilities arise from Tl providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Tl's standard terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated