Description	Designator	Footprint	LibRef	Quantity	Manufacturer
Printed Circuit Board	IPCB1		РСВ	1	Any
CAP, CERM, 4.7 pF, 50 V, +/- 1%, C0G/NP0, 0402	C1, C11, C12, C21, C22, C34	0402	GRM1555C1H4R7WA01D	6	MuRata
CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0603	C2, C4, C13, C23, C24, C26, C52, C57, C58, C59	0603	GRM188R71C104KA01D	10	MuRata
CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0603	C3, C6, C8, C14, C16, C18, C25, C29, C31, C47, C53	0603	GRM188R71H221KA01D	11	MuRata
CAP, CERM, 47 pF, 25 V, +/- 5%, C0G/NP0, 0402	C5, C9, C15, C19, C28, C32	0402	GRM1555C1E470JA01D	6	MuRata
CAP, CERM, 100 pF, 100 V,+/- 5%, C0G/NP0, 0603	C7, C17, C30	0603	GRM1885C2A101JA01D	3	MuRata
CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	C10, C20, C27, C33	0402	GRM155R71C104KA88D	4	MuRata
CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0603	C35, C38, C41, C44	0603	06033D104KAT2A	4	AVX
CAP, CERM, 330pF, 50V, +/-10%, X7R, 0603	C36, C37, C39, C40, C42, C43, C45, C46	0603	GRM188R71H331KA01D	8	MuRata
CAP, CERM, 4700 pF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	C48	0603	GCM188R71H472KA37D	1	MuRata
CAP, CERM, 1000 pF, 25 V, +/- 5%, C0G/NP0, 0603	C49, C51	0603	GRM1885C1E102JA01D	2	MuRata
CAP, CERM, 1 μF, 20 V, +/- 10%, X5R, 0805	C50, C61, C63, C65	0805_HV	TMK212BJ105KG-T	4	Taiyo Yuden
CAP, CERM, 1200 pF, 50 V, +/- 5%, C0G/NP0, 0603	C54	0603	GRM1885C1H122JA01D	1	MuRata
CAP, CERM, 0.047 µF, 100 V, +/- 10%, X7R, 0805	C55	0805_HV	GRM21BR72A473KA01L	1	MuRata
CAP, CERM, 2.2 μF, 20 V, +/- 10%, X5R, 0805	C56	0805_HV	TMK212BJ225KG-T	1	Taiyo Yuden
CAP, CERM, 10 μF, 25 V,+/- 10%, X5R, 0805	C60, C62, C64	0805_HV	GRM21BR61E106KA73L	3	MuRata
Diode, Schottky, 70 V, 0.07 A, SOD-523	D1, D2, D4, D5, D6, D7, D9, D10, D11, D12, D14, D15	SOD-523	1PS79SB70,115	12	NXP Semiconductor
Diode, Schottky, 40 V, 0.35 A, SOD-523	D3, D8, D13	SOD-523	ZHCS350TA	3	Diodes Inc.
ED, Green, SMD	D16, D17	WL-SMCW_GREEN	150060GS75000	2	Wurth Elektronik
ED, Green, SMD	D18	LG L29K_GREEN	LG L29K-G2J1-24-Z	1	OSRAM
Receptacle, 2.54mm, 10x2, Gold, TH	J1, J2	Samtec_SSW-110-x1-x-D	SSW-110-21-S-D	2	Samtec
Header, 100mil, 3x1, Gold, TH	J5, J9	TSW-103-07-G-S	TSW-103-07-G-S	2	Samtec
Header (Shrouded), 2.5mm, 2x1, Tin, TH	J6, J16	JST_B2B-EH-A	B2B-EH-A(LF)(SN)	2	JST Manufacturing
Header(shrouded), 2.54mm, 4x2, Gold, TH	J7, J8, J14	Molex_70246-0801	70246-0801	3	Molex
Header, 100mil, 4x1, Gold, TH	J10	TSW-104-07-G-S	TSW-104-07-G-S	1	Samtec
Header, 100mil, 2x1, Gold, TH	J11, J12, J13, J15	TSW-102-07-G-S	TSW-102-07-G-S	4	Samtec
Header, 100mil, 7x1, Gold, TH	J17	TSW-107-07-G-S	TSW-107-07-G-S	1	Samtec
nductor, Shielded, Ferrite, 22 µH, 0.013 A, 0.455 ohm, SMD	L1, L2	0805_HV	LQM21FN220N00L	2	MuRata
RES, 8.45 k, 0.1%, 0.063 W, 0402	R1, R9, R10, R19, R22, R33	0402	ERA-2AEB8451X	6	Panasonic
RES, 100, 5%, 0.063 W, 0402	R2, R6, R7, R11, R15, R16, R24, R30	0402	CRCW0402100RJNED	8	Vishay-Dale
RES, 3.30 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	R3, R8, R12, R18, R25, R32	0402	ERJ-2RKF3301X	6	Panasonic
RES, 120, 5%, 0.1 W, 0603	R4, R13, R26, R38, R53	0603	CRCW0603120RJNEA	5	Vishay-Dale
RES, 10.0, 1%, 0.063 W, 0402	R5, R14, R23, R27	0402	CRCW040210R0FKED	4	Vishay-Dale
RES, 1.00 k, 1%, 0.063 W, 0402	R17, R20	0402	CRCW04021K00FKED	2	Vishay-Dale
RES, 1.0, 5%, 0.063 W, 0402	R21	0402	CRCW04021R00JNED	1	Vishay-Dale
RES, 20.0, 1%, 0.063 W, 0402	R28	0402	CRCW040220R0FKED	1	Vishay-Dale
RES, 26.7 k, 1%, 0.063 W, 0402	R29	0402	CRCW040226K7FKED	1	Vishay-Dale
RES, 549 k, 1%, 0.063 W, 0402	R31	0402	CRCW0402549KFKED	1	Vishay-Dale
RES, 10 ohm, 5%, 0.25W, 0603	R34, R39, R42, R47, R49, R55, R58, R63	0603	CRCW060310R0JNEAHP	8	Vishay-Dale
RES, 4.7k ohm, 5%, 0.1W, 0603	R35, R40, R41, R43, R44, R45, R46, R50, R56, R57, R59, R60, R61, R	0603	CRCW06034K70JNEA		Vishay-Dale
RES, 22 ohm, 5%, 0.1W, 0603	R36, R51	0603	CRCW060322R0JNEA	2	Vishay-Dale
RES, 0, 5%, 0.1 W, 0603	R37, R52	0603	CRCW06030000Z0EA	2	Vishay-Dale

RES, 1.0 k, 5%, 0.063 W, 0402	R48, R54, R78	0402	CRCW04021K00JNED	3 Vishay-Dale
RES, 10 k, 5%, 0.1 W, 0603	R64, R69	0603	CRCW060310K0JNEA	2 Vishay-Dale
RES, 5.1 k, 5%, 0.1 W, 0603	R65, R70	0603	CRCW06035K10JNEA	2 Vishay-Dale
RES, 68 k, 5%, 0.1 W, 0603	R66, R72	0603	CRCW060368K0JNEA	2 Vishay-Dale
RES, 3.3 k, 5%, 0.1 W, 0603	R67, R68	0603	CRCW06033K30JNEA	2 Vishay-Dale
RES, 47.0, 0.5%, 0.1 W, 0603	R71	0603	RT0603DRE0747RL	1 Yageo America
RES, 150 k, 1%, 0.1 W, 0603	R73, R74	0603	CRCW0603150KFKEA	2 Vishay-Dale
50 MHz, Low-Noise Single-Supply Rail-to-Rail Operational Amplifier, 2.2 to 5	U1, U2, U3, U4, U5	D0008A_N	OPA2365AIDR	5 Texas Instruments
40-ns, microPOWER, Push-Pull Output Comparators, DBV0005A	U6	DBV0005A_N	TLV3201AIDBVR	1 Texas Instruments
3.3V-Supply RS-485 with IEC ESD Protection, D0008A	U7, U8, U10, U11	D0008A_N	SN65HVD78D	4 Texas Instruments
5.5-V, 2-A, 54mohm On-Resistance Load Switch, DBV0006A (SOT-23-6)	U9, U15	DBV0006A_N	TPS22918QDBVRQ1	2 Texas Instruments
2.2 nV/rtHz, 18 MHz, Precision, RRO, Operational Amplifier, 4.5 to 36 V, -40 t	dU12	D0008A_N	OPA2209AIDR	1 Texas Instruments
Low-Drift, Low-Power, Dual-Output, VREF and VREF / 2 Voltage References,	CU13	DDC0005A_N	REF2033AIDDCR	1 Texas Instruments
Single Output LDO, 300 mA, Fixed 3.3 V Output, 2 to 5.5 V Input, with Low IC	2U14	DBV0005A_N	TLV70233DBVR	1 Texas Instruments

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated