Bill of Materials

TI DESIGNS TIDA-00476 REV E1 High Efficient, Versitile Bi-Directional Power Converter for Energy Storage and DC Home Solutions

Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
1	!PCB1	Printed Circuit Board	Any	TIDA-00476	Fitted
3	C1, C2, C3	CAP, AL,390 μF, 63 V, +/- 20%, 0.043 ohm, TH	Chemi-Con	EKYB630ELL391MJ30S	Fitted
4	C4, C10, C12, C14	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0805	AVX	08053C104KAT2A	Fitted
1	C5	CAP, CERM, 220 pF, 100 V, +/- 5%, COG/NP0, 0805	MuRata	GRM2165C2A221JA01D	Not-Fitted
8	C6, C9, C15, C16, C17, C18, C19, C20	CAP, CERM, 1uF, 50V, +/-10%, X7R, 0805	AVX	08055C105KAT2A	Fitted
1	C7	CAP, CERM, 1000 pF, 100 V, +/- 5%, COG/NP0, 0805	MuRata	GRM2195C2A102JA01D	Fitted
1	C8	CAP, CERM, 10 μF, 10 V, +/- 20%, X5R, 0603	TDK	C1608X5R1A106M	Fitted
2	C11, C13	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0805	AVX	08055C222KAT2A	Fitted
1	C21	CAP, CERM, 0.1 μF, 16 V, +/- 5%, X7R, 0603	AVX	0603YC104JAT2A	Fitted
1	C22	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0805	AVX	08055C102KAT2A	Fitted
1	C23	CAP, AL, 47 μF, 35 V, +/- 20%, 0.4 ohm, TH	Rubycon	35ZLJ47MTA5X11	Fitted
1	C24	CAP, AL, 100 μF, 16 V, +/- 20%, TH	Rubycon	16PX100MEFCTA5X11	Fitted
1	C25	CAP, CERM, 100 pF, 25 V, +/- 10%, X7R, 0603	AVX	06033C101KAT2A	Fitted
2	D1, D5	Diode, Switching, 75 V, 0.3 A, SOD-523	Micro Commercial Components	1N4148X-TP	Fitted
1	D2	Diode, Zener, 36 V, 500 mW, SOD-123	Vishay-Semiconductor	MMSZ4715-V	Fitted
2	D3, D11	Diode, Schottky, 45 V, 0.75 A, SOD-523	Infineon Technologies	BAS 52-02V H6327	Fitted
1	D4	Diode, Schottky, 70 V, 0.07 A, SOT-23	Diodes Inc.	BAS70-05-7-F	Fitted
3	D6, D7, D10	Diode, Schottky, 80 V, 0.5 A, SOD-123	Micro Commercial Components	MBR0580-TP	Fitted
1	D8	Diode, Zener, 5.61 V, 500 mW, SOD-523	ON Semiconductor	MM5Z5V6ST1G	Fitted
1	D9	Diode, Zener, 9.1 V, 500 mW, SOD-123	Vishay-Semiconductor	MMSZ4696-V	Fitted
6	FID1, FID2, FID3, FID4, FID5, FID6	Fiducial mark. There is nothing to buy or mount.	N/A	N/A	Fitted
4	H1, H2, H3, H4	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	B&F Fastener Supply	NY PMS 440 0025 PH	Fitted
3	J1, J2, J3	Terminal Block, 2x1, 5.08mm, TH	TE Connectivity	282841-2	Fitted
1	J4	Header, TH, 100mil, 8x1, Gold plated, 230 mil above insulator	Samtec	TSW-108-07-G-S	Fitted
2	J5, J8	Header, 100mil, 3x1, Tin, TH	TE Connectivity	5-146278-3	Fitted
1	J6	Header, 100mil, 4x1, Tin, TH	TE Connectivity	5-146278-4	Fitted
1	L1	Inductor, Shielded Drum Core, Ferrite, 47 μH, 6.8 A, 0.0335 ohm, SMD	Wurth Elektronik eiSos	74435574700	Fitted
1	L2	Ferrite Bead, 30 ohm @ 100MHz, 1.5A, 0805	TDK	MMZ2012R300A	Fitted
1	L3	Inductor, Shielded Drum Core, Ferrite, 22 μH, 4 A, 0.04 ohm, SMD	Coilcraft	MSS1278-223MLB	Not-Fitted
1	L4	Inductor, Shielded Drum Core, Ferrite, 22 μH, 11 A, 0.0146 ohm, SMD	Wurth Elektronik eiSos	74435572200	Not-Fitted
1	L5	Inductor, Wirewound, Ferrite, 100 μH, 0.4 A, 1.596 ohm, SMD	Bourns	SRN4018-101M	Not-Fitted
1	L6	Inductor, Wirewound, Ferrite, 47 μH, 0.4 A, 1.4 ohm, SMD	Bourns	SRN3015-470M	Fitted
1	LBL1	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	Brady	THT-14-423-10	Fitted
3	Q1, Q2, Q3	MOSFET, N-CH, 60V, 6.3A, SO-8	Texas Instruments	CSD88539ND	Fitted

Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
2	Q6, Q7	Transistor, PNP, 65 V, 0.1 A, SOT-23	Diodes Inc.	BC856B-7-F	Fitted
2	Q8, Q10	Transistor, NPN, 40V, 0.2A, SOT-23	Fairchild Semiconductor	MMBT3904	Fitted
11	R1, R2, R13, R14, R41, R42, R43, R44, R45, R47, R52	RES, 2.05k ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW08052K05FKEA	Fitted
6	R3, R10, R22, R23, R30, R31	RES, 33.2k ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080533K2FKEA	Fitted
1	R4	RES, 5.1, 5%, 0.125 W, 0805	Yageo America	RC0805JR-075R1L	Fitted
1	R9	RES, 10.0 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080510R0FKEA	Fitted
2	R5, R6	RES, 0.02, 1%, 0.5 W, 1206	Stackpole Electronics Inc	CSR1206FK20L0	Fitted
2	R7, R58	RES, 10, 5%, 0.5 W, 1206	Vishay-Dale	CRCW120610R0JNEA	Fitted
1	R8	RES, 5.1, 5%, 0.1 W, 0603	Vishay-Dale	CRCW06035R10JNEA	Fitted
2	R11, R12	RES, 0.75, 1%, 0.5 W, 1206	Stackpole Electronics Inc	CSR1206FKR750	Fitted
2	R15, R50	RES, 100 k, 5%, 0.1 W, 0603	Vishay-Dale	CRCW0603100KJNEA	Fitted
1	R16	RES, 2.2 k, 5%, 0.1 W, 0603	Vishay-Dale	CRCW06032K20JNEA	Fitted
4	R17, R19, R26, R27	RES, 100k ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW0805100KFKEA	Fitted
2	R18, R20	RES, 42.2 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW080542K2FKEA	Fitted
1	R24	RES, 24.9 k, 1%, 0.125 W, 0805	Panasonic	ERJ-6ENF2492V	Fitted
1	R28	RES, 4.7 k, 5%, 0.125 W, 0805	Vishay-Dale	CRCW08054K70JNEA	Fitted
3	R29, R34, R36	RES, 7.68 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW08057K68FKEA	Fitted
5	R33, R35, R40, R48, R49	RES, 205 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW0805205RFKEA	Fitted
1	R37	RES, 10k ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW080510K0JNEA	Fitted
1	R39	RES, 200 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW0805200KFKEA	Fitted
1	R46	RES, 9.53 k, 1%, 0.125 W, 0805	Vishay-Dale	CRCW08059K53FKEA	Fitted
2	R51, R54	RES, 4.02 k, 0.1%, 0.125 W, 0805	Yageo America	RT0805BRD074K02L	Fitted
2	R53, R55	RES, 169 k, 0.1%, 0.125 W, 0805	Yageo America	RT0805BRD07169KL	Fitted
1	R56	RES, 12 k, 5%, 0.1 W, 0603	Vishay-Dale	CRCW060312K0JNEA	Fitted
1	R57	RES, 200, 5%, 0.1 W, 0603	Vishay-Dale	CRCW0603200RJNEA	Fitted
1	U1	High Voltage 1A Peak Half Bridge Gate Driver, 8- pin Narrow SOIC, Pb-Free	Texas Instruments	LM5109AMAX/NOPB	Fitted
1	U2	IC, MIXED SIGNAL MICROCONTROLLER	TI	MSP430F5132IDAR	Fitted
1	U3	Single Output LDO, 150 mA, Fixed 3.3 V Output, 2.5 to 24 V Input, with Ultra-Low IQ, 5-pin SOT- 23 (DBV), -40 to 125 degC, Green (RoHS & no Sb/Br)	Texas Instruments	TLV70433DBVR	Fitted
1	U4	IC, 36V, Single-Supply, Op Amp	TI	OPA170AIDBV	Fitted
1	U5	700-V Lowest Quiescent Current Off-Line Switcher, D0007A	Texas Instruments	UCC28880DR	Fitted

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated