Variant: 001

Generated: 2/27/2018 12:39:22 PM

TID #: TIDA-01002

## TEXAS INSTRUMENTS

## **TIDA-01002 REV E3 Bill of Materials**

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		TIDA-01002	Any	Printed Circuit Board	
C2, C6, C9, C36	4	0.1µF	C1005X7R1E104K050BB	TDK Corporation	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0402	0402 (1005 Metric)
C3, C12, C35	3	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1 µF, 10 V, +/- 10%, X5R, 0402	0402
C4, C19, C23,	7	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0402	0402
C25, C27, C28,						
C37						
C5, C8, C11, C30	4	10uF	GRM21BR71A106KE51L	MuRata	CAP, CERM, 10uF, 10V, +/-10%, X7R, 0805	0805
C7, C10, C13,	8	0.01uF	GRM155R71C103KA01D	MuRata	CAP, CERM, 0.01uF, 16V, +/-10%, X7R, 0402	0402
C16, C20, C24,						
C26, C29						
C14	1	4.7uF	JMK107BB7475MA-T	Taiyo Yuden	CAP, CERM, 4.7 µF, 6.3 V, +/- 10%, X7R, 0603	0603
C15	1	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
C17, C21	2	0.1uF	C1005X7R1H104K	TDK	CAP, CERM, 0.1uF, 50V, +/-10%, C0G/NP0, 0402	0402
C18, C22	2	4.7µF	CL10B475KQ8NQNC	Samsung Electro-Mechanics	CAP CER 4.7UF 6.3V 10% X7R 0603	0603 (1608 Metric)
·		·		America, Inc		,
C31, C32	2	10uF	CL21B106KOQNNNE	Samsung Electro-Mechanics	CAP, CERM, 10 µF, 16 V, +/- 10%, X7R, 0805	0805
·					•	
C33	1	10uF	GRM21BR71A106KE51L	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, 0805	0805
C34	1	4.7uF	GRM188Z71C475KE21D	MuRata		0603
J1	1		59S10H-40ML5-Z	Rosenberger		SMA Connector
L1, L2, L7, L8, L9	5	1000 ohm	BLM15AX102SN1D	MuRata		0402
L3	1	4.7uH	CBC3225T4R7MR	Taiyo Yuden		3.2x2.5x2.5mm
L4	1	100uH	CBC3225T101MR			3.2x2.5x2.5mm
L10	1	10uH	74479887310A	Wurth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 10 µH, 0.125 A, 0.3	2.5x1x2mm
					ohm, SMD	
L11	1	2.2uH	74479775222	Wurth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 2.2 µH, 0.5 A, 0.23	2x1.2x1mm
					ohm, SMD	
R1, R2	2	2.00k	CRCW04022K00FKED	Vishay-Dale	RES, 2.00 k, 1%, 0.063 W, 0402	0402
R3, R6, R20	3	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
R4, R5, R7, R8	4	3.3k	CRCW04023K30JNED	Vishay-Dale	RES, 3.3 k, 5%, 0.063 W, 0402	0402
R9, R11, R17	3	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402	0402
R12	1	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9 ohm, 1%, 0.063W, 0402	0402
R13	1	33	CRCW040233R0JNED	Vishay-Dale	RES, 33 ohm, 5%, 0.063W, 0402	0402
R15, R16	2	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10k ohm, 5%, 0.063W, 0402	0402
R18	1	4.70k	CRG0402F4K7	TE Connectivity	RES, 4.70 k, 1%, 0.063 W, 0402	0402
R21, R25	2	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
R22	1	82.5k	CRCW040282K5FKED	Vishay-Dale	RES, 82.5 k, 1%, 0.063 W, 0402	0402
R23	1	33.2k	CRCW040233K2FKED	Vishay-Dale	RES, 33.2 k, 1%, 0.063 W, 0402	0402
U1	1		DS90UB913ATRTVTQ1	Texas Instruments	DS90UB913A-Q1/DS90UB914A-Q1 25 to 100 MHz 10/20-Bit FPD-Link	RTV0032A
					III Serializer and Deserializer, RTV0032A	
U2	1		AS0140	ON Semiconductor	1MP+ISP Single Package Solution, BGA130	BGA, 8.5x8.5mm,
						130 Balls
U3	1		TPS62170QDSGRQ1	Texas Instruments	3-V to17-V 0.5-A Step-Down Converters with DCS-Control™, DSG0008A	
					, , , , , , , , , , , , , , , , , , , ,	
U4	1		TPS62171QDSGRQ1	Texas Instruments	3-V to 17-V, 0.5-A Step-Down Converter with DCS-Control. DSG0008A	DSG0008A
Y1	1		ASDMB-48.000MHZ-LY-T			2.5x2mm
FID1, FID2, FID3.	0		N/A	N/A		Fiducial
FID4, FID5, FID6						
	PCB1	PCB1	PCB1	PCB1	FCB1	FOBT

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated