

## PMP30092 REV B Bill of Materials

## DNP=DO NOT POPULATE

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C2	1	0.33uF	B32922C3334M	TDK	CAP, Film, 0.33 µF, 630 V, +/- 20%, TH	B32922 14.5mm
C3	1	DNP	DNP	Nichicon	CAP, AL, 27 μF, 400 V, +/- 20%, TH	12.5x20mm
C4	1	270uF	LGW2G271MELB35	Nichicon	CAP, AL, 270 μF, 400 V, +/- 20%, TH	D30xL35mm
C5	1	10pF	12062A100JAT2A	AVX	CAP, CERM, 10 pF, 200 V, +/- 5%, C0G/NP0, 1206	1206
C6, C7	2	680uF	UHW1V681MPD6	Nichicon	CAP, AL, 680 μF, 35 V, +/- 20%, 0.019 ohm, TH	TH, 2-Leads,
, -					- , ,,,	10.5x22mm, Pin
						Spacing 5mm
C8	1	470uF	UHW1V471MPD	Nichicon	CAP, AL, 470 µF, 35 V, +/- 20%, 0.03 ohm, TH	D10xL16mm
C9	1	1uF	C3216X7R1H105K160AB	TDK	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 1206	1206
C10	1	1000pF	GRM31BR72J102KW01L	MuRata	CAP, CERM, 1000 pF, 630 V, +/- 10%, X7R, 1206	1206
C11	1	33uF	EEE-FC1V330P	Panasonic	CAP, AL, 33 µF, 35 V, +/- 20%, 0.4 ohm, SMD	SMT Radial E
C12	1	1uF	C1206C105K3RACTU	Kemet	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 1206	1206
C13	1	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C14	1	DNP	Used in BOM report	Used in BOM report	CAP, [Technology], xxxF, xxV, +/-xx%, xxOhm ESR, [MountType]	Used in PnP output
• • •						and some BOM
						reports
C15	1	0.1uF	08055C104KAT2A	AVX	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0805	0805
C16	1	150pF	C0603C151J5GACTU	Kemet	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C17	1	3300pF	DE1E3KX332MN4AP01F	MuRata	CAP, CERM, 3300 pF, 300 V, +/- 20%, E, D10xT7mm	D10xT7mm
C101	1	DNP	GRM31BR72J102KW01L	MuRata	CAP, CERM, 1000 pF, 630 V, +/- 10%, X7R, 1206	1206
D1	1	600V	GBU606	Diodes Inc.	Diode, Switching-Bridge, 600 V, 6 A, TH	GBU
D2	1	85V	SMCJ85A	Littelfuse	Diode, TVS, Uni, 85 V, 1500 W, SMC	SMC
D3	1	100V	SMCJ100A	Littelfuse	Diode, TVS, Uni, 100 V, 1500 W, SMC	SMC
D4	1	600V	MURS160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 2 A, SMB	SMB
D5	1	30V	MMSZ5255B-7-F	Diodes Inc.	Diode, Zener, 30 V, 500 mW, SOD-123	SOD-123
D6, D7	2	1000V	1N4007	Fairchild Semiconductor	Diode, P-N, 1000 V, 1 A, TH	DO-41
D8	1	100V	ES1B-13-F	Diodes Inc.	Diode, Superfast Rectifier, 100 V, 1 A, SMA	SMA
D9	1	1001	BAS316.115	NXP Semiconductor	Diode, Ultrafast, 100 V, 0.25 A, SOD-323	SOD-323
D10	1	200V	MBR20200CTTU	Fairchild Semiconductor	Diode, Schottky, 200 V, 10 A, TH	TO-220AB
D11	1	70V	BAV70-E3-08	Vishay-Semiconductor	Diode, Switching, 70 V, 0.25 A, AEC-Q101, SOT-23	SOT-23
F1	1		37213150001	Littelfuse	Fuse, 3.15 A, 250VAC/VDC, TH	TR5 fuse 8.5mm DIA
H1	1		SK 178 30 SA	Fischer	HEATSINK, Fischer, 7K/W	35x16x30mm
H2, H3	2		V6560X	Assman WSW	HEATSINK, ALUM, ANOD, for TO-220	29x12mm
H4	1		573300D00010G	Aavid	Heatsink, DDPAK/TO-263, SMT	Heatsink, DDPAk
L1, L3	2	47uH	DO5040H-473MLB	Coilcraft	Inductor, Drum Core, Ferrite, 47 µH, 3.7 A, 0.05 ohm, SMD	DO5040H
L2	1	10mH	744825510	Wurth Elektronik	Coupled inductor, 10 mH, 5 A, 0.055 ohm, TH	30x35x21mm
 L101	1	1mH	744823601	Wurth Elektronik	Coupled inductor, 1 mH, 6 A, 0.013 ohm, TH	13x22x17.5mm
Q1	1	800V	IPA80R650	Infineon Technologies	MOSFET, N-CH, 800 V, TO-220AB	TO-220AB
Q2	1	DNP	DNP	ON Semiconductor	Transistor, PNP, 150 V, 0.5 A, SOT-23	SOT-23
R1	1	20	CRCW251220R0JNEG	Vishay-Dale	RES, 20, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
R2	1	20.0k	RC0603FR-0720KL	Yageo America	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R3	1	10.0	CRCW080510R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.125 W, 0805	0805
R4, R7	2	100k	CRCW1206100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.25 W, 1206	1206
R5	1	4.99	RC0805FR-074R99L	Yageo America	RES, 4.99, 1%, 0.125 W, 0805	0805
R6	1	1k	STD	Vishay-Dale	RES, 1k, 5%, 0.125 W, 0805	0805
R8	1	47	ERJ-6GEYJ470V	Panasonic	RES, 47, 5%, 0.125 W, 0805	0805
		1				

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R9	1	DNP	DNP	Vishay-Dale	RES, 100, 1%, 0.125 W, 0805	0805
R10	1	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R11	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R12	1	24.3k	CRCW060324K3FKEA	Vishay-Dale	RES, 24.3 k, 1%, 0.1 W, 0603	0603
R13	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R14	1	3.92k	CRCW06033K92FKEA	Vishay-Dale	RES, 3.92 k, 1%, 0.1 W, 0603	0603
R15, R16	2	0.3	CSRN2512FKR300	Stackpole Electronics Inc	RES, 0.3, 1%, 2 W, 2512	2512
R17	1	30.9k	CRCW060330K9FKEA	Vishay-Dale	RES, 30.9 k, 1%, 0.1 W, 0603	0603
R18	1	10pF	Used in BOM report	Used in BOM report	Cap, COG, 0603	Used in PnP output
						and some BOM
						reports
R19	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
RT1	1	470k ohm	NCP18WM474J03RB	MuRata	Thermistor NTC, 470k ohm, 5%, 0603	0603
RV1	1	430V	B72214S0271K101	TDK	Varistor, 430V, 4.5KA, TH	Disc, 14x5mm
T1	1	250uH	750316326R01	Wurth Elektronik	Transformer, 250 uH, TH	TH, 14-Leads, Body
						44x36.5mm, Pitch
						5mm
TP1, TP2, TP3,	4		1503-2	Keystone	Terminal, Turret, TH, Double	Keystone1503-2
TP4						
U1	1		UCC28633DR	Texas Instruments	High-Power Flyback Controller with Primary-Side Regulation and Peak-	D0007A
					Power Mode, D0007A	
U2	1		UCC24650DBVR	Texas Instruments	200-V Wake-Up Monitor for Fast Transient PSR, DBV0005A	DBV0005A

## **IMPORTANT NOTICE FOR TI REFERENCE DESIGNS**

Texas Instruments Incorporated ('TI') reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<u>http://www.ti.com/sc/docs/stdterms.htm</u>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated