

PMP40347 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	470uF	16SEPC470M+T	Panasonic	CAP, Aluminum Polymer, 470 µF, 16 V, +/- 20%, 0.01 ohm, TH	D10xL13mm
C2, C3, C30, C34	4	47uF	C3216X5R1E476M160AC	TDK	CAP, CERM, 47 μF, 25 V, +/- 20%, X5R, 1206_190	1206_190
C4	1	470pF	06035A471JAT2A	AVX	CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C5	1	330pF	GRM31A5C2J331JW01D	MuRata	CAP, CERM, 330 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
C6, C13	2	330uF	EEU-FR1E331B	Panasonic	CAP, AL, 330 μF, 25 V, +/- 20%, TH	D8xL13
C7	1	330uF	25SEPF330M	Panasonic	CAP, Aluminum Polymer, 330 µF, 25 V, +/- 20%, 0.014 ohm, TH	D10xL13mm
C8	1	220uF	860020373010	Wurth Electronics Inc.	CAP, AL, 220 μF, 16 V, +/- 20%, TH	Radial, Can
C9, C11, C17, C18	4	22uF	860241378003	Wurth Elektronik	CAP, AL, 22 μF, 400 V, +/- 20%, TH	D13xL20mm
C10, C15	2	100pF	06035A101JAT2A	AVX	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C21	1	33uF	UVR1E220MDD6TP	Nichicon	CAP, AL, 33 μF, 25 V, +/- 20%, TH	D5xL11mm
C22	1	1000pF	GRM188R71E102KA01D	MuRata	CAP, CERM, 1000 pF, 25 V, +/- 10%, X7R, 0603	0603
C23	1	0.047uF	C1608X7R1H473K080AA	TDK	CAP, CERM, 0.047 µF, 50 V, +/- 10%, X7R, 0603	0603
C24, C32, C33	3	0.1uF	06033D104KAT2A	AVX	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X5R, 0603	0603
C25	1	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C26	1	10uF	C1608X5R1A106M080AC	TDK	CAP, CERM, 10 µF, 10 V, +/- 20%, X5R, 0603	0603
C27	1	0.01uF	C1608NP01H103J080AA	TDK	CAP, CERM, 0.01 µF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C28	1	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C29	1	1uF	C0603C105K3RACTU	Kemet	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C14	1	0.1uF	06033C104KAT2A	AVX	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	0603
C31	1	2200pF	DE1E3RA222MA4BP01F	MuRata	CAP, CERM, 2200 pF, 500 V, +/- 20%, E, Disc 10x8mm	Disc 10x8mm
D1	1	100V	MURA210T3G	ON Semiconductor	DIODE GEN PURP 100V 2A SMA	DO-214AC, SMA
D2	1	200V	BAS20HT1G	ON Semiconductor	Diode, Switching, 200 V, 0.2 A, AEC-Q101, SOD-323	SOD-323
D3, D5, D6, D7, D8, D10, D11, D12	8	1000V	MRA4007T3G	ON Semiconductor	Diode, Standard Recovery Rectifier, 1000 V, 1 A, AEC-Q101, SMA	SMA
D4	1	150V	SK215ATR	SMC Diode Solutions	Diode, Schottky, 150 V, 2 A, SMA	SMA
D9	1	45pF	ES3C-13-F	Diodes	DIODE GEN PURP 150V 3A SMC	
D13	1	1000V	RS1M-13-F	Diodes Inc.	Diode, P-N, 1000 V, 1 A, SMA	SMA
D15	1	15V	MMSZ4702T1G	ON Semiconductor	Diode, Zener, 15 V, 500 mW, SOD-123	SOD-123
D16	1	400V	P6KE400A	Fairchild Semiconductor	Diode, TVS, Uni, 400 V, 482 Vc, DO-15	DO-15
F1	1		39213150000	Littelfuse	Fuse, 3.15 A, 250VAC/VDC, TH	8x8.5x4mm
L1	1	220uH	7447462221	Wurth Elektronik	Inductor, Unshielded Drum Core, Ferrite, 220 µH, 0.5 A, 0.96 ohm, TH	D6 x 8.5mm
L2	1	10uH	XAL4040-103MEB	Coilcraft	Inductor, Shielded, Composite, 10 µH, 3 A, 0.084 ohm, SMD	4.0x4.1x4.0mm
L4	1		7447462010	Wurth Electronics Inc.	FIXED IND 1UH 8.5A 15 MOHM TH	Radial
L6	1	22uH	78438335220	Wurth Elektronik	Inductor, Shielded, Powdered Iron, 22 µH, 0.6 A, 1.04 ohm, AEC-Q200 Grade 1, SMD	SMD, 2-Leads, Body 3x3mm
Q1	1	40 V	MMBT3904LT1G	ON Semiconductor	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
Q2, Q4	2		STD2HNK60Z-1	STMicroelectronics	MOSFET N-CH 600V 2A IPAK	TO-251-3 Short Leads, IPak, TO- 251AA
R1, R11, R22, R25	4	1.00Meg	CRCW12061M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.25 W, 1206	1206

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R2, R3, R15, R20,	8	240k	CRCW1206240KJNEA	Vishay-Dale	RES, 240 k, 5%, 0.25 W, 1206	1206
R23, R27, R28,						
R46						
R4	1	1.50Meg	CRCW06031M50FKEA	Vishay-Dale	RES, 1.50 M, 1%, 0.1 W, 0603	0603
R5	1	10.0k	CRCW080510K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.125 W, 0805	0805
R6, R7	2	51.0	RC1206FR-0751RL	Yageo America	RES, 51.0, 1%, 0.25 W, 1206	1206
R8	1	330k	CRCW1206330KJNEA	Vishay-Dale	RES, 330 k, 5%, 0.25 W, 1206	1206
R9, R29	2	1.10k	CRCW12061K10FKEA	Vishay-Dale	RES, 1.10 k, 1%, 0.25 W, 1206	1206
R12, R13	2	0	ERJ-6GEY0R00V	Panasonic	RES, 0, 5%, 0.125 W, 0805	0805
R16, R31, R32,	6	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R33, R41, R44	ŭ	10.01	11.00000111 07 10112	Tagos / inionea	1,25, 1010 11, 170, 011 11, 0000	
R18	1	560	CRCW0603560RJNEA	Vishay-Dale	RES, 560, 5%, 0.1 W, 0603	0603
R19, R49	2	51.0k	RC0603FR-0751KL	Yageo America	RES, 51.0 k, 1%, 0.1 W, 0603	0603
R21, R45	2	110k	CRCW0603110KFKEA	Vishay-Dale	RES, 110 k, 1%, 0.1 W, 0603	0603
R24, R35	2	10	CRCW080510R0JNEA	Vishay-Dale Vishay-Dale	RES, 10, 5%, 0.125 W, 0805	0805
R34	1	75	CRCW080575R0JNEA	Vishay-Dale Vishay-Dale	RES, 75, 5%, 0.125 W, 0805	0805
R36, R37	2	2.20	ERJ-6RQF2R2V	Panasonic	RES, 2.20, 1%, 0.125 W, 0805	0805
R38	1	1.60k	RC0603FR-071K6L	Yageo America	RES, 1.60 k, 1%, 0.1 W, 0603	0603
R39	1	3.0k	CRCW12063K00JNEA	Vishay-Dale	RES, 3.0 k, 5%, 0.25 W, 1206	1206
R40	1	5.1k	RC0805FR-075K1L	·	RES, 5.1 k, 1%, 0.125 W, 0805	0805 (2012 Metric)
R42	1			Yageo America		0603 (2012 Wetric)
	1	470	RC0603FR-07470RL	Yageo America	RES, 470, 1%, 0.1 W, 0603	
R43	1	56.0K	CDCW420C4C0KINEA	Yageo America	RES, 56.0k, 1%, 0.1 W, 0603	0603
R47	1	160k	CRCW1206160KJNEA	Vishay-Dale	RES, 160 k, 5%, 0.25 W, 1206	1206
R48	1	10	CRCW120610R0JNEA	Vishay-Dale	RES, 10, 5%, 0.25 W, 1206	1206
RF1, RF2, RF3	3	4.7	FKN1WSJR-52-4R7	Yageo America	RES, 4.7, 5%, 1 W, Axial resistor	Axial resistor
T2	1		7503433972	Wurth Elektronik	Transformer, Flyback	EE20
U1	1		LP2992AIM5-5.0/NOPB	Texas Instruments	Micropower 250 mA Low-Noise Ultra Low-Dropout Regulator, 5-pin SOT-23	MF05A
U3, U7	2		TPS560430XFDBVR	Texas Instruments	4V to 36 V 0.6 A Synchronous Step-Down Converter, DBV0006A (SOT-23-6)	DBV0006A
U4	1		LTV-817S	Lite-On	Optocoupler, 5 kV, 50-600% CTR, SMT	DIP-4 SMT
U5	1		TL431AIDBZT	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U6	1		UCC28600D	Texas Instruments	Quasi-Resonant Flyback Green-Mode Controller with Current Control, 99 % Duty Cycle, -40 to +105 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	D0008A
R10	0	330k	CRCW1206330KJNEA	Vishay-Dale	RES, 330 k, 5%, 0.25 W, 1206	1206
R26	0	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
RV1, RV2, RV3	0	470V	Used in BOM report	Used in BOM report	Varistor, xxxVAC, xxVDC, xxJ, [Diameter], [Package]	Used in PnP output and some BOM reports
C12	0	2200pF	DE1E3RA222MA4BP01F	MuRata	CAP, CERM, 2200 pF, 500 V, +/- 20%, E, Disc 10x8mm	Disc 10x8mm
TP1, TP2, TP3, TP4	0	=	5005	Keystone	Test Point, Compact, Red, TH	Red Compact Testpoint
	i	1	i e	i		1 . 20tpon t

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated