

**COP820CJ,COP840CJ,COP880C,COP884BC,
COP888CF,COP888CL,COP888EK,COP888FH,
COP888GW,COP8ACC5,COP8AME9,COP8CBE9,
COP8CBR9,COP8CCE9,COP8CCR9,COP8CDR9,
COP8SAA7,COP8SAC7,COP8SBR9,COP8SCR9,
COP8SDR9,COP8SGE5,COP8SGE7,COP8SGG5,
COP8SGH5,COP8SGK5,COP8SGR5,COP8SGR7,
COP912C,DS3658**

AN-714 Using COP800 Devices to Control DC Stepper Motors



Literature Number: SNLA019

Using COP800 Devices to Control DC Stepper Motors

National Semiconductor
Application Note 714
Michelle Giles
September 1990



Using COP800 Devices to Control DC Stepper Motors

INTRODUCTION

COP800 devices can be used to control DC stepper motors with limited effort. This application note describes the use of a COP820 to control the speed, direction and rotation angle of a stepper motor. In addition to the COP820, this application requires a quad high current peripheral driver (DS3658) to meet the high current needs of the stepper motor.

DC STEPPER MOTOR

A DC stepper motor translates current pulses into rotor movement. A typical motor contains four winding coils labeled red, yellow/white, red/white, and yellow. Applying current to these windings forces the motor to step. For normal operation, two windings are activated (pulsed) concurrently. The motor moves clockwise one step per change in windings activated with the following activation sequence: red and yellow, yellow and red/white, red/white and yellow/white, yellow/white and red, repeat. Half-steps may be generated by altering the sequence to: red and yellow, yellow, yellow and red/white, red/white, red/white and yellow/white, yellow/white, yellow/white and red, red, repeat. The motor runs in a counterclockwise direction if either sequence is applied in reverse order. The speed of rotation (number of steps/second) is controlled by the frequency of the pulses.

COP820 CONTROL OF STEPPER MOTOR

The COP820 controls the stepper motor by sending pulse sequences to the motor windings in response to control commands. Commands executed by the code in this application include: single step the motor in a clockwise or counterclockwise direction (i.e. rotate the rotor through a certain number of degrees), run the motor continuously at one of four speeds in a clockwise or counterclockwise direction, and stop the motor.

Note: Half-stepping is not implemented in this example.

During continuous mode operation, the 16-bit timer of the COP820 is used to control the speed of the stepper motor. The timer is set up with a value that causes an underflow once every x seconds or at a frequency of $1/x$. Each underflow of the timer interrupts the microcontroller. In response to the timer interrupt, the microcontroller generates a new pulse and causes a single step of the motor. Thus the motor steps at the frequency of the timer underflows. This application sets up the timer to generate interrupts at four different frequencies. These frequencies produce the following motor speeds: 25 steps/second, 100 steps/second, 200 steps/second, and 400 steps/second.

The determination of which windings to activate and deactivate to step the motor is performed by a single subroutine in this example. A block of memory is allocated to store a step pointer and the four possible stepper drive values are shown in Table I (9,C,6,3). Consecutive memory locations are used to store the stepper drive values so that applying the value from location X and then location $X+1$ (or $X-1$) causes the motor to step once. The motor drive subroutine increments or decrements the pointer to the current drive value based on the selection of a clockwise or counterclockwise direction. Writing the value from the newly selected location to the motor causes a single step of the motor in the appropriate direction.

During single step operation, the microcontroller steps the motor the exact number of times requested in the control command. Each step corresponds to 1.8 degrees of rotor movement. Therefore, a request to perform 200 steps will rotate the rotor through one complete revolution (360 degrees) at a fixed speed.

A block diagram of the application is shown in *Figure 1*. A flowchart of the code used to control the motor is given in *Figure 2*. The complete code is given at the end.

TABLE I. Stepper Motor Drive Sequence

Step	Yellow	Red/White	Yellow/White	Red	Hex Value
0	ON	OFF	OFF	ON	9
1	ON	ON	OFF	OFF	C
2	OFF	ON	ON	OFF	6
3	OFF	OFF	ON	ON	3
4	ON	OFF	OFF	ON	9

AN-714




FIGURE 1. Schematic Diagram

TL/DD/11044-1




FIGURE 2. Program Flowchart

TL/DD/11044-2

```

1          ;STEPPER MOTOR CONTROL PROGRAM
2          ;MAY 1990
3          ;
4          ;This program controls the speed, direction, and degree of rotation of
5          ;a DC stepper motor.
6          ;
7          ;
8          ; Memory Map
9          ; RAM CONTENTS
10         ; 00 (MS0) step motor drive value 09H (two windings active per pulse)
11         ; 01 (MS1) step motor drive value 0CH
12         ; 02 (MS2) step motor drive value 06H
13         ; 03 (MS3) step motor drive value 03H
14         ; 04 (CMD) control command
15         ; bit7 - bit4 = motor speed or upper nibble of # single steps
16         ; bit 3 = unused
17         ; bit 2 = (MODE) single step or continuous mode select (1 = ss)
18         ; bit 1 = (DIR) cw or ccw direction select (1 = cw)
19         ; bit 0 = (GO) motor go or motor stop select (1 = stop)
20         ; 05 (STEPS) lower byte of number of single steps
21         ; 07 (FLGREG) flag register
22         ; bit 0 = (INT) ready to read in cmd (ext int occurred)
23         ; bit1 - bit7 = unused
24         ; 14 (TVAL0) value to load in lower byte of timer for speed X
25         ; 15 (TVAL1) value to load in upper byte of timer for speed X
26         ; D2 (PORTLP) port L input pins used for incoming commands
27         ; D4 (PORTGD) port G data pins used to drive status LEDs
28         ; DC (PORTD) port D data pins used to output pulses to the stepper motor
29         ; F0 (CREG0) step counter register zero
30         ; F1 (CREG1) step counter register one
31         ; F2 (STPPTR) pointer to current step motor drive value (RAM 00 - 03)
32         ;
33         ;REGISTER AND CONSTANT DEFINITIONS
34         ;COMMAND BITS
35         0000 GO = 0 ;GO COMMAND BIT
36         ; 1 = STOP 0 = GO
37         0001 DIR = 1 ;DIRECTION COMMAND BIT
38         ; 1 = CW 0 = CCW
39         0002 MODE = 2 ;MODE COMMAND BIT
40         ; 1 = SINGLE STEP 0 = CONTINUOUS
41         ;
42         ;PORTG BITS
43         0000 INT = 0 ;FLAG BIT (SET IF EXTINT OCCURS)
44         0001 READY = 1 ;READY LED
45         0002 CW = 2 ;CLOCKWISE LED
46         0003 CCW = 3 ;COUNTER CLOCKWISE LED
47         0004 SS = 4 ;SINGLE STEP LED
48         0005 NS = 5 ;CONTINUOUS (NON-STOP) LED
49         ;
50         ;REGISTERS
51         0004 CMD = 04 ;INPUT COMMAND STORAGE REGISTER

```

NATIONAL SEMICONDUCTOR CORPORATION
 COP800 CROSS ASSEMBLER, REV: D1, 12 OCT 88

```

52      0005          STEPS = 05          ;INPUT #STEPS/SPEED REGISTER
53      00F0          CREG0 = 0F0        ;COUNTER REGISTER
54      00F1          CREG1 = 0F1        ;COUNTER REGISTER
55      0007          FLGREG = 07        ;FLAG REGISTER (FLAG BITS)
56      00F2          STPPTR = 0F2       ;CURRENT MOTOR STEP POINTER
57      0014          TVAL0 = 014        ;MOTOR SPEED LOAD VALUES
58      0015          TVAL1 = 015
59      0000          MS0 = 00           ;STEPPER MOTOR DRIVE VALUES
60      0001          MS1 = 01
61      0002          MS2 = 02
62      0003          MS3 = 03
63
64          ;ASSIGNMENTS FOR COP820
65
66      00D5          PORTGC = 0D5
67      00D4          PORTGD = 0D4
68      00D6          PORTGP = 0D6
69      00D1          PORTLC = 0D1
70      00D0          PORTLD = 0D0
71      00D2          PORTLP = 0D2
72      00DC          PORTD = 0DC
73      00D7          PORTI = 0D7
74      00E9          SIOR = 0E9
75      00EA          TMRLO = 0EA
76      00EB          TMRHI = 0EB
77      00EC          TAULO = 0EC
78      00ED          TAUHI = 0ED
79      00EE          CNTRL = 0EE
80      00EF          PSW = 0EF
81
82
83      0000          GIE = 0
84      0001          ENI = 1
85      0002          BUSY = 2
86      0003          IPND = 3
87      0004          ENTI = 4
88      0005          TPND = 5
89
90      0002          IEDG = 2
91      0003          MSEL = 3
92      0004          TRUN = 4
93      0005          TC3 = 5
94      0006          TC2 = 6
95      0007          TC1 = 7
96
97
98          .CHIP      820
99
100     ;INITIALIZATION OF REGISTERS          ;*****
101 0000 DD2F          LD      SP,#02F
102 0002 BCEE80       LD      CNTRL,#080

```

TL/DD/11044-4

NATIONAL SEMICONDUCTOR CORPORATION
COP800 CROSS ASSEMBLER, REV: D1, 12 OCT 88

```

103 0005 BCEF03          LD      PSW,#003          ;GLOBAL INT ENABLE/EXTINT ENABLE
104 0008 BCD401          LD      PORTGD,#01
105 000B BCD53E          LD      PORTGC,#03E      ;CONFIG PORTG FOR OUTPUTS
106 000E BCD009          LD      PORTD,#09        ;START MOTOR DRIVE VALUE
107 0011 BCD100          LD      PORTLC,#00       ;CONFIG PORTL FOR INPUTS
108 0014 BCD0FF          LD      PORTLD,#0FF     ;CONFIG PORTL FOR WEAK PULL-UPS
109 0017 5F              LD      B,#MS0          ;SETUP MOTOR DRIVE VALUES
110 0018 9A09            LD      [B+],#09
111 001A 9A0C            LD      [B+],#0C
112 001C 9A06            LD      [B+],#06
113 001E 9E03            LD      [B],#03
114 0020 D200            LD      STPPTR,#00      ;INIT STEP POINTER
115 0022 BC0700          LD      FLGREG,#00      ;INIT FLAG REGISTER
116
117
118                      ;READ, DECODE, AND EXECUTE COMMAND
119                      ;*****
120 0025 BDD479          TOP:   SBIT   READY,PORTGD ;TURN ON READY FOR NEXT CMD LED
121 0028 3081            JSR    WAIT              ;WAIT FOR CMD AND READ CMD
122 002A BDD469          RBIT   READY,PORTGD    ;TURN OFF READY FOR NEXT CMD LED
123 002D 9C04            X      A,CMD            ;STORE IN CMD REGISTER
124 002F BD0470          IFBIT  GO,CMD          ;IF STOP BIT SET
125 0032 08             JP     STOP             ;THEN STOP MOTOR
126 0033 BD0472          IFBIT  MODE,CMD        ;ELSE CHEK MODE
127 0036 3041            JSR    SSTEP            ;IF MODE SET THEN GO SINGLE STEP
128 0038 305F            JSR    CONT             ;ELSE GO CONTINUOUS
129 003A EA             JP     TOP              ;GO WAIT FOR NEXT COMMAND
130
131 003B 308E            STOP: JSR    TMRSET         ;STOP THE MOTOR
132 003D BCD401          LD      PORTGD,#01     ;STOP THE TIMER
133 0040 E4             JP     TOP              ;TURN OFF ALL LEDS
134
135
136                      ;SINGLE STEP THE MOTOR (SS)
137
138                      ;*****
139 0041 308E            SSTEP: JSR    TMRSET         ;STOP TIMER
140 0043 BCD410          LD      PORTGD,#010    ;TURN ON SS LED (RST ALL OTHER LEDS)
141 0046 3081            JSR    WAIT              ;WAIT FOR CMD BYTE 2 (# STEPS)
142 0048 8A             INC    A                ;ADD 1 TO CORRECT FOR LOOP
143 0049 9CF0            X      A,CREG0          ;STORE #STEPS IN LOBYTE COUNT REG
144 004B 9D04            LD      A,CMD           ;LOAD HIBYTE # STEPS
145 004D 65             SWAP   A                ;MOVE TO LOWER NIBBLE
146 004E 950F            AND    A,#0F           ;GET RID OF UPPER BITS
147 0050 8A             INC    A                ;ADD 1 TO CORRECT FOR LOOP
148 0051 9CF1            X      A,CREG1          ;MOVE TO HIBYTE OF COUNT REG
149 0053 C0             TP2:  DRSZ  CREG0        ;DECR LOBYTE AND IF NOT ZERO
150 0054 05             JP     DO               ;THEN GO DO A STEP
151 0055 C1             MID:  DRSZ  CREG1        ;ELSE DECR HIBYTE AND IF NOT ZERO
152 0056 01             JP     DO2              ;THEN GO DO A STEP AND RST LO COUNT
153 0057 8D             RETSK                    ;ELSE END OF LOOP RETURN

```

TL/DD/11044-5

NATIONAL SEMICONDUCTOR CORPORATION
COP800 CROSS ASSEMBLER, REV: D1, 12 OCT 88

```

154 0058 D0FF      DO2:  LD      CREG0,#0FF      ;RESET LOBYTE OF COUNTER
155 005A 3098      DO:   JSR     NXTVAL      ;STEP THE MOTOR
156 005C 3158      JSR     DELAY      ;SLOW THE STEPPING
157 005E F4        JP      TP2        ;GO TO TOP OF LOOP
158
159
160                ;RUN THE MOTOR CONTINUOUSLY (NS = NON-STOP = CONTINUOUSLY)
161
162                CONT:
163 005F BDEE74      IFBIT   TRUN,CNTRL      ;*****
164 0062 01         JP      CHKSPD      ;IF MOTOR ALREADY RUNNING NS
165 0063 03         JP      SETGO      ;THEN CHECK THE CURRENT SPEED
166 0064 3148      CHKSPD: JSR     SPEED      ;ELSE GO START THE MOTOR
167 0066 8E        RET      ;COMPARE INPUT WITH ACTUAL SPD
168 0067 308E      SETGO:  JSR     TMRSET      ;IF EQUAL RET ELSE RESTART MOTOR
169 0069 BCD420      LD      PORTGD,#020    ;STOP THE TIMER
170 006C 3126      JSR     TIMVAL      ;TURN ON CONTINUOUS LED
171 006E AE        LD      A,[B]        ;CALCULATE TIMER (SPEED) VALUE
172 006F 9CEB      X      A,TMRHI        ;LOAD A WITH TVAL1
173 0071 AB        LD      A,[B-]        ;MOVE SPEED VAL INTO TIMER
174 0072 9CED      X      A,TAUHI        ;LOAD A WITH TVAL1 POINT TO TVAL0
175 0074 AE        LD      A,[B]        ;MOVE SPEED VAL INTO AUTORELOAD REG
176 0075 9CEA      X      A,TMRLO        ;LOAD A WITH TVAL0
177 0077 AE        LD      A,[B]        ;MOVE SPEED VAL INTO TIMER
178 0078 9CEC      X      A,TAULO        ;LOAD A WITH TVAL0
179 007A BDEF7C      SBIT   ENT1,PSW      ;ENABLE TIMER INTERRUPT
180 007D BDEE7C      SBIT   TRUN,CNTRL    ;START THE TIMER
181 0080 8E        RET      ;RET TO MAIN AND WAIT FOR TMRINT
182
183                ;SUPPORT ROUTINES *****
184
185                WAIT:
186                ;WAIT FOR AN EXTERNAL INTERRUPT TO SIGNAL AN INCOMMING COMMAND
187                ;READ THE INCOMMING COMMAND FROM PORT L
188 0081 BD0770      IFBIT   INT,FLGREG      ;IF EXTERNAL INTERRUPT OCCURED
189 0084 01         JP      OUT          ;THEN JUMP OUT OF LOOP
190 0085 FB        JP      WAIT         ;ELSE CONTINUE TO WAIT
191 0086 BD0768      OUT:   RBIT   INT,FLGREG ;RESET EXTERNAL INTERRUPT FLAG
192 0089 9DD2      LD      A,PORTLP      ;READ INCOMMING COMMAND
193 008B 96FF      XOR     A,#0FF        ;COMPLEMENT INCOMMING COMMAND
194 008D 8E        RET      ;RETURN COMMAND IN ACC
195
196
197                TMRSET:
198                ;*****
199 008E BDEE6C      RBIT   TRUN,CNTRL      ;STOP THE TIMER
200 0091 BDEF6D      RBIT   TPND,PSW      ;RESET THE TIMER PENDING BIT
201 0094 BDEF6C      RBIT   ENT1,PSW      ;DISABLE TIMER INTERRUPT
202 0097 8E        RET
203
204

```

TL/DD/11044-6

NATIONAL SEMICONDUCTOR CORPORATION
COP800 CROSS ASSEMBLER, REV: D1, 12 OCT 88

```

205          NXTVAL:          ;*****
206          ;SEND THE NEXT DRIVE VALUE TO STEP THE MOTOR ONE STEP IN THE
207          ;APPROPRIATE DIRECTION (CW OR CCW)
208 0098 9DF2          LD      A,STPPTR          ;LOAD STEP VALUE POINTER
209 009A DED4          LD      B,#PORTGD        ;POINT TO PORT G
210 009C BD0471       IFBIT   DIR,CMD          ;IF CLOCKWISE
211 009F 11           JP      IPTR            ;THEN GO INCREMENT POINTER
212 00A0 6A          DPTR:  RBIT   CW,[B]        ;ELSE RST CW LED
213 00A1 7B          SBIT   CCW,[B]        ;TURN ON CCW LED
214 00A2 8B          DEC     A              ;AND DECREMENT POINTER
215 00A3 92FF       IFEQ   A,#0FF          ;IF OFF BOTTOM OF STEPS
216 00A5 9803       LD      A,#03              ;THEN LOOP TO TOP OF STEPS
217 00A7 9CF2       WRVAL:  X      A,STPPTR        ;A -> STPPTR (SAVE NEW STPPTR)
218 00A9 9DF2       LD      A,STPPTR        ;[STPPTR] -> PORTD (LOOKUP VAL)
219 00AB 9CFE       X      A,B
220 00AD AE         LD      A,[B]
221 00AE 9CDC       X      A,PORTD          ;WRITE STEP VALUE TO MOTOR
222 00B0 8E         RET
223 00B1 6B          IPTR:  RBIT   CW,[B]        ;TURN OFF CCW LED
224 00B2 7A          SBIT   CW,[B]        ;TURN ON CW LED
225 00B3 8A          INC     A              ;INCREMENT THE STEP POINTER
226 00B4 9204       IFEQ   A,#04              ;IF OFF TOP OF STEPS
227 00B6 64         CLR     A              ;THEN LOOP TO BOTTOM OF STEPS
228 00B7 EF         JP      WRVAL          ;GO WRITE VALUE TO MOTOR
229
230
231          ; INTERRUPT HANDLERS
232          . = OFF          ;*****
233          ;BRANCH TO THE APPROPRIATE INTERRUPT HANDLER
234 00FF BDEF75       IFBIT   TPND,PSW          ;TIMER UNDERFLOW
235 0102 08          JP      TMRINT
236 0103 BDEF73       IFBIT   IPND,PSW          ;EXTERNAL INTERRUPT
237 0106 16          JP      EXTINT
238 0107 BDEF78       SBIT   GIE,PSW          ;SOFTWARE TRAP
239 010A 8D          RETSK
240
241          TMRINT:          ;*****
242          ;RESET THE TIMER INTERRUPT PENDING BIT AND STEP THE MOTOR
243 010B 9CF9       X      A,0F9          ;CONTEXT SAVE ROUTINE
244 010D 9DFE       LD      A,B
245 010F 9CFA       X      A,0FA
246 0111 BDEF6D       RBIT   TPND,PSW          ;RESET PENDING BIT
247 0114 3098       JSR   NXTVAL          ;STEP THE MOTOR
248 0116 9DFA       LD      A,0FA          ;CONTEXT RESTORE ROUTINE
249 0118 9CFE       X      A,B
250 011A 9DF9       LD      A,0F9
251 011C 8F         RETI
252
253          EXTINT:          ;*****
254 011D BD0778       SBIT   INT,FLGREG        ;SET INTERRUPT OCCURED FLAG
255 0120 3158       JSR   DELAY          ;WAIT

```

TL/DD/11044-7

NATIONAL SEMICONDUCTOR CORPORATION
COP800 CROSS ASSEMBLER, REV: D1, 12 OCT 88

```

256 0122 BDEF6B          RBIT  IPND,PSW          ;RESET PENDING BIT
257 0125 8F             RETI
258
259                     ;SUPPORT ROUTINES CONTINUED
260
261                     TIMVAL: ;*****
262                     ;During continuous operation, the motor is stepped once every
263                     ;timer underflow. Therefore, a timer value is calculated that will
264                     ;produce timer underflows every X microseconds causing the motor
265                     ;to step Xsteps/second.
266                     ;For example: To step 100 times per second.
267                     ;      microseconds/step = 1000000uS/sec x 1sec/100steps = 10000
268                     ;      10000uS/step = 02718Hex uS/step
269                     ;      1uS = one count down of the timer
270                     ; Therefore, load the timer with 02718H for 100 steps/sec.
271
272 0126 DE14             LD      B,#TVAL0          ;POINT TO STORAGE FOR TIMVAL
273 0128 BD0474          IFBIT  4,CMD          ;IF LOWEST SPEED BIT SET
274 012B 17             JP      SLOWER          ;THEN USE SLOWEST SPEED
275 012C BD0475          IFBIT  5,CMD          ;IF SECOND LOWEST SPD BIT SET
276 012F 0E             JP      SLOW          ;THEN USE SLOW SPEED
277 0130 BD0476          IFBIT  6,CMD          ;IF SECOND HIGHEST SPD BIT SET
278 0133 05             JP      FAST          ;THEN USE FAST SPEED
279 0134 9A02           FASTER: LD      [B+],#02          ;ELSE USE FASTEST SPEED
280 0136 9E08           LD      [B],#08          ;400steps/sec = 2rev/sec
281 0138 8E             RET
282 0139 9A88           FAST:  LD      [B+],#088          ;200steps/sec = 1rev/sec
283 013B 9E13           LD      [B],#013
284 013D 8E             RET
285 013E 9A18           SLOW:  LD      [B+],#018          ;100steps/sec = .5rev/sec
286 0140 9E27           LD      [B],#027
287 0142 8E             RET
288 0143 9A54           SLOWER: LD     [B+],#054          ;25steps/sec = .125rev/sec
289 0145 9E9C           LD      [B],#09C
290 0147 8E             RET
291
292
293                     SPEED: ;*****
294                     ;COMPARE CURRENT MOTOR SPEED WITH DESIRED MOTOR SPEED
295 0148 3126           JSR      TIMVAL          ;CALCULATED DESIRED SPEED VAL
296 014A 9D14           LD      A,TVAL0
297 014C BDEC82          IFEQ   A,TAULO          ;IF DESIRED LBYTE EQUALS CURRENT LBYTE
298 014F 01             JP      TSTHI          ;THEN GO TEST HI-BYTE
299 0150 8D             RETSK          ;ELSE NOT EQUAL RETURN AND SKIP
300 0151 9D15           TSTHI: LD     A,TVAL1
301 0153 BDED82          IFEQ   A,TAUHI          ;IF HI-BYTE EQUALS CURRENT HI-BYTE
302 0156 8E             RET          ;THEN DESIRED = CURRENT RETURN
303 0157 8D             RETSK          ;ELSE DESIRED != CURRENT RET & SKIP
304
305                     DELAY: ;*****
306                     ;INSERT A DELAY

```

TL/DD/11044-8

NATIONAL SEMICONDUCTOR CORPORATION
COP800 CROSS ASSEMBLER, REV: D1, 12 OCT 88

```

307 0158 D301          LD      0F3,#01          ;FOR SINGLE STEP & EXTINT DEBOUNCE
308 015A D4FF          DLY1: LD      0F4,#0FF        ;APPROX .256mS X 6
309 015C C4            DLY2: DRSZ   0F4
310 015D FE            JP      DLY2
311 015E C3            DRSZ   0F3
312 015F FA            JP      DLY1
313 0160 8E            RET
314
315                    .END
    
```

TL/DD/11044-9

B	00FE	BUSY	0002	*	CCW	0003	CHKSPD	0064
CMD	0004	CNTRL	00EE		CONT	005F	CREG0	00F0
CREG1	00F1	CW	0002		DELAY	0158	DIR	0001
DLY1	015A	DLY2	015C		DO	005A	DO2	0058
DPTR	00A0	ENI	0001	*	ENTI	0004	EXTINT	011D
FAST	0139	FASTER	0134	*	FLGREG	0007	GIE	0000
GO	0000	IEDG	0002	*	INT	0000	IPND	0003
IPTR	00B1	MID	0055	*	MODE	0002	MS0	0000
MS1	0001	MS2	0002	*	MS3	0003	MSEL	0003
NS	0005	NXTVAL	0098		OUT	0086	PORTD	00DC
PORTGC	00D5	PORTGD	00D4		PORTGP	00D6	PORTI	00D7
PORTLC	00D1	PORTLD	00D0		PORTLP	00D2	PSW	00EF
READY	0001	SETGO	0067		SIOR	00E9	SLOW	013E
SLOWER	0143	SP	00FD		SPEED	0148	SS	0004
SSTEP	0041	STEPS	0005	*	STOP	003B	STPPTR	00F2
TAUHI	00ED	TAULO	00EC		TC1	0007	TC2	0006
TC3	0005	TIMVAL	0126		TMRHI	00EB	TMRINT	010B
TMRLO	00EA	TMRSET	008E		TOP	0025	TP2	0053
TPND	0005	TRUN	0004		TSTHI	0151	TVAL0	0014
TVAL1	0015	WAIT	0081		WRVAL	00A7	X	00FC

TL/DD/11044-10

MACRO TABLE

NO WARNING LINES

NO ERROR LINES

282 ROM BYTES USED

SOURCE CHECKSUM = 80C0
OBJECT CHECKSUM = 0520

INPUT FILE C:MOTOR.MAC
LISTING FILE C:MOTOR.PRN
OBJECT FILE C:MOTOR.LM

TL/DD/11044-11

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation
2900 Semiconductor Drive
P.O. Box 58090
Santa Clara, CA 95052-8090
Tel: 1(800) 272-9959
TWX: (910) 339-9240

National Semiconductor GmbH
Livry-Gargan-Str. 10
D-82256 Fürstenfeldbruck
Germany
Tel: (81-41) 35-0
Telex: 527849
Fax: (81-41) 35-1

National Semiconductor Japan Ltd.
Sumitomo Chemical
Engineering Center
Bldg. 7F
1-7-1, Nakase, Mihama-Ku
Chiba-City,
Ciba Prefecture 261
Tel: (043) 299-2300
Fax: (043) 299-2500

National Semiconductor Hong Kong Ltd.
13th Floor, Straight Block,
Ocean Centre, 5 Canton Rd.
Tsimshatsui, Kowloon
Hong Kong
Tel: (852) 2737-1600
Fax: (852) 2736-9960

National Semicondutores Do Brazil Ltda.
Rue Deputado Lacorda Franco
120-3A
Sao Paulo-SP
Brazil 05418-000
Tel: (55-11) 212-5066
Telex: 391-1131931 NSBR BR
Fax: (55-11) 212-1181

National Semiconductor (Australia) Pty. Ltd.
Building 16
Business Park Drive
Monash Business Park
Nottingham, Melbourne
Victoria 3168 Australia
Tel: (3) 558-9999
Fax: (3) 558-9998

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated