



1 Photo

The photographs below show the PMP10299 Rev A assembly. This circuit was built on a PMP10299 Rev A PCB.

Top side




Bottom side



2 Converter Efficiency

The efficiency data are shown in the tables and graph below with 220V_{AC}/50Hz input.



120V_{AC}/60Hz

Vin(ac)	Iin(A)	Pin(W)	Vo1(V)	Io1(A)	Vo2(V)	Io2(A)	Vo3(V)	Io3(A)	Pout(W)	Eff. (%)
120.05	0.24	11.222	12.31	0.306	-12.47	0.301	4.66	0.202	8.452	75.32%
120.05	0.21	9.459	12.31	0.249	-12.47	0.251	4.59	0.199	7.105	75.12%
120.05	0.17	7.817	12.33	0.201	-12.50	0.200	4.53	0.197	5.866	75.05%
120.05	0.14	5.971	12.36	0.152	-12.54	0.150	4.57	0.152	4.455	74.60%
120.05	0.10	4.103	12.37	0.101	-12.54	0.101	4.63	0.100	2.981	72.64%
120.06	0.06	2.285	12.36	0.050	-12.55	0.051	4.70	0.050	1.492	65.31%
120.06	0.04	1.407	12.38	0.025	-12.58	0.026	4.78	0.025	0.752	53.44%


220V_{AC}/50Hz

Vin(ac)	Iin(A)	Pin(W)	Vo1(V)	Io1(A)	Vo2(V)	Io2(A)	Vo3(V)	Io3(A)	Pout(W)	Eff. (%)
220.3	0.15	10.830	12.39	0.301	-12.54	0.300	4.67	0.202	8.438	77.92%
220.3	0.13	9.284	12.38	0.251	-12.54	0.250	4.60	0.198	7.159	77.11%
220.3	0.12	7.761	12.38	0.202	-12.55	0.201	4.55	0.197	5.911	76.16%
220.3	0.09	5.984	12.37	0.152	-12.55	0.151	4.58	0.152	4.466	74.64%
220.3	0.07	4.168	12.37	0.101	-12.54	0.100	4.63	0.100	2.978	71.46%
220.3	0.04	2.406	12.37	0.050	-12.55	0.050	4.71	0.049	1.485	61.71%
220.3	0.03	1.461	12.39	0.025	-12.57	0.025	4.77	0.025	0.748	51.22%


3 Startup

The output voltages at startup are shown in the images below.

3.1 Start Up @ 120V_{AC}: 12V/0.3A, -12V/0.3A, 5V/0.2A.



3.2 Start Up @ 120V_{AC}: no load.



4 Cross regulation


Output voltage cross regulation is tested at 220V_{AC}/50Hz input.

I _{12V} (A)	I _{-12V} (A)	I _{5V} (A)	V _{12V} (V)	V _{-12V} (V)	V _{5V} (V)
0.3021	0.3008	0.1989	12.17	-12.32	4.591
0.3037	0.3008	0	12.23	-12.35	5.036
0.3094	0	0	12.46	-14.47	5.138
0.3091	0	0.196	12.45	-14.68	4.519
0	0	0.2012	12.59	-13.37	2.242
0	0.3008	0.1977	14.43	-12.51	4.562
0	0.3008	0	14.45	-12.51	5.421
0	0	0	12.48	-12.84	4.891
V _{out_max}			14.45	-12.32	5.421
V _{out_min}			12.23	-14.68	2.242
ΔV			2.22	2.36	3.179


5 Output Ripple Voltages

The output ripple voltages are shown in the plots below at full load (12V/0.3A, -12V/0.3A and 5V/0.2A) with 120V_{AC}/60Hz.


5.1 12V_{ripple}



5.2 -12V_{ripple}




5.3 5V_{ripple}




6 Switching Waveforms

The images below show key switching waveforms of PMP10299RevA. The waveforms are measured with 12V/0.3A, -12V/0.3A and 5V/0.2A full load.

6.1 Voltage at U1 pin 8 @ 100V_a/60Hz



6.2 Voltage at U1 pin 8 @ 265V_a/50Hz



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com